



|                        |               |                               |           |
|------------------------|---------------|-------------------------------|-----------|
| <b>EAN:</b>            | 4013288155672 | <b>Size:</b>                  | 89x7x6 mm |
| <b>Part number:</b>    | 05134658001   | <b>Weight:</b>                | 19 g      |
| <b>Article number:</b> | 867/4 IPR     | <b>Country of origin:</b>     | CZ        |
|                        |               | <b>Customs tariff number:</b> | 82079030  |

- For recessed TORX PLUS® IPR screws with safety pin
- TORX PLUS® IPR bit with bore hole on the output side
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)

High quality bits for recessed TORX PLUS® screws with safety pin. A 5-flank TORX PLUS® profile with bore hole. 1/4" hexagon, suitable for holders as per DIN ISO 1173-F 6.3.

**Web link**

<https://www.wera.de/en/05134658001>

Wera - 867/4 IPR

05134658001 - 4013288155672

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

For recessed TORX PLUS® IPR screws with safety pin





Tough bits



A 5-flank TORX PLUS® profile with a borehole. This drive geometry has only five flanks instead of the usual six and a borehole to protect safety screws against unauthorised unfastening. The screws cannot be turned with conventional, widely available tools.

Tough Wera bits prevent the tip from breaking prematurely. Z-bits usually are the bit for universal screwdriving applications.

Further versions in this product family:

|                    |  |  |  |  |
|--------------------|--|--|--|--|
|                    |  | mm   | inch   | mm   |
| 05160821001        | 10 IPR   | 50   | 2"   | 4.0  |
| 05134657001        | 10 IPR   | 89   | 3 1/2"   | 4.0  |
| 05134654001        | 15 IPR   | 50   | 2"   | 4.0  |
| 05134720001        | 15 IPR   | 89   | 3 1/2"   | 4.0  |
| 05204126001        | 20 IPR   | 50   | 2"   | 4.5  |
| 05259135001        | 20 IPR   | 89   | 3 1/2"   | 4.5  |
| 05134655001        | 25 IPR   | 50   | 2"   | 6.0  |
| 05134722001        | 25 IPR   | 89   | 3 1/2"   | 6.0  |
| 05134656001        | 27 IPR   | 50   | 2"   | 6.0  |
| <b>05134658001</b> | <b>27 IPR</b>  | <b>89</b>  | <b>3 1/2"</b>  | <b>6.0</b>   |
| 05134732001        | 30 IPR   | 50   | 2"   | 6.0  |
| 05134723001        | 30 IPR   | 89   | 3 1/2"   | 6.0  |

**Web link**

<https://www.wera.de/en/05134658001>

Wera - 867/4 IPR

05134658001 - 4013288155672

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)