

• TRUSTED QUALITY SINCE 1921 •

RUST-OLEUM®
Transformations®**RUST-OLEUM® TRANSFORMATIONS®**
DECORATIVE GLAZE**DESCRIPTION AND USES**

Rust-Oleum® Transformations® Decorative Glaze allows you to add a custom antique finish to any painted surface. This semi-transparent Decorative Glaze has a long open time, allowing you to customize your handcrafted final look. Great for cabinetry, furniture, accessories and more. Ideal for painted wood, laminate, melamine, or metal surfaces.

PRODUCTS**SKU DESCRIPTION (1 Quart)**

266227	Java Brown
402677	Charcoal Gray

COMPANION PRODUCTS**SKU DESCRIPTION (1 Quart)**

402676	Transformations Protective Topcoat - Clear Semi-Gloss
--------	---

PRODUCT APPLICATION**SURFACE PREPARATION**

The Decorative Glaze must be applied over a clean, fully cured, and painted surface. For best results, apply over a non-glossy finish. Test glaze in a small area first before applying on entire project.

To get a high-end look, a cheesecloth or lint-free rag should be used to remove portions of the Decorative Glaze. To complete your project, use the Transformations Protective Topcoat to seal in the Decorative Glaze finish.

PRODUCT APPLICATION (cont.)**APPLICATION**

Apply when air (ambient) temperature is between 50°F (10°C) and 95°F (35°C) and the relative humidity is below 70%.

Stir thoroughly. Using a 2" synthetic brush or 2" foam brush, coat the painted surface with the Decorative Glaze. Be certain to get the Decorative Glaze in all corners, crevices, and raised panel sections. Using a cheesecloth, wipe the surface (using varying pressure) in the direction of the grain or brush marks to remove the Decorative Glaze to the desired look. If you are not satisfied with the appearance of the Decorative Glaze, wipe the surface down completely while the glaze is still wet with a clean, damp rag and repeat the glazing process.

Let dry a minimum of 8 hours and finish by applying the Transformations Protective Topcoat to seal in the Decorative Glaze finish.

NOTE: The Decorative Glaze will be very subtle over dark paint colors.

COVERAGE

Up to 200 sq. ft. per qt.

CLEANUP

Soap and water.

	TECHNICAL DATA	CAB-02
• TRUSTED QUALITY SINCE 1921 • RUST-OLEUM® Transformations®	RUST-OLEUM® TRANSFORMATIONS® DECORATIVE GLAZE	

PHYSICAL PROPERTIES

		DECORATIVE GLAZE
Resin Type		Acrylic
Pigment Type		Varies depending on color
Weight	Per Gallon	8.67 lbs.
	By Liter	1.04 kg
Volatile Organic Compounds		<860 g/L (7.15 lbs./gal.)
Practical Coverage at Recommended DFT (assumes 15% material loss)		150-200 sq.ft./qt (13.9-18.6 m²/qt)
Dry Times at 70-80°F (21-27°C) and 50% Relative Humidity		8 hours
Shelf Life		3 years
Flash Point		>200°F (93°C)
Safety Information		For additional information, see SDS

Calculated values are shown and may vary from the actual manufactured material.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.



Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, Illinois 60061

Phone: 800-901-0411
www.rustoleum.com

Form: GDH-44
Rev.: 030326