MEESE

95PSL SHELF-TRUX® with Split Lid and Door
PRODUCT INFO SHEET



The 95PSL combines the double protection of a solid top and durable, lockable doors in an oversized design to deliver and return large volumes



Three, ventilated, plastic, repositionable shelves separate linens onto four levels and may be slid into vertical position for use as a bulk bin.



Sporting smooth, sleek looks and protective security features, the 95PSL is often specified for luxury properties.

Overview: The smooth, sleek, secure 95PSL bulk truck comes with three shelves and a solid lid, providing a secure, organized option for delivery of linens, most often in a healthcare setting.

Benefits: The 95PSL has a split lid and durable, lockable doors in an oversized design, offering security and protection from the elements. Its three ventilated, poly, removeable and repositionable shelves provide a clean, flexible and organized way to transport linens. These shelves can also be slid into the vertical position to be used as a bulk bin to transport soiled linens. It is made of the stronger and lighter High Density Polyethylene (HDPE) compared to Linear Low Density Polyethylene (LLDPE), common with many competitors. And the 95PSL, like all Meese carts, has a metal free interior to avoid snags and tears.

Standard Features

- Rotationally molded from waterproof, chemical-resistant High Density Polyethylene (HDPE)
- Torque-resistant, molded-in inserts
- Heavy duty powder coated, steel base
- Split, hinged top for ergonomic access
- Pull strap on top for easy closing
- Three, removable, ventilated, plastic shelves in colonial white
- Molded-in, recessed handles
- Two, double-wall, molded doors that swing 270 degrees flush against cart side
- Molded-in door, reinforcing bars
- Stainless steel latch and security lock
- Four 8" x 2,"gray rubber non-marking Colson casters
- Drain holes

Featured Options (May affect shipping weight)

- Stencil, Mold-in or Mold-on text, logos or graphics
- Wire shelves
- Nylon cart covers
- Four 6" x 2,"gray rubber non-marking premium casters

Dimensions 58" L x 30½" W x 72" O.A.H.
Capacity 40 Bushels/49 cubic feet
Load Capacity 900 lbs.
Shipping Weight 303 lbs. for standard part only
NOTE: Non-nesting containers; (33) per standard trailer

Color Selections

Red #186C	Forest Green #3308C	Royal Blue #2727C	Brilliant Orange #171C	Metallic Silver/ Cool Gray 6	Cadet Blue #303C	Black	Jade Green #16-5942 TPX

1745 Cragmont Street ■ Madison, Indiana 47250-2874 ■ 800-829-4535 ■ Fax: 812-273-1878 ■ meese-inc.com ■ e-mail: customerservice@meese-inc