



G-Tek® PolyKor® X7™

Seamless Knit PolyKor™ X7™ Blended Glove with Double-Dipped Nitrile Coated MicroSurface Grip on Full Hand - Touchscreen Compatible

- Seamless construction offers increased comfort and breathability
- PolyKor™ blended shell with X7™ technology is super light-weight and thin, offering exceptional cut resistance and durability in a thin liner configuration
- Nitrile MicroSurface coatings are impermeable providing an elevated grip in dry and oily conditions, infused with thousands of tiny suction cup pockets that create a vacuum effect that dispenses fluids away on contact
- Double-Dipped nitrile coating on the full hand helps keep hands dry, extends the life of the glove and provides excellent abrasion resistance
- Microsurface nitrile palm provides excellent grip in dry, wet & oily conditions
- Touchscreen compatible to allow the user to operate a touch screen phone or device without removing gloves

Applications

- Secure Dry Grip and Oil Resistant
- Handling and Assembly of Medium to Large Parts and Materials
- Metal Fabrication
- Mechanical Equipment Maintenance and Repair
- Heavy to Medium Fastening and Anchoring



Technical Data

Color	Blue
Sizes Available	XS-2XL
Packaging	Pair Bagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	17.32 x 11.81 x 11.02
Case Weight (lbs)	8.60
Country of Origin	China
Liner Material	PolyKor X7
Coating	Nitrile
Coating Color	Black
Coating Coverage	Full Hand
Grip	MicroSurface
Gauge	18
Cuff	Knit Wrist
Construction	Coated Seamless Knit, Touchscreen Compatible,
Certifications	Silicone Free
Product Circularity	Reusable / Launderable

Performance Data

Cut Level	A4
ANSI Abrasion Level	6
ANSI Puncture Level	3
EN 388	4X42C

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-16

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
16-939/XS	Blue	XS	616314347238	1061634347235	2061634347232
16-939/S	Blue	S	616314266058	01616314266057	02616314266056
16-939/M	Blue	M	616314266065	01616314266064	02616314266063
16-939/L	Blue	L	616314266072	01616314266071	02616314266070
16-939/XL	Blue	XL	616314266089	01616314266088	02616314266087
16-939/XXL	Blue	2XL	616314266096	01616314266095	02616314266094