

CONTRACTOR MASKING TAPE

PREMIUM



AmTape® Contractor Masking Tape features Cellux® semi-crepe paper technology for reliable, cost-effective performance in construction, automotive, and marine use. It offers strong adhesion and clean outdoor removal for up to 30 days of UV exposure — ideal for surface protection and labeling.

Surfaces

Wood – Metal – Glass -Plastic

1 Quick Snapshot (Visual Summary)

Feature	Value
Use	Indoor / Outdoor
Adhesive Type	Acrylic
UV Resistance	Up to 30 days
Clean Removal	Up to 30 days
Paper Type	Advanced Cellux® technology super semi-crepe paper
Available color	Yellow ●

3 Ideal Uses

- Professional painting with water-based or solvent-based paints.
- Masking door and window frames before painting.
- Architectural and design projects.
- Protecting machinery and tools from dust and overspray.
- Temporary marking on floors, walls, wood, metal, during renovations.

2 Technical Performance

Property	Imperial	Metric
Adhesion to steel	8 - 12 oz/in	3.2 N/25mm
Tensile strength	20 lbs/in	35 N/10mm
Residue after removal	Visual inspection	None
Temperature Range	248°F	120°C

4 Premium Insights (Why It Stands Out)

- Super Semi-crepe technology - Clean lines, zero bleed, solvent resistance.
- Smart adhesive - Strong hold, easy removal without residue
- Extended UV/weather exposure capabilities – up to 30 days
- Sticks to masking film and paper film.

5 Product Reference

Customization: OEM branding and special colors available (MOQ required)

SKU	Size / Description	Cases/pallet	Roll/Case
CON001-12060PK1	0.47"(12mm)x60 yd(54.8m) Yellow 30 days outdoor contractor masking tape - individually packaged	64	48
CON001-18060PK1	0.70"(18mm)x60 yd(54.8m) Yellow 30 days outdoor contractor masking tape - individually packaged	64	32
CON001-24060PK1	0.94"(24mm)x60 yd(54.8m) Yellow 30 days outdoor contractor masking tape - individually packaged	64	24
CON001-36060PK1	1.41"(36mm)x60 yd(54.8m) Yellow 30 days outdoor contractor masking tape - individually packaged	64	16
CON001-48060PK1	1.88"(48mm)x60 yd(54.8m) Yellow 30 days outdoor contractor masking tape - individually packaged	64	12
CON001-72060PK1	2.83"(72mm)x60 yd(54.8m) Yellow 30 days outdoor contractor masking tape - individually packaged	64	8

6 Usage Recommendations

- Apply on clean, dry surfaces
- Press down firmly to ensure full adhesion
- Remove at a 45° angle after job completion
- Avoid removing tape when paint is still wet to prevent tearing or lifting.



WE STICK STRONG