



JSP® Evolution® Deluxe 6151 Cap Style Hard Hat with HDPE Shell, 6-Point Polyester Suspension and Wheel Ratchet Adjustment

- High-Density Polyethylene (HDPE) shell designed with five raised channels running across the top for strength, and an extended back area for extra protection
- 6-Point polyester textile suspension system offers unrivaled comfort without compromising performance
- Unique "3D Adjustment" provides a precise fit using harness depth settings unlike any other hard hat on the US market today
- Revolution™ Wheel Ratchet is easy to use and creates a firm comfortable fit
- Chamlon™ sweatband
- Universal accessory slots accepts virtually any competitors' accessories
- ⚠️ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Construction Applications
- Road Work
- Excavation
- Industrial Applications



Technical Data

Color	Green, White, Red, Gray, Neon Orange, Neon Yellow, Pink, Blue, Black, Yellow
Sizes Available	OS
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	23.03 x 9.45 x 17.91
Case Weight (lbs)	11.02
Country of Origin	United Kingdom
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Suspension	6 Point Polyester
Sweatband	Chamlon
Size Range	53cm-63cm
Certifications	ANSI/ISEA Z89.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Performance Data

ANSI Type	Type I
Electrical Class	Class E

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-EV6151-11	Black	OS	5038428160223	5038428813280	5038428813280
280-EV6151-50	Blue	OS	5038428136747	5038428811965	5038428811965
280-EV6151-40	Gray	OS	5038428151146	5038428812979	5038428812979
280-EV6151-30	Green	OS	5038428136730	5038428811958	5038428811958
280-EV6151-OR	Neon Orange	OS	5038428136778	5038428811996	5038428811996
280-EV6151-LY	Neon Yellow	OS	5038428136785	5038428812009	5038428812009
280-EV6151-39	Pink	OS	5038428143646	5038428812351	5038428812351
280-EV6151-60	Red	OS	5038428136754	5038428811972	5038428811972
280-EV6151-10	White	OS	5038428136716	5038428811934	5038428811934
280-EV6151-20	Yellow	OS	5038428136723	5038428811941	5038428811941