



G-Tek® PosiGrip®

Seamless Knit Nylon Glove with Polyurethane Coated Flat Grip on Palm & Fingers - 15 Gauge

- Seamless knit nylon shell offers increased comfort, finger dexterity and breathability
- Polyurethane coatings take on the surface properties of the glove liner providing a tactile grip in dry and slightly oily conditions, ideal for applications that require dexterity for precise handling
- Silicone Free
- Knit Wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- **WARNING:** Cancer - www.P65Warnings.ca.gov

Applications

- Thin Coating, Good Grip for High Dexterity Handling
- Small Parts Handling
- Maintenance and Repair Operations
- Quality Control and Inspection



Technical Data

Color	Black
Sizes Available	XS-2XL
Packaging	Pair Bagged Plain
Packed	12 Dozen/Case
Case Dimensions (in)	20.60 x 12.10 x 12.50
Case Weight (lbs)	0.00
Country of Origin	China
Liner Material	Nylon
Coating	Polyurethane
Coating Color	Gray
Coating Coverage	Palm & Fingers
Grip	Flat
Gauge	15
Cuff	Knit Wrist
Construction	Coated Seamless Knit
Certifications	Silicone Free
Product Circularity	Recycled via Terracycle Reusable / Launderable

Performance Data

ANSI Abrasion Level	4
ANSI Puncture Level	2
EN 388	4131XX

Care Instructions



KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-03

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
715SUGB/XS	Black	XS	662909072993	20662909072997	10662909072990
715SUGB/S	Black	S	662909073006	20662909073000	10662909073003
715SUGB/M	Black	M	662909073013	20662909073017	10662909073010
715SUGB/L	Black	L	662909073020	20662909073024	10662909073027
715SUGB/XL	Black	XL	662909073037	20662909073031	10662909073034
715SUGB/XXL	Black	2XL	662909073044	20662909073048	10662909073041