



EAN:	4013288196057	Size:	122x83x15 mm
Part number:	05078605001	Weight:	55 g
Article number:	7770	Country of origin:	TW
		Customs tariff number:	82079099

- Square head insert tool 9x12 mm
- For torque wrenches from the Click-Torque X series with 9x12 mm mounting
- Application: Hexagon screw heads or nuts
- With safety pin
- The chrome-vanadium steel version makes the plug-in tools suitable for heavy loads

Open end insert, for hexagon screw heads or nuts; for torque wrenches of the Click-Torque X series with 9x12 mm holder.

Web link
<https://www.wera.de/en/05078605001>

Wera - 7770
05078605001 - 4013288196057

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Drive 9x12 mm

Chrome vanadium steel

With pin lock



For torque wrenches from the Click-Torque X series with 9x12 mm mounting.





The insert tools are suitable for high loads thanks to their chrome-vanadium steel design.



Safe working and rapid tool change thanks to the pin lock of the insert tools.

Further versions in this product family:

							
	mm	mm	mm	mm	mm	mm	mm
05078600001	9x12	7	17.5	39.5	22.9	22.6	5.0
05078601001	9x12	8	17.5	39.5	22.9	22.6	5.0
05078602001	9x12	9	17.5	41.0	24.4	26.7	5.5
05078603001	9x12	10	17.5	39.0	24.1	26.7	5.5
05078604001	9x12	11	17.5	40.9	24.3	26.7	5.5
05078605001	9x12	12	17.5	41.3	24.7	30.7	7.2
05078606001	9x12	13	17.5	40.6	24.0	30.6	7.2
05078607001	9x12	14	17.5	41.0	24.63	34.3	8.0
05078608001	9x12	15	17.5	41.0	24.4	34.5	8.0
05078609001	9x12	16	17.5	42.7	26.1	37.5	8.2
05078610001	9x12	17	17.5	42.7	26.1	37.5	8.2
05078611001	9x12	18	17.5	46.7	30.1	41.0	8.5
05078612001	9x12	19	17.5	46.7	30.1	41.0	9.2

Web link

<https://www.wera.de/en/05078605001>

Wera - 7770

05078605001 - 4013288196057

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de