



Technical Data

Color	Black
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	26.85 x 11.22 x 15.08
Case Weight (lbs)	19.84
Country of Origin	Malaysia
Lens	IR Filter
Frame Style	Over-The-Glass
Lens Color	Green
Frame Fit	Universal
Lens Coating	Anti-Scratch
Bridge	Molded
Temple	Adjustable Length, Co-Molded, Tilt Adjustment
Base Curve	3
Certifications	ANSI Z87.1
Product Circularity	Recycled via Terracycle

Bouton® Optical OverSite™ OTG Rimless Safety Glasses with Black / Gray Temple, IR Filter Shade 3.0 Lens and Anti-Scratch Coating

- Over-the-glass design helps keep prescription eyewear users in compliance
- Can also be worn by itself as a regular safety glass
- Rimless frame design ensures an unobstructed view
- Adjustable length temples are rubber co-molded, offering the user a secure custom fit
- Ratchet temples for better angle adjustment
- Molded nose bridge design to fit the vast majority of users
- U-Fit® spatula temples
- Meets ANSI Z87.1+
- Meets CSA Z94.3
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Fits Comfortably Over Personal Eyewear
- Soldering
- Torch Blazing
- Cutting

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-13

SKU Information

SKU	FRAME COLOR	LENS	LENS		UPC	UPC (INNER)	UPC (CASE)
			LENS COLOR	COATING			
250-98-0000	Black	Clear	Clear	AS	616314131165	01616314131164	02616314131163
250-98-0013	Black	IR Filter	Green	AS	616314131172	01616314131171	02616314131170
250-98-0020	Black	Clear	Clear	AS/AF	616314161964	01616314161963	02616314161962
250-98-0024	Black	IR Filter	Green	AS/AF	616314267277	01616314267276	02616314267275
250-98-0080	Black	Clear	Clear	U	616314131158	01616314131157	02616314131156

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated