

162 i PH/S SB VDE Insulated screwdriver for PlusMinus screws (Phillips/slotted), #
2 x 100 mm



EAN:	4013288186577	Size:	265x48x36 mm
Part number:	05100020001	Weight:	97 g
Article number:	162 i PH/S SB	Country of origin:	CZ
		Customs tariff number:	82054000

- Insulated blades for secure work at 1,000 volts
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- Handle markings simplify finding and sorting of tools
- Hexagonal anti-roll feature against rolling away
- Combination profile Phillips / slotted

Wera VDE screwdrivers with multi-component Kraftform Plus handle for fast and low-fatigue working: hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. Combination profile - slotted and Phillips particularly for jobs on terminal blocks, fuse boxes, switches and relays. Individually tested in water bath at 10,000 volts for secure work at the permissible voltage of 1,000 volts. The hexagonal anti-roll feature prevents any bothersome rolling away at the workplace.

Web link
<https://www.wera.de/en/05100020001>

Wera - 162 i PH/S SB
05100020001 - 4013288186577

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

PlusMinus screwdrivers



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.



For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Individually tested



The individual testing at 10,000 volts, in accordance with IEC 60900, ensures safe working with loads up to 1,000 volts.

Impact strength test



Impact strength tested at -40°C, guaranteeing safety even under extreme conditions.

Multicomponent Kraftform handle



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

Prevents hand injuries



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Rapid hand repositioning



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels through the hand.

Identification marking



All Kraftform Plus screwdrivers are marked with their drive profile and size. This enables faster and more reliable selection of the correct tool from the tool case.

162 i PH/S SB VDE Insulated screwdriver for PlusMinus screws (Phillips/slotted), #
2 x 100 mm



Set contents:

162 i PH/S VDE Insulated screwdriver for PlusMinus screws (Phillips/slotted), # 2 x 100 mm



05006381001

1x # 2 x 100 mm



Web link

<https://www.wera.de/en/05100020001>

Wera - 162 i PH/S SB

05100020001 - 4013288186577

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de