TOL SERIES

TREE OF LIGHT

2024



TOL-YOSEMITE SERIES



TOL-YOSEMITE

The TOL-YOSEMITE outdoor light features three sleek branches, offering powerful 75W illumination in a modern, natural design. Available in Black or Bronze, it's ideal for enhancing with versatile color temperatures and durable, weather-resistant construction.


TOL-YOSEMITE SERIES



TREE OF LIGHT - YOSEMITE

BRONZE / BLACK

The TOL light fixtures are built with robust construction and weather-resistant materials, ensuring long-term performance and minimal maintenance. Their durable design stands up to the elements, providing reliable and consistent illumination over time with little need for upkeep.



1. BRONZE FINISH


TOL-YOSEMITE-BR
TREE OF LIGHT
75W | 125LM/W | 3000K/4000K/5000K
BRONZE HOUSING

2. BLACK FINISH

TOL-YOSEMITE-BK
TREE OF LIGHT
75W | 125LM/W | 3000K/4000K/5000K
BLACK HOUSING

TOL-YOSEMITE SERIES

TOL-YOSEMITE COMPONENTS





3 LIGHT BARS:
25W EACH
2.2"(H) x 26.77"(W) x 2"(D)



2 "Y"
CONNECTORS
10.24"(H) x 7.8"(W) x 1.57"(D)



1 TOP CAP TO
COVER POLE
OPENING
3.31"(H) x 2.83"(D)



1 TRUNK - 2-3/4"
INSIDE DIAMETER
FITS OVER 2-1/2"
ROUND POLES
5.91"(H) x 4.72"(W) x 2.8"(D)



DECORATIVE 3-
PIECE LIGHT POLE

MUST BE
PURCHASED
SEPARATELY

*SHOWN WITH POL SYSTEM

*SEE SPEC SHEET FOR MORE INFORMATION

TOL-SEQUOIA SERIES



TOL-SEQUOIA

The TOL-SEQUOIA Tree of Light series features 4-light branches with 220W of total power, using 528 MTC 2835 LEDs. Built with durable die-cast aluminum and an opal PC lens, it's designed for outdoor spaces. Compatible with the POL series poles, it offers versatile and efficient lighting with a sleek aesthetic.


TOL-SEQUOIA SERIES



TREE OF LIGHT - SEQUOIA

BRONZE / BLACK

The TOL light fixtures are ideal for versatile outdoor use, providing effective illumination for streets, parks, and squares, and enhancing visibility across various public spaces.




1. BRONZE FINISH

TOL-SEQUOIA-BR
TREE OF LIGHT
100W | 125LM/W | 3000K/4000K/5000K
BRONZE HOUSING

2. BLACK FINISH

TOL-SEQUOIA-BK
TREE OF LIGHT
100W | 125LM/W | 3000K/4000K/5000K
BLACK HOUSING

TOL-SEQUOIA COMPONENTS





4 LIGHT BARS:
25W EACH
2.2"(H) x 26.77"(W) x 2"(D)



3 "Y"
CONNECTORS
10.24"(H) x 7.8"(W) x 1.57"(D)



1 TOP CAP TO
COVER POLE
OPENING
3.31"(H) x 2.83"(D)



1 TRUNK - 2-3/4"
INSIDE DIAMETER
FITS OVER 2-1/2"
ROUND POLES
5.91"(H) x 4.72"(W) x 2.8"(D)



DECORATIVE 3-
PIECE LIGHT POLE

MUST BE
PURCHASED
SEPARATELY

*SHOWN WITH POL SYSTEM

*SEE SPEC SHEET FOR MORE INFORMATION

TOL-KINGS SERIES



TOL- KINGS

The TOL-KINGS series showcases a dynamic design with 6-light branches and 150W of powerful illumination. Its sleek and modern style ensures an eye-catching presence while delivering efficient lighting for streets, parks, and squares.

TOL-KINGS SERIES



TREE OF LIGHT - KINGS

Engineered for wet location use, making them ideal for environments exposed to moisture and precipitation. With a robust design and IP65 rating, these fixtures provide reliable performance and durability in challenging conditions.

BRONZE / BLACK




1. BRONZE FINISH

TOL-KINGS-BR
TREE OF LIGHT
150W | 125LM/W | 3000K/4000K/5000K
BRONZE HOUSING

2. BLACK FINISH

TOL-KINGS-BK
TREE OF LIGHT
150W | 125LM/W | 3000K/4000K/5000K
BLACK HOUSING

TOL-KINGS COMPONENTS





6 LIGHT BARS:
25W EACH
2.2"(H) x 26.77"(W) x 2"(D)



3 "Y"
CONNECTORS
10.24"(H) x 7.8"(W) x 1.57"(D)



1 TOP CAP TO
COVER POLE
OPENING
3.31"(H) x 2.83"(D)



3 TRUNK - 2-3/4"
INSIDE DIAMETER
FITS OVER 2-1/2"
ROUND POLES
5.91"(H) x 4.72"(W) x 2.8"(D)



DECORATIVE 3-
PIECE LIGHT POLE

MUST BE
PURCHASED
SEPARATELY

*SHOWN WITH POL SYSTEM

*SEE SPEC SHEET FOR MORE INFORMATION

TOL-JOSHUA SERIES



TOL- JOSHUA

The TOL-JOSHUA Tree of Light series features a striking 9-light post top design with 225W MTC 2835 LEDs. Its bronze/black finish and durable die-cast aluminum construction make it ideal for brightening with style and efficiency.


TOL-JOSHUA SERIES



TREE OF LIGHT - JOSHUA

BRONZE / BLACK

The TOL light fixtures provide customizable lighting with various color temperature options, allowing you to adjust illumination to suit different environments and personal preferences. This flexibility ensures the perfect ambiance and optimal performance for any setting.



1. BRONZE FINISH

TOL-JOSHUA-BR
TREE OF LIGHT
225W | 125LM/W | 3000K/4000K/5000K
BRONZE HOUSING

2. BLACK FINISH

TOL-JOSHUA-BK
TREE OF LIGHT
225W | 125LM/W | 3000K/4000K/5000K
BLACK HOUSING

TOL-JOSHUA SERIES

TOL-JOSHUA COMPONENTS





9 LIGHT BARS:
25W EACH
2.2"(H) x 26.77"(W) x 2"(D)



6 "Y"
CONNECTORS
10.24"(H) x 7.8"(W) x 1.57"(D)



1 TOP CAP TO
COVER POLE
OPENING
3.31"(H) x 2.83"(D)



3 TRUNK - 2-3/4"
INSIDE DIAMETER
FITS OVER 2-1/2"
ROUND POLES
5.91"(H) x 4.72"(W) x 2.8"(D)



DECORATIVE 3-
PIECE LIGHT POLE

MUST BE
PURCHASED
SEPARATELY

*SHOWN WITH POL SYSTEM

*SEE SPEC SHEET FOR MORE INFORMATION

TOL-REDWOOD SERIES



TOL- REDWOOD

The TOL-Redwood series delivers exceptional lighting with its impressive 12-light branch configuration and 275W power. Its multi-color temperature options provide flexible ambiance for any setting, while its robust design ensures long-lasting performance.


TOL-REDWOOD SERIES



TREE OF LIGHT - REDWOOD

BRONZE / BLACK

The TOL light fixtures offer a user-friendly design that streamlines installation. Their compatibility with standard mounting options ensures a smooth and efficient setup, minimizing installation time and effort.



1. BRONZE FINISH

TOL-REDWOOD-BR
TREE OF LIGHT
275W | 125LM/W | 3000K/4000K/5000K
BRONZE HOUSING

2. BLACK FINISH

TOL-REDWOOD-BK
TREE OF LIGHT
275W | 125LM/W | 3000K/4000K/5000K
BLACK HOUSING

TOL-REDWOOD SERIES

TOL-REDWOOD COMPONENTS





11 LIGHT BARS:
25W EACH
2.2"(H) x 26.77"(W) x 2"(D)



8 "Y"
CONNECTORS
10.24"(H) x 7.8"(W) x 1.57"(D)



1 TOP CAP TO
COVER POLE
OPENING
3.31"(H) x 2.83"(D)



4 TRUNK - 2-3/4"
INSIDE DIAMETER
FITS OVER 2-1/2"
ROUND POLES
5.91"(H) x 4.72"(W) x 2.8"(D)



DECORATIVE 3-
PIECE LIGHT POLE

MUST BE
PURCHASED
SEPARATELY

*SHOWN WITH POL SYSTEM

*SEE SPEC SHEET FOR MORE INFORMATION

TOL-A SERIES



TOL-A1-1L

25W | 125LM/W | 3000K/4000K/5000K
BRONZE/BLACK HOUSING
1.97" Dia x 29.92" W x 27.17" H



TOL-A2-1L

25W | 125LM/W | 3000K/4000K/5000K
BRONZE/BLACK HOUSING
1.97" Dia x 29.33" W x 27.36" H



TOL-A2-3L

75W | 125LM/W | 3000K/4000K/5000K
BRONZE/BLACK HOUSING
1.97" Dia x 29.33" W x 27.36" H



TOL-A3-3L

75W | 125LM/W | 3000K/4000K/5000K
BRONZE/BLACK HOUSING
1.97" Dia x 28.35" W x 22.05" H



TOL-A4-4L

100W | 125LM/W | 3000K/4000K/5000K
BRONZE HOUSING
1.97" Dia x 26.38" W x 27.36" H

Customizable Geometric Lighting

1 to 4 Light Configurations

POL SERIES



LIGHT POLE SYSTEM

BRONZE / BLACK

The POL series light poles offer stylish support for the TOL series, available in 120in and 144in heights. These decorative poles feature a 2.36in tenon and come in sleek black or bronze finishes, adding both elegance and durability to your lighting setup.

1. BLACK FINISH

POL-D1-120-3PC-BK
LIGHT POLE EXTENSIONS
120" | 3PC. | 2.36" TENON
BLACK FINISH

2. BRONZE FINISH


POL-D1-120-3PC-BR
LIGHT POLE EXTENSIONS
120" | 3PC. | 2.36" TENON
BRONZE FINISH

3. BLACK FINISH

POL-D1-144-3PC-BK
LIGHT POLE EXTENSIONS
144" | 3PC. | 2.36" TENON
BLACK FINISH

4. BRONZE FINISH

POL-D1-144-3PC-BR
LIGHT POLE EXTENSIONS
144" | 3PC. | 2.36" TENON
BRONZE FINISH



POL-D1-BASECVR



POL-D1-ABK

