



| | | | |
|------------------------|-----------------|-------------------------------|--------------|
| EAN: | 4013288227461 | Size: | 100x45x20 mm |
| Part number: | 05005523001 | Weight: | 102 g |
| Article number: | 8790 B Impaktor | Country of origin: | TW |
| | | Customs tariff number: | 82042000 |

- For use with electric or pneumatic wrenches with 3/8" drive
- Impaktor technology for above-average service life
- Hexagon profile allows precise and profile-friendly screwdriving with high power transmission
- With Take it easy tool finder: colour coding by size
- With cross hole and ring socket to attach the safety pin and safety ring of machine operated tools

Impaktor socket wrench insert for use with electric or pneumatic wrenches with 3/8" drive. The Impaktor technology ensures a higher-than-average service life even at extreme requirements. With Take it easy Tool finder with colour coding by size - for quick and easy identification of the required tool. With hexagon profile and socket with hole. The hexagon profile offers the transmission of high forces and loads the edges of the bolt or the screw head less than a double hexagon profile. For external hexagon bolts and screws.

Web link

<https://www.wera.de/en/05005523001>

Wera - 8790 B Impaktor
05005523001 - 4013288227461

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

For electric or pneumatic wrenches



The Impaktor technology ensures above-average service life of the Impaktor socket wrench plug-ins even under extreme conditions.

Cross hole and ring socket



Thanks to the hole and the ring socket, the tools can be held securely on the power tool with a safety pin or an O-ring.

Profile-friendly power transmission



The hexagon profile offers the transmission of high forces and loads the edges of the bolt or the screw head less than a double hexagon profile. Fine-toothed ratchets also make use of a double hexagon profile superfluous, even in confined spaces, thanks to their small return angle.

Take it easy tool finder system



Take it easy tool finder system - with profile and size colour-coding for quick and easy tool selection. Colour-coded system for hexagon drive screws (L-Keys, Zyklop bit sockets), external hex drive screws and nuts (Joker wrenches, Zyklop sockets and Zyklop bit sockets with holding function), and TORX® drive screws (L-Keys, Zyklop bit sockets).






Web link

<https://www.wera.de/en/05005523001>

Wera - 8790 B Impaktor
05005523001 - 4013288227461

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Further versions in this product family:

| | |  |  |  |  |  |
|--------------------|--------------------|---|---|--|---|---|
| | | mm | inch | mm | mm | mm |
| 05005500001 | leuchtpink_232C | 8.0 | - | 30.0 | 14.1 | 19.0 |
| 05005501001 | leuchtgelb_yellowC | 10.0 | - | 30.0 | 16.6 | 19.0 |
| 05005502001 | cyan_2985C | 11.0 | - | 30.0 | 17.8 | 19.0 |
| 05005503001 | schwarz_blackC | 12.0 | - | 30.0 | 18.2 | 19.0 |
| 05005504001 | tuerkis_339C | 13.0 | - | 30.0 | 20.0 | 22.0 |
| 05005505001 | pink_241C | 14.0 | - | 30.0 | 21.0 | 22.0 |
| 05005506001 | weiss | 15.0 | - | 30.0 | 22.0 | 22.0 |
| 05005507001 | violett_2735C | 16.0 | - | 30.0 | 22.0 | 24.0 |
| 05005508001 | rot_200C | 17.0 | - | 30.0 | 23.0 | 25.0 |
| 05005509001 | gruen_363C | 18.0 | - | 30.0 | 23.0 | 26.0 |
| 05005510001 | blau_307C | 19.0 | - | 30.0 | 25.0 | 27.8 |
| 05005511001 | gruen_363C | 21.0 | - | 32.0 | 27.0 | 30.0 |
| 05005512001 | gelb_123C | 22.0 | - | 32.0 | 28.0 | 32.0 |
| 05005513001 | cyan_2985C | 24.0 | - | 32.0 | 30.0 | 34.0 |
| 05005514001 | gelb_123C | - | 1/4" | 30.0 | 11.0 | 19.0 |
| 05005515001 | blau_307C | - | 5/16" | 30.0 | 14.1 | 19.0 |
| 05005516001 | rot_200C | - | 3/8" | 30.0 | 16.6 | 19.0 |
| 05005517001 | violett_2735C | - | 7/16" | 30.0 | 17.8 | 19.0 |
| 05005518001 | tuerkis_339C | - | 1/2" | 30.0 | 20.0 | 22.0 |
| 05005519001 | pink_241C | - | 9/16" | 30.0 | 21.0 | 22.0 |
| 05005520001 | schwarz_blackC | - | 5/8" | 30.0 | 22.0 | 24.0 |
| 05005521001 | cyan_2985C | - | 11/16" | 30.0 | 23.0 | 25.0 |
| 05005522001 | gelb_123C | - | 3/4" | 30.0 | 25.0 | 28.0 |
| 05005523001 | blau_307C | - | 13/16" | 32.0 | 27.0 | 30.0 |
| 05005524001 | leuchtgruen_375C | - | 7/8" | 32.0 | 28.0 | 32.0 |
| 05005525001 | rot_200C | - | 15/16" | 32.0 | 30.0 | 34.0 |
| 05005526001 | tuerkis_339C | - | 1" | 32.0 | 32.0 | 36.0 |

Web link

<https://www.wera.de/en/05005523001>

Wera - 8790 B Impaktor
 05005523001 - 4013288227461

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de