



jalas® ZENIT EVO 7158

ASTM F2413-18 M/I/C/SD 35/PR ASTM F3445-21 SR EN ISO 20345:2022 S1, PL, SR, FO, SC

Learn more

COMFORTABLE AND A LITTLE MORE COLORFUL.

A comfortable safety shoe with colorful sport-inspired design, BOA® Fit System and high-quality protection. A functional knitted textile upper with padded Memory foam keeps feet safe, cool and snug on long workdays. The oil-resistant RPU outer sole provides excellent grip, while our JALAS® aluminium toe cap, plasma-treated textile puncture protection and double impact protection zones in PORON® XRD® mean safe feet at work.

CHARACTERISTICS

- Excellent grip
- Perfect fit
- Extra comfortable
- Very breathable
- Excellent shock absorption
- Extremely light

FUNCTIONS

- Low weight
- Oil-resistant outsole
- Anti-static properties
- Bellows tongue
- Ventilating insole
- BOA® Fit System
- Ergonomically shaped
- Conforms with IEC 61340-5-1 (ESD)
- Free from animal-derived materials

BOA DIALED IN. PRECISION FIT.

XRD PROTECTION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Toe injuries, Nail penetration, Antistatic, Slipping

PRIMARY ENVIRONMENTS OF USE

Outdoors, Indoors, Environments with risk for outsole penetration, Dry environments, Clean environments

SPECIFICATION

TYPE Safety footwear, Low shoes
CATEGORY Cat. II
NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile
FITTING Regular
COLLECTION Zenit Evo
UPPER MATERIAL Knitted textile, Microfiber
TOECAP MATERIAL Aluminium
LINING MATERIAL Polyester
INSOLE JALAS 8303 FX3 Supreme
INNERSOLE MATERIAL Textile, Soft EVA, Rigid EVA, Polyester-based conductive thread, Neo foam, Double shock absorption zones in PORON® XRD®
MIDSOLE MATERIAL PU midsole
OUTSOLE MATERIAL RPU outsole
FASTENING BOA® Fit System
COLOUR Blue
NET WEIGHT, (SIZE 42) 1.17 kg

COMPLIANCE

CE Cat. II

EAC

TP TC 019:2011

ASTM F2413-18
M/I/C/SD 35/PR

ASTM F3445-21
SR

EN ISO 20345:2022
S1, PL, SR, FO, SC

FEATURES

- Anti-static properties
- Ergothan Shock Absorption System
- ESD
- Aluminium toecap
- Oil-resistant outsole
- Nail protection in plasma-treated composite (PTC) textile

SIZE				ARTICLE NUMBER	EAN
EU	UK	US M	US W		
35	2	3.5	4	7158-35	6408487524233
36	3	4	5	7158-36	6408487524271
37	4	5	6	7158-37	6408487524318
38	5	5.5	6.5	7158-38	6408487524356
39	6	6.5	7.5	7158-39	6408487524394
40	6.5	7.5	8.5	7158-40	6408487524431
41	7	8	9	7158-41	6408487524479
42	8	9	10	7158-42	6408487524516
43	9	9.5	11	7158-43	6408487524554
44	10	10.5	11.5	7158-44	6408487524592
45	10.5	11	12.5	7158-45	6408487524639
46	11	12	13	7158-46	6408487524677
47	12	13	14	7158-47	6408487524714
48	13	13.5	14.5	7158-48	6408487524752

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.