



Technical Data

Color	Clear
Sizes Available	OS
Packaging	Bagged Each
Packed	144 Pair/Case
Case Dimensions (in)	23.23 x 12.99 x 10.83
Case Weight (lbs)	12.35
Country of Origin	Taiwan
Lens	Clear
Frame Style	Rimless
Lens Color	Clear
Frame Fit	Universal
Lens Coating	FogLess 3Sixty, Anti-Scratch
Bridge	Rubber
Temple	Bayonet, Rubber Tips
Base Curve	9.75
Certifications	ANSI Z87.1, TAA Compliant
Product Circularity	Recycled via Terracycle

Bouton® Optical Pulse™

Rimless Safety Glasses with Clear Temple, Clear Lens and FogLess® 3Sixty™ Coating

- Lightweight, rimless design provides all day user comfort
- Universal fit nose bridge, with soft nose pads for superior comfort
- TPR temple end inserts for excellent grip
- FogLess® 3Sixty™ enhanced hydrophobic action resists lens fogging and provides clear vision in extreme working conditions
- 9.5 Base curve lens front offers wide and unobstructed vision
- ⚠ **WARNING:** Reproductive Harm - www.P65Warnings.ca.gov

Applications

- General Manufacturing
- Construction Applications
- Indoor Work

KEY: Made from recycled or bio-based Launderable Recyclable via TerraCycle®

PIP GLOBAL SAFETY | PROTECTION EMPOWERED™

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobalsafety.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2026-08-12

SKU Information

SKU	FRAME COLOR	LENS	LENS COLOR	LENS	UPC	UPC (INNER)	UPC (CASE)
				COATING			
250-49-0000	Clear	Clear	Clear	AS	616314180200	01616314180209	02616314180208
250-49-0020	Clear	Clear	Clear	AS/AF	616314166051	01616314166050	02616314166059
250-49-0021	Gray	Tinted	Gray	AS/AF	616314166068	01616314166067	02616314166066
250-49-0022	Clear	I/O	Clear	AS/AF	616314166075	01616314166074	02616314166073
250-49-0520	Clear	Clear	Clear	FL360/AS	616314232480	01616314232489	02616314232488
250-49-0521	Gray	Tinted	Gray	FL360/AS	616314232497	01616314232496	02616314232495

KEY: AF = Anti-Fog / AR = Anti-Reflective / AS = Anti-Scratch / FL360 = Fogless 3Sixty / U = Uncoated