

Highly dexterous and made with 48% Dyneema® bio-circular fiber.

TEGERA® 909

Learn more

THIN WITH BIO-CIRCULAR CUT PROTECTION

Thin and dexterous cut protection glove for fine assembly work with small sharp objects. The glove is made with 48% Dyneema® bio-circular fiber, an innovation that reduces dependence on fossil raw materials. The glove is extremely light, 18 gg, and has PU dipping for better grip. Cut resistance level B. Bulk packed.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

FUNCTIONS

- Ultra thin
- Super soft

Dyneema®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Inspection work, Building and construction, Installation work, Construction, Metalwork

PRIMARY INDUSTRIES OF USE

Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Pulp and paper, Rubber and plastics manufacturing, Transport equipment manufacturing, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Cut resistant gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Dyneema® fiber from bio-circular feedstock , Nylon, Spandex
LENGTH 210-270 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR Grey
PAIRS PER: BUNDLE/CARTON 12/120
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) TDM: 7 N
INNER MATERIAL SPECIFICATION UHMWPE (Ultra high molecular weight polyethylene), Glass fibre thread
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 3X41B

ANSI A2 CUT

ANSI 3 ABR

FEATURES

Cut protection

SIZE		ARTICLE NUMBER	EAN
5	XXS	909-5	7340118329406
6	XS	909-6	7340118300320
7	S	909-7	7340118300344
8	M	909-8	7340118300368
9	L	909-9	7340118300382
10	XL	909-10	7340118300283
11	XXL	909-11	7340118300306

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.