




Master MHD-30P 30" High Velocity, Heavy-Duty Pedestal Fan 7550 CFM, 1/4 HP, 120 Volt



- Great for your garage, barn, warehouse, or outdoor space
- All-metal heavy-duty construction for durability
- Direct-drive motor with high airflow for up to 7550 CFM
- Swivel head, adjustable height post, and OSHA-compliant safety guards
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading, 30" High Velocity Heavy-Duty Pedestal Fan. The heat of summer is no match for its powerful, direct-drive motor and long lasting, all-metal, heavy-duty construction. Plus, the swivel head and adjustable height post give you unrivaled versatility for all your cooling needs. Whether you're in the barn or working in the garage, this fan will do the job while giving your A/C and wallet a rest. **Master – built for power.**



Features and Benefits

- Great for your garage, barn, warehouse, or outdoor space
- All metal, heavy-duty construction
- Direct-drive motor with airflow up to 7550 CFM
- 1/4 HP industrial motor
- Versatile swivel head
- OSHA-compliant safety guards
- 3 variable speed settings
- Adjustable height post
- Steel fan blades
- 1-year limited warranty

Key Specs

Model Number	MHD-30P	Variable Speed	Yes
Brand	Master Industrial	Volts	120
Warranty	1-year limited warranty	Amps	1.7
Net Weight (lb.)	57	Product Dimensions (L x W x H) (in.)	41 x 8 x 35
Air Flow (CFM)	7550 / 6800 / 5800		
Motor Size (HP)	1/4		

