

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Material number : 000000000001038047

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : Compliance Services - 877-428-9937

Emergency telephone numbers

For SDS Information : Compliance Services - 877-428-9937

For a Medical Emergency : 877-541-2016 Toll Free - All Calls Recorded

For a Transportation Emergency : CHEMTREC: 800-424-9300 - All Calls Recorded.
In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : POLISHES

Note: This product is labeled as a consumer product in accordance with the United States Consumer Product Safety Commission regulations. The warnings presented below in this Safety Data Sheet (SDS) comply with the 2012 OSHA Hazard Communication Standard (GHS - Globally Harmonized System of Classification and Labeling). The requirements for the labeling and warnings of consumer products may differ from those required for GHS based hazard communication.

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	Aerosol containing a liquefied gas
Colour	white
Odour	like fruit

GHS Classification

Gases under pressure : Liquefied gas

GHS label elements

Hazard pictograms :



Gas cylinder

Signal word : Warning

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

Hazard statements : H280 Contains gas under pressure; may explode if heated.

Precautionary statements : **Storage:**
P410 + P403 Protect from sunlight. Store in a well-ventilated place.
P412 Do not expose to temperatures exceeding 50 °C/ 122 °F.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
White mineral oil (petroleum)	8042-47-5	>= 10 - < 30
propane	74-98-6	>= 1 - < 5

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Do not leave the victim unattended.

If inhaled : If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.

In case of skin contact : Wash off immediately with plenty of water for at least 15 minutes.
Take off contaminated clothing and shoes immediately.
Get medical attention if irritation develops and persists.
Wash contaminated clothing before re-use.

In case of eye contact : If in eyes, rinse with water for 15 minutes.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.

If swallowed : Keep respiratory tract clear.
DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.

Most important symptoms and effects, both acute and delayed : Effects may be delayed, symptoms may include minor eye or skin irritation.
Overexposure may cause mild eye or skin irritation.

Notes to physician : Treat symptomatically. Symptoms may be delayed.

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
Unsuitable extinguishing media	: High volume water jet
Specific hazards during firefighting	: Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	: Carbon dioxide (CO ₂) Carbon monoxide Smoke
Specific extinguishing methods	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	: Standard procedure for chemical fires. Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations. For safety reasons in case of fire, cans should be stored separately in closed containments. Use a water spray to cool fully closed containers.
Special protective equipment for firefighters	: Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	: Use personal protective equipment. Ensure adequate ventilation. Remove all sources of ignition. Beware of vapours accumulating to form explosive concentrations. Vapours can accumulate in low areas.
Environmental precautions	: Prevent further leakage or spillage if safe to do so. Prevent product from entering drains. If the product contaminates rivers and lakes or drains, inform respective authorities.
Methods and materials for containment and cleaning up	: Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Sweep up or vacuum up spillage and collect in suitable container for disposal.

SECTION 7. HANDLING AND STORAGE

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

- Advice on safe handling : For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Dispose of rinse water in accordance with local and national regulations.
Do not breathe vapours or spray mist.
Always replace cap after use.
Avoid exposure - obtain special instructions before use.
- Conditions for safe storage : BEWARE: Aerosol is pressurized. Keep away from direct sun exposure and temperatures over 50 °C. Do not open by force or throw into fire even after use. Do not spray on flames or red-hot objects.
Observe label precautions.
Keep in a cool, well-ventilated place.
Electrical installations / working materials must comply with the technological safety standards.
Keep in a dry, cool and well-ventilated place.
- Materials to avoid : Oxidizing agents
- Storage temperature : 5 - 40 °C

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Components	CAS-No.	Value type (Form of exposure)	Control parameters / Permissible concentration	Basis
White mineral oil (petroleum)	8042-47-5	TWA (Mist)	5 mg/m ³	OSHA Z-1
		TWA (Inhalable fraction)	5 mg/m ³	ACGIH
		TWA (Mist)	5 mg/m ³	OSHA P0
		TWA (Mist)	5 mg/m ³	NIOSH REL
		ST (Mist)	10 mg/m ³	NIOSH REL
		PEL (particulate)	5 mg/m ³	CAL PEL
propane	74-98-6	TWA	1,000 ppm 1,800 mg/m ³	NIOSH REL
		TWA	1,000 ppm 1,800 mg/m ³	OSHA Z-1
		TWA	1,000 ppm 1,800 mg/m ³	OSHA P0
		PEL	1,000 ppm 1,800 mg/m ³	CAL PEL

Engineering measures : effective ventilation in all processing areas

Personal protective equipment

Respiratory protection : Use respiratory protection unless adequate local exhaust

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Hand protection

Remarks

: The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection

: Ensure that eyewash stations and safety showers are close to the workstation location.
Tightly fitting safety goggles

Skin and body protection

: Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Hygiene measures

: Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

: Aerosol containing a liquefied gas

Colour

: white

Odour

: like fruit

Odour Threshold

: No data available

pH

: Not applicable

Melting point/freezing point

: No data available

Boiling point

: No data available

Flash point

:
Not applicable

Evaporation rate

: No data available

Flammability (solid, gas,
liquid)

: The product is not flammable.

Upper explosion limit

: No data available

Lower explosion limit

: No data available

Vapour pressure

: No data available

Relative vapour density

: No data available

Density

: No data available

Solubility(ies)

Water solubility

: No data available

Solubility in other solvents

: not determined

Partition coefficient: n-
octanol/water

: No data available

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

Auto-ignition temperature : not determined
Thermal decomposition : No data available
Heat of combustion : 7.54 kJ/g

SECTION 10. STABILITY AND REACTIVITY

Reactivity : Stable
Chemical stability : Stable under normal conditions.
Possibility of hazardous reactions : Vapours may form explosive mixture with air.
No decomposition if stored and applied as directed.
Conditions to avoid : Heat, flames and sparks.
Exposure to sunlight.
Incompatible materials : Oxidizing agents
Hazardous decomposition products : Carbon oxides

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

Aggravated Medical Condition : None known.
Symptoms of Overexposure : Effects may be delayed, symptoms may include minor eye or skin irritation.
Overexposure may cause mild eye or skin irritation.
Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
OSHA No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.
NTP No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

Acute toxicity

No data available

Skin corrosion/irritation

No data available

Serious eye damage/eye irritation

No data available

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n- : Remarks: No data available

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

octanol/water

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation 40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances

Remarks This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information : No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues : Do not dispose of waste into sewer.
Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with local regulations.

Contaminated packaging : Empty remaining contents.
Dispose of as unused product.
Do not re-use empty containers.
Do not burn, or use a cutting torch on, the empty drum.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: IMDG (Vessel):
UN1950, AEROSOLS, 2.2, - Limited quantity

Transportation Regulation: IATA (Cargo Air):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: IATA (Passenger Air):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

Transportation Regulation: TDG (Canada):
UN1950, AEROSOLS, NON-FLAMMABLE, 2.2, - Limited quantity

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Gases under pressure

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

DSL This product contains one or more components that are listed on the Canadian NDSL. All other components are on the Canadian DSL.

TSCA On TSCA Inventory

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

SECTION 16. OTHER INFORMATION

Further information

NFPA:

HEALTH	1
FLAMMABILITY	1
INSTABILITY	0
SPECIAL HAZARD.	SA

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	1
FLAMMABILITY	0
PHYSICAL HAZARD	2

0 = not significant, 1 = Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms



Gas cylinder

Signal word

: **Warning:**

Hazard statements

: Contains gas under pressure; may explode if heated.

Precautionary statements

:

Storage: Protect from sunlight. Store in a well-ventilated place. Do not expose to temperatures exceeding 50 °C/ 122 °F.

SAFETY DATA SHEET

MISTY ASPIRE STAINLESS STEEL CLEANER & POLISH 20N16 12CT

Version 1.5

Revision Date 10/01/2023

Print Date 10/27/2026

Version:	1.5
Revision Date:	10/01/2023
Print Date:	10/27/2026

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.