



TEGERA® CHEMFORCE 7363

Learn more

3 STRONG PROTECTIONS IN ONE GLOVE

Nitrile glove 0,3* mm/11,8 mil with chemical, cut and heat protection with dipping for non-slip finish. Suitable for work where chemical protection is needed and where there is a risk of cuts and heat damage. Comfortable lining and enhanced dexterity. With Oeko-Tex certificate.

CHARACTERISTICS

- High level of protection
- Good fingertip sensitivity
- Durable
- Excellent grip
- Excellent grip in oily environments
- Good fit
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Phthalate-free
- Latex-free
- Oil and grease resistant
- Waterproof

CRF®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Heat injuries, Corrosive injuries, Cut injuries, Contact with chemicals, Contact with moisture, Contact with damp, Contact with oil, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Chemical risk environments, Corrosive environments, Cut risk environments, Slippery environments, Wet environments, Oily and greasy environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Building and construction, Chemical technology work, Chemical work, Construction, Glass industry work, Hot work, Machine operating, Metalwork, Paper industry work, Petro-chemical work, Wood industry work

PRIMARY INDUSTRIES OF USE

Metal manufacturing and fabrication, Transport equipment manufacturing, Chemical and petrochemical industry, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Mining and quarrying, Pulp and paper, Public safety, security and defence

TYPE OF WORK

Medium weight

CHEMICAL RESISTANCE

According to EN16523-1:2015. For details, please contact Ejendals.

SPECIFICATION

TYPE Chemical protection gloves, Cut resistant gloves, Heat protection gloves
CATEGORY Cat. III
COLLECTION Chemforce
THICKNESS 0,3* mm (*chem-layer)
LINING Fully lined
KNITTING GAUGE (GG) 18
LINING MATERIAL CRF® Technology, Glass fibre thread, HPPE, Nylon, Polyester, Spandex
LENGTH 340 mm
DEXTERITY 5
GRIP DESIGN Sandy finish
COLOUR Green
PAIRS PER: BUNDLE/CARTON 12/60
DIPPING Fully dipped
DIPPING MATERIAL Nitrile
CUFF STYLE Extended safety cuff
CUT RESISTANCE (EN ISO 13997) Cut resistance level C

COMPLIANCE

CE 2777

EAC

TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018
4X32C

EN 407:2020 (No flame protection)
X1XXXX

EN ISO 374-1:2016+A1:2018 Type A
AJKMNOPT

EN ISO 374-5:2016 Virus

NOT FOR FATTY FOOD

ANSI A3 CUT

ANSI 5 ABR

FEATURES

Chemical protection

Cut protection

Waterproof

TEST ACCORDING TO EN ISO 374-1:2016

Tested chemical	A	J	K	M	N	O	P	T
Permeation level	2	4	6	2	3	3	6	6
Degradation %	8,6	12,4	-2,3	14,6	8,2	1,4	3,8	12,1

SIZE		ARTICLE NUMBER	EAN
7	S	7363-7	7340118326900
8	M	7363-8	7340118326399
9	L	7363-9	7340118326511
10	XL	7363-10	7340118326634
11	XXL	7363-11	7340118326757

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.