ABB BALDOR RELIANCE

Customer information packet

VXM18342T-5

3HP, 1760RPM, 3PH, 60HZ, 182TC, 3632M, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 12:31:31 PM

Specifications

Enclosure	XPFC
Frame	182TC
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	575.0 V @ 60 HZ
Agency Approvals	UL
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	No Mounting
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	3.300 A @ 575.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	3.3 a
Insulation Class	F
Inverter Code	Inverter Duty

Part Detail

Revision	-
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	36WGS582
Layout	36LYQ330
Eff. date	03-11-2021
CD Diagram	CD0006
Poles	04
Leads	3#16
Proprietary	False
Created date	03-02-2021

IP Rating	NONE
KVA Code	L
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	2700 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3632M
Mounting Arrangement	F1
Number of Poles	4
Overall Length	18.86 IN
Power Factor	73
Product Family	General Purpose
Pulley Face Code	C-Face
Rodent Screen	None
Service Factor	1.00
Shaft Diameter	1.125 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1760 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP0887XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	36-0000-0473			**INV.TYPE**	PWM						
CAT.NO.	VXM18342T-5			**C HP FR**	60	**C HP TO**	90				
HP	3			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	575			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	3.3		**MAG CUR**	1.9							
RPM	1760		**MX RPM**	2700							
HZ	60	**PH**	3	**CL**	F	**NOM.EFF.**	89.5				
SER.F.	1.00	**DES**	B	**SL HZ**	1.6	**WK2**	0.3				
FRAME	182TC	**RATING**	40C AMB-CONT								
	NEMA MG-1 PART 5, IP54										
	1.15 SF ON SINE WAVE										

AC Induction Motor Performance Data
Record # 68835
Typical performance - not guaranteed values

Winding: 36WGS582-R020	**Type:** 3632M	**Enclosure:** TEFC

Nameplate Data				**575 V, 60 Hz: Single Voltage Motor**	
Rated Output (KW)			2.2	**Full Load Torque**	8.8 LB-FT
Volts			575	**Start Configuration**	direct on line
Full Load Amps			3.3	**Breakdown Torque**	36.5 LB-FT
R.P.M.			1760	**Pull-up Torque**	19.2 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	22.4 LB-FT
NEMA Design Code	B	**KVA Code**	L	**Starting Current**	26.8 A
Service Factor (S.F.)			1	**No-load Current**	1.95 A
NEMA Nom. Eff.	89.5	**Power Factor**	73	**Line-line Res. @ 25ºC**	5.97 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	
				Locked-rotor Power Factor	42.5
				Rotor inertia	0.298 LB-FT2

Load Characteristics 575 V, 60 Hz, 2.2 KW

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	33	53	65	73	78	81
Efficiency	81.2	87.9	90.1	90.4	90.3	89.8
Speed	1795	1788	1779	1771	1762	1752
Line amperes	2.09	2.43	2.85	3.36	3.94	4.52


ABB Motors and Mechanical Inc.


WINDING # 36WGS582

2.2 KW 3 PH 60 HZ 1760 RPM 575 V 3632M

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=36.5 PU=19.2 LR=22.4 LRA=26.8





36LYQ330
614-623 = 17.49
624-634 = 18.86
635-646 = 20.36
5.74
2.75
.25
2.62
.25 KEY
1.75 LONG
8.84
X-PROOF NAMEPLATE
BALDOR
PT. NO. 35CB3500
Ø8.500
8.497
1.1250
1.1245
Ø7.86
7.55
45°
45°
LEAD HOLE
.75 N.P.T.
5.96
4 HOLES
.50-13 TAP
Ø7.25 B.C.
.0015 MAX
CLEARANCE
(.09)
.08 MIN.
(.41)
.38 MIN.
.006
.004
1.19
(1.12)
1.06 MIN.
DRIVE END DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CONVERT AUTOCAD DRW TO SWD DRW
REV: A
VERSION: 01
REVISED: 01:20:40 02/15/2023
TDR: 000001203217
MODEL NO. 36LYQ330
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
VERT 182-4TC XPFC 36M CL-I GP-D CL-II GP-F&G, INVERTER DUTY
36LYQ330


CD0006

TYPICAL WYE–CONNECTED MOTOR





TYPICAL DELTA–CONNECTED MOTOR



NOTES:

1. THREE LEAD MOTOR MAY BE EITHER WYE CONNECTED OR DELTA CONNECTED.
2. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
3. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
4. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY VARY.
5. LEAD COLORS ARE OPTIONAL. LEADS MUST BE NUMBERED AS SHOWN.

CD0006

REV. DESC: ADD CLASS CONN00000007			BALDOR - RELIANCE®
REV. LTR: E	VERSION: 01	TDR: 000001099922	
FILE: \AAA\00005\141	REVISED: 10:24:49 02/19/2019	BY: ENBRIR0	3PH, SV, 3 LEADS, WYE OR DELTA CONNECTED
MTL: –			SH 1 of 1