marathon®

General Purpose Motors

Model No: LM16762
Catalog No: LM16762

General Purpose Motor, 15 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 380-415 V, 1800 RPM, 254TC Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: LM16762, Catalog No: LM16762 General Purpose Motor, 15 & 15 HP, 3 Ph, 60 & 50 Hz, 230/460 & 380-415 V, 1800 RPM, 254TC Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**15 & 15 Hp**
Output KW	**11.2 & 11.2 kW**	Voltage	**230/460 & 380-415 V**
Speed	**1775 & 1460 r/min**	Synchronous RPM	**1800 & 1500 r/min**
Service Factor	**1.25 & 1.15**	Frame	**254TC**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**92.4 & 91 %**	Ambient Temperature	**40 °C**
Frequency	**60 & 50 Hz**	Current	**37.5/18.8 & 22.5-21.5 A**
Power Factor	**81**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6208**	UL	**Recognized**
CSA	**Y**	CE	**Y**
IP Code	**43**	Number of Speeds	**1**


Technical Specifications

Electrical Type	**Squirrel Cage Induction Run**	Starting Method	**Across The Line**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.649 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Aluminum**
Shaft Type	**T**	Overall Length	**24.0 in**
Frame Length	**12.0 in**	Shaft Diameter	**1 5/8 in**
Shaft Extension	**4 in**	Assembly/Box Mounting	**F1/F2 Capable**

Drawings

Connection Drawing	**EE7308K**	Outline Drawing	**SS321103LN-1200**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 16/10/2026



NOTES:

1. CONDUIT BOX CAN BE ROTATED IN 90° STEPS
2. NAMEPLATES TO BE READ FROM CONDUIT BOX SIDE OF MOTOR

DASH	FRAME	C	B	BS	2F	2FF	AG	N
1200	254TC	24.28	12.13	1.73	8.25	---------	20.53	4
1375	254/6TC	26.03	13.88	1.73	8.25	10.00	22.28	8

DRAWING REVISION	REVISION BY	REV DATE/© DATE
C	SB	05/27/2026
REQUEST NUMBER	APPROVED BY	DATE
CR-0026396	RMS	05/27/2026

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES (EXCEPT AS NOTED):

DEC.	INCH	mm	ANGLE
.X	±0.1	[±3]	±7' 30"
.XX	±0.03	[±0.8]	
.XXX	±0.005	[±0.13]	
.XXXX	±0.0005	[±0.013]	

REMOVE BURRS & BREAK SHARP
EDGES: .003/.015 [.08/.38] X 45°
CORNER FILLETS: R.02 [.5]
MACHINED SURFACES: 200 / 5.1 / INCH / mm
mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY

DRAWN BY	
CTO	
DATE	
05-11-2004	
APPROVED BY	
TB	
DATE	
05-11-2004	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
OUTLINE
250TC FR - ALUM FR - TEFC

MATERIAL | PROCESS/FINISH

SIZE B | DRAWING NUMBER SS321103LN | SHEET 1 OF 1