



<b>EAN:</b>	4013288019257	<b>Size:</b>	42x16x3 mm
<b>Part number:</b>	05024001001	<b>Weight:</b>	2 g
<b>Article number:</b>	967 TORX®	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82041100

- L-keys for recessed TORX® screws
- BlackLaser for high corrosion protection and long service life
- Laser-engraved and thereby wear-resistant size markings

High quality L-keys for recessed TORX® screws. The BlackLaser surface treatment provides outstanding surface protection, even against corrosion, and a long service life. The tools are quickly to hand thanks to the laser-engraved and thereby wear-resistant size markings on the L-keys.

**Web link**

<https://www.wera.de/en/05024001001>

Wera - 967 TORX®

05024001001 - 4013288019257

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

**Size identification**

**Surface protection**



The size of each L-keys has been engraved by a laser. In addition Take it easy L-keys have a colour coding according to sizes - for simple and rapid accessing of the required tool. Making it easy to find the right tool.

L-keys with BlackLaser surface treatment for outstanding surface protection and long service life. High corrosion protection.

**Further versions in this product family:**



mm



mm



inch



inch

		mm	mm	inch	inch
<b>05024001001</b>	<b>TX 6</b>	<b>42</b>	<b>16</b>	<b>1 5/8"</b>	<b>5/8"</b>
05024002001	TX 7	48	16	1 7/8"	5/8"
05024003001	TX 8	48	16	1 7/8"	5/8"
05024004001	TX 9	48	16	1 7/8"	5/8"
05024005001	TX 10	51	17	2"	21/32"
05024008001	TX 15	54	18	2 1/8"	23/32"
05024010001	TX 20	57	19	2 1/4"	3/4"
05024012001	TX 25	60	20	2 3/8"	25/32"
05024013001	TX 27	64	21	2 1/2"	27/32"
05024015001	TX 30	70	24	2 3/4"	1"
05024020001	TX 40	76	26	3"	1 1/32"

**Web link**

<https://www.wera.de/en/05024001001>

Wera - 967 TORX®

05024001001 - 4013288019257

Wera Werkzeuge GmbH

Korzter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)