



SAFETY DATA SHEET

1. Identification

Product identifier F9J88Series
Other means of identification Not available.
Recommended use Inkjet printing
Recommended restrictions None known.
Company identification HP Inc.
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
Telephone 650-857-5020

HP Inc. health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-760-710-0048
HP Inc. Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards Not classified.
Health hazards Not classified.
Environmental hazards Not classified.
OSHA defined hazards Not classified.

Label elements

Hazard symbol None.
Signal word None.
Hazard statement Not available.
Precautionary statement
Prevention Not available.
Response Not available.
Storage Not available.
Disposal Not available.

Hazard(s) not otherwise classified (HNOC) Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions. Complete toxicity data are not available for this specific formulation.

Supplemental information Contains 1-Aza-5-ethyl-3,5-dioxabicyclo(3,3,0)octane. May produce an allergic reaction. This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	50-60
Glycerol		56-81-5	<40
2-pyrrolidone		616-45-5	<7.5
ethoxylated 2,4,7,9-tetramethyl-5-decyn-4,7-diol		9014-85-1	<2.5

Composition comments This ink supply contains an aqueous ink formulation.
This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

4. First-aid measures

Inhalation Move to fresh air. If symptoms persist, get medical attention.
Skin contact Wash affected areas thoroughly with mild soap and water. If irritation persists get medical attention.
Eye contact Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
Ingestion If ingestion of a large amount does occur, seek medical attention.
Most important symptoms/effects, acute and delayed Not available.

5. Fire-fighting measures

Suitable extinguishing media CO2, water, dry chemical, or foam
Unsuitable extinguishing media None known.
Specific hazards arising from the chemical Not applicable.
Special protective equipment and precautions for firefighters Not available.
Specific methods Wear self contained breathing apparatus for fire fighting if necessary.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Wear appropriate personal protective equipment.
Methods and materials for containment and cleaning up Not available.
Environmental precautions Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling Avoid contact with skin, eyes and clothing.
Conditions for safe storage, including any incompatibilities Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Glycerol (CAS 56-81-5)	PEL	5 mg/m3 15 mg/m3	Respirable fraction. Total dust.

Biological limit values No biological exposure limits noted for the ingredient(s).
Exposure guidelines Exposure limits have not been established for this product.
Appropriate engineering controls Use in a well ventilated area.
Individual protection measures, such as personal protective equipment
Eye/face protection Not available.
Skin protection
Hand protection Not available.
Other Not available.
Respiratory protection Not available.
Thermal hazards Not available.

9. Physical and chemical properties

Appearance

Physical state Liquid.

Color Clear.

Odor Not available.

Odor threshold Not available.

pH 8.8 - 9.1

Melting point/freezing point Not available.

Initial boiling point and boiling range Not available.

Flash point > 200.0 °F (> 93.3 °C) Pensky-Martens Closed Cup

Evaporation rate Not available.

Flammability (solid, gas) Not available.

Upper/lower flammability or explosive limits

Flammability limit - lower (%) Not available.

Flammability limit - upper (%) Not available.

Explosive limit - lower (%) Not available.

Explosive limit - upper (%) Not available.

Vapor pressure Not available.

Solubility(ies)

Solubility (water) Not available.

Partition coefficient (n-octanol/water) Not available.

Auto-ignition temperature Not available.

Decomposition temperature Not available.

Viscosity 3.2 - 3.3 cP

Other information

Specific gravity 1 - 1.1

VOC (Weight %) < 445 g/L

10. Stability and reactivity

Reactivity Not available.

Chemical stability Stable under recommended storage conditions.

Possibility of hazardous reactions Will not occur.

Conditions to avoid Not available.

Incompatible materials Not available.

Hazardous decomposition products Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.

11. Toxicological information

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitization

Respiratory sensitization Based on available data, the classification criteria are not met.

Skin sensitization Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure Based on available data, the classification criteria are not met.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

Further information Complete toxicity data are not available for this specific formulation

Components	Species	Test Results
------------	---------	--------------

2-pyrrolidone (CAS 616-45-5)

Acute

Oral

LD50	Guinea pig	6500 mg/kg
	Rat	6500 mg/kg

12. Ecological information

Ecotoxicity

Components	Species	Test Results
------------	---------	--------------

2-pyrrolidone (CAS 616-45-5)

Aquatic

Crustacea	EC50	Water flea (Daphnia pulex)	13.21 mg/l, 48 hours
-----------	------	----------------------------	----------------------

Glycerol (CAS 56-81-5)

Aquatic

Fish	LC50	Rainbow trout,donaldson trout (Oncorhynchus mykiss)	51000 - 57000 mg/l, 96 hours
------	------	---	------------------------------

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Partition coefficient n-octanol / water (log Kow)

2-pyrrolidone	-0.85
Glycerol	-1.76

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

ADR

Not regulated as dangerous goods.

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information**US federal regulations** US TSCA 12(b): Does not contain listed chemicals.
US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.**TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)**

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**Hazard categories** Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No**SARA 302 Extremely hazardous substance**

Not listed.

SARA 311/312 No
Hazardous chemical**Other federal regulations****Safe Drinking Water Act (SDWA)** Not regulated.**US state regulations****US. Massachusetts RTK - Substance List**2-pyrrolidone (CAS 616-45-5)
Glycerol (CAS 56-81-5)**US. New Jersey Worker and Community Right-to-Know Act**

Glycerol (CAS 56-81-5)

US. Pennsylvania Worker and Community Right-to-Know Law2-pyrrolidone (CAS 616-45-5)
Glycerol (CAS 56-81-5)**US. Rhode Island RTK**

Not regulated.

US. California Proposition 65

Not Listed.

Other information VOC content (less water, less exempt compounds) = < 1127 g/L (U.S. requirement, not for emissions)
VOC data based on formulation (Organic compounds minus solids)**Regulatory information** All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision**Issue date** 10-Jun-2016
Revision date 11-Jun-2016
Version # 02

Disclaimer

This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Manufacturer information

HP Inc.
1501 Page Mill Road
Palo Alto, CA 94304-1112 US
Direct 1-650-857-5020

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds