
SCHAEFER®

36CFO-HE

36CFO-HE



Product Description

Schaefer OSHA compliant high-efficiency circulation fans meet all OSHA safety regulation while delivering maximum airflow. These 2-speed fans have the versatility to be mounted on a ceiling, wall, pedestal or cart, which makes them the ideal cooling solution for any commercial, industrial or agricultural facility.

Features

Direct drive engineering for low noise levels and long lasting performance

Powder coated steel guards for corrosion resistant and durability

10 volt signal controller integrates into building management system for single point of control (Control not included)

Thermally protected, heavy-duty, maintenance free, 2-speed motors for long life

Two year warranty

Made in the USA

Specifications

Blade Color	Metallic
Brand	Schaefer
Cfm/watt (@0.10")	TBD
Drive	Direct
Phase	1
Speeds	Variable w Control
Vfd Compatible	No
Cord	Not included
Diameter (inches)	36
Frequency (hz)	60
Guard Color	White
Nameplate Amps	5.6/3.5

Number Of Wings	3
Cfm/watt (@0.05")	TBD
Power (hp)	1/2
Product Dimensions (l X W X H Inches)	40 3/8 x 40 3/8 x 14.5
Product Net Weight (lbs)	59
Switch	On product
Voltage	115/230
Maximum Rpm	1800
Blade Material	Aluminum
Cfm (high)	9000
Cfm Calculation Standard	ANSI/AMCA Standard 230-99
Product Color	White

Product Shipping Dimensions (in)	41 X 41 X 15
Speed Control Compatible?	No
Able To Ship Small Parcel	No
Cfm Range (free Air)	5001 - 10000
Fixed Or Portable	Fixed
Guard Material	Powder Coated Steel
Oscillating	No
Thermal Protection	Yes
Country Of Origin	US
Guard Spacing (inches)	1/2 OSHA