SAFETY DATA SHEET
ZEP PROVISIONS SOLID WAREWASH DETERGENT - METAL SAFE 8LB 4CT

Version 2.5 Revision Date 10/01/2023 Print Date 10/27/2026

SECTION 1. PRODUCT AND COMPANY IDENTIFICATION

Material name : ZEP PROVISIONS SOLID WAREWASH DETERGENT - METAL SAFE 8LB 4CT

Material number : 000000000000269401

Manufacturer or supplier's details

Company : Zep Inc.

Address : 350 Joe Frank Harris Parkway, SE
Emerson, GA 30137

Telephone : Compliance Services - 877-428-9937

Emergency telephone numbers		
For SDS Information	:	Compliance Services - 877-428-9937
For a Medical Emergency	:	877-541-2016 Toll Free - All Calls Recorded
For a Transportation Emergency	:	CHEMTREC: 800-424-9300 - All Calls Recorded. In the District of Columbia 202-483-7616

Recommended use of the chemical and restrictions on use

Recommended use : FOOD RETAIL

SECTION 2. HAZARDS IDENTIFICATION

Emergency Overview

Appearance	solid
Colour	white
Odour	characteristic

GHS Classification

Skin corrosion : Category 1
Serious eye damage : Category 1
Specific target organ toxicity - single exposure : Category 3 (Respiratory system)

GHS label elements

Hazard pictograms :



Corrosion

Exclamation mark

Signal word : Danger

Hazard statements : H314 Causes severe skin burns and eye damage.
H335 May cause respiratory irritation.

Precautionary statements : **Prevention:**
P260 Do not breathe dust or mist.
P264 Wash skin thoroughly after handling.
P271 Use only outdoors or in a well-ventilated area.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response:
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304 + P340 + P310 IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER/doctor.
P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.
P363 Wash contaminated clothing before reuse.
Storage:
P403 + P233 Store in a well-ventilated place. Keep container tightly closed.
Disposal:
P501 Dispose of contents/container in accordance with local regulation.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Substance / Mixture : Mixture

Hazardous components

Chemical name	CAS-No.	Concentration [%]
Sodium metasilicate (disodium salt)	6834-92-0	>= 30 - < 60

The exact percentages of disclosed substances are withheld as trade secrets.

SECTION 4. FIRST AID MEASURES

General advice : Move out of dangerous area.
Get medical attention immediately.
Show this safety data sheet to the doctor in attendance.

If inhaled : If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.

In case of skin contact : Immediate medical treatment is necessary as untreated wounds from corrosion of the skin heal slowly and with difficulty.

		Wash off immediately with plenty of water for at least 15 minutes. Remove contaminated clothing and shoes. Wash contaminated clothing before reuse. If skin irritation persists, call a physician.
In case of eye contact	:	Remove contact lenses. Small amounts splashed into eyes can cause irreversible tissue damage and blindness. Protect unharmed eye. Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists, consult a specialist. Keep eye wide open while rinsing.
If swallowed	:	Keep respiratory tract clear. Never give anything by mouth to an unconscious person. Take victim immediately to hospital. DO NOT induce vomiting unless directed to do so by a physician or poison control center.
Most important symptoms and effects, both acute and delayed	:	Effects are immediate and delayed. Symptoms may include blistering, irritation, burns, and pain. Effects are dependent on exposure (dose, concentration, contact time). Causes severe skin burns and eye damage. Review section 2 of SDS to see all potential hazards.
Notes to physician	:	Treat symptomatically. Symptoms may be delayed.

SECTION 5. FIREFIGHTING MEASURES

Suitable extinguishing media	:	Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide.
Unsuitable extinguishing media	:	High volume water jet
Specific hazards during firefighting	:	Do not allow run-off from fire fighting to enter drains or water courses.
Hazardous combustion products	:	No hazardous combustion products are known
Specific extinguishing methods	:	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Further information	:	Standard procedure for chemical fires. Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Collect contaminated fire extinguishing water separately. This must not be discharged into drains.

Special protective equipment for firefighters	:	Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures	:	Use personal protective equipment. Avoid dust formation. Ensure adequate ventilation. Evacuate personnel to safe areas.
Environmental precautions	:	Prevent product from entering drains. If the product contaminates rivers and lakes or drains, inform respective authorities.
Methods and materials for containment and cleaning up	:	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Sweep up or vacuum up spillage and collect in suitable container for disposal. Avoid dispersal of dust in the air (i.e., clearing dust surfaces with compressed air).

SECTION 7. HANDLING AND STORAGE

Advice on safe handling	:	Avoid contact with skin and eyes. Do not get on skin or clothing. Do not breathe vapours/dust.
Conditions for safe storage	:	Keep container tightly closed in a dry and well-ventilated place.
Materials to avoid	:	Do not store near acids. Strong oxidizing agents

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

Engineering measures	:	effective ventilation in all processing areas

Personal protective equipment

Respiratory protection	:	In the case of dust or aerosol formation use respirator with an approved filter.

Hand protection

Material	:	Protective gloves

Remarks	:	The suitability for a specific workplace should be discussed with the producers of the protective gloves.
Eye protection	:	Safety glasses Access to clean water to rinse eyes must be available, options include: eye wash stations or showers, or eye wash bottles with pure water.
Skin and body protection	:	Choose body protection according to the amount and concentration of the dangerous substance at the work place. Impervious clothing
Hygiene measures	:	When using do not smoke. When using do not eat or drink. Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance	:	solid
Colour	:	white
Odour	:	characteristic
Odour Threshold	:	No data available
pH	:	> 11.5, (as aqueous solution)
Melting point/freezing point	:	No data available
Boiling point	:	No data available
Flash point	:	No data available
Evaporation rate	:	No data available
Upper explosion limit	:	No data available
Lower explosion limit	:	No data available
Vapour pressure	:	No data available
Density	:	> 1.5 g/cm3
Solubility(ies)		
Water solubility	:	completely soluble
Solubility in other solvents	:	soluble Solvent: Acetone
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	not determined
Thermal decomposition	:	No data available
Viscosity		

Viscosity, kinematic	:	No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity	:	Stable
Chemical stability	:	Stable under normal conditions.
Possibility of hazardous reactions	:	Stable under recommended storage conditions. No hazards to be specially mentioned.
Conditions to avoid	:	No data available
Incompatible materials	:	Strong oxidizing agents Strong bases Strong acids
Hazardous decomposition products	:	Carbon oxides Sodium oxides

SECTION 11. TOXICOLOGICAL INFORMATION

Potential Health Effects

Aggravated Medical Condition	:	None known.
Symptoms of Overexposure	:	Effects are immediate and delayed. Symptoms may include blistering, irritation, burns, and pain. Effects are dependent on exposure (dose, concentration, contact time). Causes severe skin burns and eye damage. Review section 2 of SDS to see all potential hazards. Treat symptomatically. Symptoms may be delayed.

Carcinogenicity:

IARC	No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
ACGIH	No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.
OSHA	No component of this product present at levels greater than or equal to 0.1% is on OSHA's list of regulated carcinogens.
NTP	No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

Acute toxicity

Product:

Acute oral toxicity : Acute toxicity estimate : 2,453 mg/kg
Method: Calculation method

Components:

Sodium metasilicate (disodium salt):
Acute oral toxicity : LD50 Rat: 1,153 mg/kg

Skin corrosion/irritation

Product:

Remarks: Extremely corrosive and destructive to tissue.

Serious eye damage/eye irritation

Product:

Remarks: May cause irreversible eye damage.

Respiratory or skin sensitisation

No data available

Germ cell mutagenicity

No data available

Carcinogenicity

No data available

Reproductive toxicity

No data available

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

Further information

Product:

Remarks: No data available

SECTION 12. ECOLOGICAL INFORMATION

Ecotoxicity

No data available

Persistence and degradability

No data available

Bioaccumulative potential

Product:

Partition coefficient: n-octanol/water	:	Remarks: No data available

Mobility in soil

No data available

Other adverse effects

No data available

Product:

Regulation	40 CFR Protection of Environment; Part 82 Protection of Stratospheric Ozone - CAA Section 602 Class I Substances
Remarks	This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

Additional ecological information	:	No data available

SECTION 13. DISPOSAL CONSIDERATIONS

Disposal methods

Waste from residues	:	The product should not be allowed to enter drains, water courses or the soil. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of in accordance with local regulations.
Contaminated packaging	:	Dispose of as unused product. Do not re-use empty containers. Empty remaining contents.

SECTION 14. TRANSPORT INFORMATION

Transportation Regulation: 49 CFR (USA):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IMDG (Vessel):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Cargo Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: IATA (Passenger Air):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

Transportation Regulation: TDG (Canada):
NOT REGULATED AS DANGEROUS GOODS OR HAZARDOUS MATERIAL

The product as delivered to the customer conforms to packaging requirements for shipment by road under US Department of Transportation (DOT) regulations. Additional transportation classifications noted above are for reference only, and not a certification or warranty of the suitability of the packaging for shipment under these alternative transport regulations.

SECTION 15. REGULATORY INFORMATION

TSCA list : No substances are subject to a Significant New Use Rule.

No substances are subject to TSCA 12(b) export notification requirements.

EPCRA - Emergency Planning and Community Right-to-Know Act

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA 304 Extremely Hazardous Substances Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Skin corrosion or irritation
Serious eye damage or eye irritation
Specific target organ toxicity (single or repeated exposure)

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

California Prop. 65

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

The components of this product are reported in the following inventories:

TSCA	On TSCA Inventory
DSL	All components of this product are on the Canadian DSL

For information on the country notification status for other regions please contact the manufacturer's regulatory group.

Inventory Acronym and Validity Area Legend:

TSCA (USA), DSL (Canada), NDSL (Canada)

SECTION 16. OTHER INFORMATION

Further information

NFPA:

HEALTH	2
FLAMMABILITY	0
INSTABILITY	0
SPECIAL HAZARD.	

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme

HMIS III:

HEALTH	2
FLAMMABILITY	0
PHYSICAL HAZARD	0

0 = not significant, 1 =Slight,
2 = Moderate, 3 = High
4 = Extreme, * = Chronic

OSHA - GHS Label Information:

Hazard pictograms :



Corrosion



Exclamation mark

Signal word : **Danger:**
Hazard statements : Causes severe skin burns and eye damage. May cause respiratory irritation.
Precautionary statements :

Prevention: Do not breathe dust or mist. Wash skin thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response: IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower. IF INHALED: Remove person to fresh air and keep comfortable for breathing. Immediately call a POISON CENTER/doctor. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor. Wash contaminated clothing before reuse.

Storage: Store in a well-ventilated place. Keep container tightly closed.
Disposal: Dispose of contents/container in accordance with local regulation.

Version:	2.5
Revision Date:	10/01/2023
Print Date:	10/27/2026

We believe the statements, technical information and recommendations contained herein are reliable, but they are given without warranty or guarantee of any kind. The information in this document applies to this specific material as supplied. It may not be valid for this material if it is used in combination with any other materials. Users should make their own investigations to determine the suitability and applicability of the information for their particular purposes. This SDS has been prepared by the Compliance Services organization supporting this manufacturer, supplier or distributor.