

Warm-lined premium glove, touchscreen-compatible. Waterproof and breathable.

TEGERA® DYNAMIC STRENGTH 7798

Learn more

TOP QUALITY ALL THE WAY

Experience extraordinary comfort and support on your longest workdays with our warm-lined premium glove in high-visibility color. This touchscreen-compatible gloves, made of top-quality full-grain goat skin and lined with 40g Thinsulate™, offer warmth, waterproofing, and breathability. Suitable for all-around work, this glove ensure you can use your smartphone effortlessly while keeping your hands protected. Exceptionally good fit.

CHARACTERISTICS

- Flexible
- Durable
- Perfect fit
- Excellent grip
- Extra comfortable

FUNCTIONS

- For touchscreen
- High visibility colour
- Reinforced index finger
- Reinforced fingertips
- Reinforced thumb
- Specially designed thumb
- Waterproof
- Reflector
- Specially designed details
- Elastic

Thinsulate™ INSULATION

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Blisters, Grazes, Scratches, lacerations, Contact with dirt, Drying out, Chapping, Contact with moisture, Contact with damp, Contact with cold

PRIMARY ENVIRONMENTS OF USE

Dark environments, Windy environments, Dry environments, Cold environments, Wet environments, Moist environments, Oily and greasy environments, Dirty environments, Slippery environments, Harsh environments

PRIMARY AREAS OF USE

Machine operating, Building and construction, Carpentry, Installation work, HVAC installation, Construction, Soil preparation, Concrete work, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Wood industry work, Forest work, Agricultural work, Gardening, Repair work, Paper industry work

PRIMARY INDUSTRIES OF USE

Automotive repair and maintenance, Glass, ceramics and construction materials, Metal manufacturing and fabrication, Transport equipment manufacturing, Agriculture, forestry and fishing, Accommodation and food service (HoReCa), Facility management services, Basic metals manufacturing, Machinery and equipment manufacturing, Automotive manufacturing, Transportation and logistics, Electricity and gas supply, Building and construction, Mining and quarrying, Warehousing, Pulp and paper, Public safety, security and defence, Retail and wholesale

TYPE OF WORK

Medium weight

SPECIFICATION

TYPE Cold insulation gloves, Heavy duty gloves
CATEGORY Cat. II
COLLECTION Dynamic Strength
PALM MATERIAL Full grain goatskin of top quality
BACK MATERIAL Spandex
LINING Winter-lined
LINING MATERIAL Thinsulate™ 40g, Fleece
LENGTH 240-275 mm
DEXTERITY 5
COLOUR Yellow
PAIRS PER: BUNDLE/CARTON 6/36
DISPLAY TYPE Hangtag with euro slot
FASTENING Elasticated 180°
INNER MATERIAL SPECIFICATION Polyester
MIDDLE MATERIAL SPECIFICATION Polyurethane
OUTER MATERIAL SPECIFICATION Leather, Polyurethane, Polyester

COMPLIANCE

CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 2111X

EN 511:2006 111

EN ISO 11640:2012 Dry 150 cycles 4/5 Wet 50 cycles 3/4

ANSI 3 ABR

FEATURES


For touchscreen


Warm lining


Waterproof


Windproof

SIZE		ARTICLE NUMBER	EAN
7	S	7798-7	7340118347004
8	M	7798-8	7340118347097
9	L	7798-9	7340118347189
10	XL	7798-10	7340118347271
11	XXL	7798-11	7340118347363
12	3XL	7798-12	7340118347455

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.