



Technical Data Sheet

3M™ Adhesive Transfer Tape 8056



[Product Details](#)



[Regulatory Info/SDS](#)

Product Description

0.005 in. (0.13 mm) thick adhesive transfer tape

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Test Method	Value
Color		Clear
Adhesive Type		Acrylic
Total Tape Thickness	ASTM D3652	0.13 mm (5 mil)
Liner		60# Densified Kraft Paper
Liner Thickness		0.1 mm (4 mil)
Primary Liner Color		Tan

Typical Performance Characteristics

Temperature: 22 °C (72 °F)

Backing: 2 mil Aluminum Foil

Attribute Name	Test Method	Value
180° Peel Adhesion	ASTM D3330	3.8 N/cm (35 oz/in) ¹

¹ 12 in/min (300 mm/min)

Attribute Name	Value
Short Term Temperature Resistance	65 °C (150 °F) ¹
Long Term Temperature Resistance	48 °C (120 °F) ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Performance

Attribute Name	Value
Solvent Resistance	Low
UV Resistance	Excellent

Handling/Application Information

Application Examples

The very aggressive adhesive of adhesive transfer tape 8056 is ideal for making many zero speed and flying splices. It has been used on many webs that are difficult to splice because of "hard-to-stick to" coatings on the web.

Some applications ideas include:

- Flying splices on coated papers.
- Flying splices on chemically saturated non-woven fabric.
- Zero speed splices on chemically saturated low density foam.
- Flying splices on vinyl and rubber coated fabric.

- Flying splices on polyethylene.

Application Techniques

- Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
- To obtain optimum adhesion, the bonding surfaces must be clean, dry, and well unified. Some typical surface cleaning solvents are isopropyl alcohol or heptane. Note: Be sure to follow manufacturer's safety precautions and directions for use when using solvents.
- Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 20°F (-7°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Storage and Shelf Life

18 months from date of manufacture when stored in original cartons at 70°F (21°C) and 50% R.H.

Available Sizes

Attribute Name	Width	Value
Core Size (ID)		76.2 mm (3 in)
Maximum Available Width		584 mm (23 in)
Maximum Length	1/2 in to 1 in widths	54.9 m (60 yd)
Maximum Length	1 in to maximum	165 m (180 yd)
Minimum Available Width		12.7 mm (1/2 in)
Normal Slitting Tolerance		± 0.8 mm (± 1/32 in)
Note		Subject to Minimum Order Requirements
Standard Roll Length		54.9 m (60 yd)

Recognition/Certification

MSDS: 3M has not prepared a MSDS for this product which is not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, the product should not present a health and safety hazard. However, use or processing of the product in a manner not in accordance with the directions for use may affect its performance and present potential health and safety hazards.

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

Information

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customer's application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.

Disclaimer: 3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable health and safety regulations and standards (e.g., U.S. OSHA, ANSI), as well as all product literature, user instructions, warnings, and limitations, and the user must take any action required under any recall, field action or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, or death. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert. For additional product information, visit www.3M.com.

ISO Statement

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001 standards.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/bonding. Address correspondence to: 3M Bonding Systems Division, 3M Center, Building 220-7E-01, St. Paul, MN 55144-1000. Our fax number is 651-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-809-750-3000. In Mexico, phone: 5-728-2180.

3M
Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550

©3M IPC 2000