Customer information packet

XM21362T

3HP, 1160//960RPM, 3PH, 60HZ, 213T, XPFC, F1
Class - CLI GP D; CLII GP F,G
Division - Division I

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 10:11:39 AM

Specifications

Enclosure	XPFC
Frame	213T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	CLI GP D; CLII GP F,G
Haz Area Division	Division I
Motor Letter Type	Three Phase
Output @ Frequency	3.000 HP @ 60 HZ
	2.000 HP @ 50 HZ
Phase	3
Synchronous Speed @ Frequency	1200 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	190.0 V @ 50 HZ
	230.0 V @ 60 HZ
	380.0 V @ 50 HZ
Agency Approvals	UL
	CSA EEV
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Constant Torque Speed Range	6
Current @ Voltage	4.000 A @ 380.0 V
	4.600 A @ 460.0 V
	8.000 A @ 190.0 V
	9.200 A @ 230.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	89.5 %

Part Detail

Revision	G
Type	AC
Mech. spec.	
Base	
Status	PRD/A
Elec. spec.	37WGS519
Layout	37LYN517
Eff. date	10-13-2022
CD Diagram	CD0005
Poles	06
Leads	9#14
Proprietary	False
Created date	04-04-2019

Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Haz Area Temp Code	T3C
Heater Indicator	No Heater
High Voltage Full Load Amps	4.0 a
Insulation Class	F
Inverter Code	Inverter Duty
IP Rating	NONE
KVA Code	L
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Max Speed	1800 rpm
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3738M
Mounting Arrangement	F1
Number of Poles	6
Overall Length	19.32 IN
Power Factor	68
Product Family	General Purpose
Pulley Face Code	Standard
Rodent Screen	None
RoHS Status	ROHS NON-COMPLIANT
Service Factor	1.00
Shaft Diameter	1.375 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Speed	1160 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	Normally Closed Thermostat
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP0887XPSLEV											
NO.				**CC**	010A						
S/N				**TEMP CODE**	T3C						
SPEC.	37-0000-0041			**INV.TYPE**	PWM						
CAT.NO.	XM21362T			**C HP FR**	60	**C HP TO**	90				
HP	3//2			**CT HZ FROM**	6			**CT HZ TO**	60		
VOLTS	230/460//190/380			**VT HZ FROM**	6			**VT HZ TO**	60		
AMPS	9.2/4.6//8/4			**MAG CUR**	5.2/2.6						
RPM	1160//960			**MX RPM**	1800						
HZ	60//50	**PH**	3	**CL**	F	**NOM.EFF.**	89.5				
SER.F.	1.00	**DES**	A	**SL HZ**	2	**WK2**	0.945				
FRAME	213T	**RATING**	40C AMB-CONT								
	55C AMB @ 1.0 SF										
	1.15 SF SINEWAVE				NEMA MG-1 PT 5,IP54						

AC Induction Motor Performance Data
Record # 73672
Typical performance - not guaranteed values

Winding: 37WGS519-R048	**Type:** 3738M	**Enclosure:** XPFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			3//2	**Full Load Torque**	13.4 LB-FT
Volts			230/460//190/380	**Start Configuration**	direct on line
Full Load Amps			9.2/4.6//8/4	**Breakdown Torque**	50.17 LB-FT
R.P.M.			1160//960	**Pull-up Torque**	31.8 LB-FT
Hz	60//50	**Phase**	3	**Locked-rotor Torque**	33.9 LB-FT
NEMA Design Code	A	**KVA Code**	L	**Starting Current**	34 A
Service Factor (S.F.)			1	**No-load Current**	2.56 A
NEMA Nom. Eff.	89.5	**Power Factor**	68	**Line-line Res. @ 25ºC**	2.67 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	39°C
				Locked-rotor Power Factor	22.9
				Rotor inertia	0.945 LB-FT2

Load Characteristics 460 V, 60 Hz, 3 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**
Power Factor	32	51	63	69	73	75
Efficiency	78.5	86.3	87.9	88.5	88.1	86.7
Speed	1193	1186	1178	1170	1160	1148
Line amperes	2.75	3.22	3.86	4.57	5.49	6.47


ABB Motors and Mechanical Inc.


WINDING # 37WGS519

3 HP 3 PH 60 HZ 1170 RPM 460 V 3738M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=50.17 PU=31.8 LR=33.9 LRA=34




37LYN517
(717-735) = 18.19
(736-744) = 19.32
(745-750) = 20.06
(751-756) = 20.82
5.25
3.82
3.38
.31 KEY
2.38 LONG
LISTING
NAMEPLATE
BALDOR
PT. NO. 35CB3500
X-PROOF NAMEPLATE
Ø 1.3750
1.3745
6 HOLES
Ø.43
5.50
.50
7.00
3.50
8.00
Ø9.65
8.39
2.00
REF
GREASE FITTING
(EA. END)
GREASE PLUG
(EA. END)
10.04
5.25 +.00 -.06
LEAD HOLE
.75 N.P.T.
4.25
4.25
6.80
4.75
9.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: LOAD PER BOM REV G
REV: B
VERSION: 02
REVISED: 02:09:01 10/25/2022
TDR: 000001198704
MODEL NO. 37LYN517
REF: -
BY: ENALEM0
B
BALDOR - RELIANCE®
HORZ 213-5T XPFC M CLI GP D, CLII GP F&G, INVERTER
37LYN517

CD0005





NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0005

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: E	BY: JLP	REVISED: 01/19/99 10:15	TDR: 0171435
CD0005		FILE: AAA00005140	MDL: –
		MTL: –	3PH, DV, 9 LEADS