



SAFETY DATA SHEET

1. Identification

Product identifier CN050Series
Other means of identification Not available.
Recommended use Inkjet printing
Recommended restrictions None known.
Company identification HP
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
Telephone 650-857-5020

HP health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-760-710-0048
HP Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards Not classified.
Health hazards Carcinogenicity Category 2
Environmental hazards Not classified.
OSHA defined hazards Not classified.

Label elements



Signal word Warning
Hazard statement Suspected of causing cancer.

Precautionary statement

Prevention P280 - Wear protective gloves/protective clothing/eye protection/face protection.
P201 - Obtain special instructions before use.
P202 - Do not handle until all safety precautions have been read and understood.

Response P308 + P313 - IF exposed or concerned: Get medical attention/advice.

Storage P405 - Store locked up.

Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.

Hazard(s) not otherwise classified (HNOC) None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA. Complete toxicity data are not available for this specific formulation. Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	75-85
1-(2-hydroxyethyl)-2-pyrrolidone		3445-11-2	< 10

Chemical name	Common name and synonyms	CAS number	%
2-pyrrolidone		616-45-5	< 7.5
Cyan colorant		Proprietary	< 2.5
Hydroxyethyliminodiacetic acid, disodium salt		135-37-5	< 1

Composition comments This ink supply contains an aqueous ink formulation. This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

4. First-aid measures

Inhalation Move to fresh air. If symptoms persist, get medical attention.

Skin contact Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.

Eye contact Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.

Ingestion If ingestion of a large amount does occur, seek medical attention.

Most important symptoms/effects, acute and delayed Not available.

General information Wash affected areas thoroughly with mild soap and water.

5. Fire-fighting measures

Suitable extinguishing media Dry chemical, CO₂, water spray or regular foam.

Unsuitable extinguishing media None known.

Specific hazards arising from the chemical Not applicable.

Special protective equipment and precautions for firefighters Not available.

Specific methods None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures Wear appropriate personal protective equipment.

Methods and materials for containment and cleaning up Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.

Environmental precautions Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling Avoid contact with skin, eyes and clothing.

Conditions for safe storage, including any incompatibilities Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection

Occupational exposure limits No exposure limits noted for ingredient(s).

Biological limit values No biological exposure limits noted for the ingredient(s).

Exposure guidelines Exposure limits have not been established for this product.

Appropriate engineering controls Use in a well ventilated area.

Individual protection measures, such as personal protective equipment

Eye/face protection Not available.

Skin protection

Hand protection Not available.

Other Not available.

Respiratory protection	Not available.
Thermal hazards	Not available.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Color	Cyan
Odor	Not available.
Odor threshold	Not available.
pH	8.5 - 9.5
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	> 212.0 °F (> 100.0 °C) Pensky-Martens Closed Cup US EPA Method 1020
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	3.2 - 3.3 cP
Other information	For other VOC regulatory data/information see Section 15.
VOC (Weight %)	< 291 g/L

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under recommended storage conditions.
Possibility of hazardous reactions	Will not occur.
Conditions to avoid	Not available.
Incompatible materials	Incompatible with strong bases and oxidizing agents.
Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.

11. Toxicological information

Symptoms related to the physical, chemical and toxicological characteristics	Not available.
Information on toxicological effects	
Acute toxicity	Based on available data, the classification criteria are not met.

Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory or skin sensitization	
Respiratory sensitization	Based on available data, the classification criteria are not met.
Skin sensitization	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Suspected of causing cancer.
Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Further information	Complete toxicity data are not available for this specific formulation Refer to Section 2 for potential health effects and Section 4 for first aid measures.

Components	Species	Test Results
2-pyrrolidone (CAS 616-45-5)		
Acute		
<i>Oral</i>		
LD50	Guinea pig	6500 mg/kg
	Rat	6500 mg/kg

12. Ecological information

Ecotoxicity

Components	Species	Test Results
2-pyrrolidone (CAS 616-45-5)		
Aquatic		
Crustacea	EC50	Water flea (<i>Daphnia pulex</i>)
		13.21 mg/l, 48 hours
Persistence and degradability	Not available.	
Bioaccumulative potential	Not available.	
Partition coefficient n-octanol / water (log Kow)		
2-pyrrolidone		-0.85
Mobility in soil	Not available.	
Other adverse effects	Not available.	

13. Disposal considerations

Disposal instructions	Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle .
------------------------------	---

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

ADR

Not regulated as dangerous goods.

15. Regulatory information

US federal regulations US TSCA 12(b): Does not contain listed chemicals.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
Delayed Hazard - Yes
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 No

Hazardous chemical

Other federal regulations

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations

US. Massachusetts RTK - Substance List

2-pyrrolidone (CAS 616-45-5)

US. New Jersey Worker and Community Right-to-Know Act

Not listed.

US. Pennsylvania Worker and Community Right-to-Know Law

2-pyrrolidone (CAS 616-45-5)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65

Not Listed.

Other information VOC content (less water, less exempt compounds) = 1148 g/L (U.S. requirement, not for emissions) VOC data based on formulation (Organic compounds minus solids)

Regulatory information All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision

Issue date 23-Mar-2015

Revision date 05-Nov-2015

Version # 06

Disclaimer This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Revision Information Composition / Information on Ingredients

Manufacturer information

HP
1501 Page Mill Road
Palo Alto, CA 94304-1112 US
Direct 1-650-857-5020

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds