

Part #	Power			Flow M ³ /H	0	1	2	2.6	3.2	3.6	4.2	4.5	Weight (lbs)
	HP	Volt	Amp	Flow (GPM)	0	4.6	9.1	11.5	14	16	18.4	20	
MA0343X-4 SS.MA0343X-4-115	1/2	115	6.5	Head (ft)	154	142	120	103	80	56	27	5	26
MA0343X-4A SS.MA0343X-4A-230	1/2	230	3.3	Head (ft)	154	142	120	103	80	56	27	5	26

A	B	C	D	E	MAX
26"	15.6"	13.7	1-1/4 NPT	3.86"	4.0"

Features & Technical Specifications:

- 4" deep well submersible pump, 150 feet max head. For 5" or larger well casing.
- Patented impeller provides heavy duty high flow: 25 GPM. That is greater than almost all other 1/2 HP well pumps.
- Water temperature: (32 ~113°F)
- Trans medium's Ph: 6.5~ 8.5
- Solid stainless steel body with heavy duty cast iron or stainless discharge
- Industrial grade heavy duty, also good for home usage
- Built in capacitor start, and thermal protection for longer life and powerful start.
- Built in control box. This pump DOES NOT require an external control box!
- This pump uses high quality UL approved motor, UL file No.: E233961
- This is a 2 wire pump with 3-Wire (2 wires + ground wire)
- 10' long electric cord comes with this submersible deep well pump.
- 1 1/4" NPT discharge
- Designed to fit inside 5" ID or larger pipe/well casing
- Heavy-duty thermoplastic impellers, diffusers, and intake screen.
- High efficiency, hermetically sealed motor is thermally protected to prevent overheating
- Submersible design eliminates the need for priming and creates quiet operation

