Safety Data Sheet

RUST-OLEUM CORPORATION
* Trusted Quality Since 1921 *
www.rustoleum.com

1. Identification

Name on Label: Specialty Appliance Epoxy

Product Name: SPECLT SSPR 6PK EPOXY APPL. STAINLESS

Revision Date: 2/5/2026

Product Identifier: 7887830

Supercedes Date: 10/5/2023

Recommended Use: Appliance Epoxy Topcoat/Aerosols

Supplier: Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, IL 60061
USA

Manufacturer: Rust-Oleum Corporation
11 Hawthorn Parkway
Vernon Hills, IL 60061
USA

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

Classification

Symbol(s) of Product



Signal Word
Danger

Possible Hazards
27% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS Hazard Statements

Aerosol, category 1	H222	Extremely flammable aerosol.
	H229	Pressurized container: may burst if heated.
Skin Sensitizer, category 1	H317	May cause an allergic skin reaction.
Eye Irritation, category 2A	H319	Causes serious eye irritation.
STOT, Single Exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Germ Cell Mutagenicity, category 1B	H340	May cause genetic defects.
Carcinogenicity, category 1B	H350	May cause cancer.
STOT, Repeated Exposure, category 2	H373	May cause damage to organs through prolonged or repeated exposure.

GHS Label Precautionary Statements

P201	Obtain special instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.

P251	Do not pierce or burn, even after use.
P260	Do not breathe dust, fumes, gas, mist, vapours, or spray.
P264	Wash thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P272	Contaminated work clothing should not be allowed out of the workplace.
P280	Wear protective gloves, protective clothing, eye protection, and face protection.
P302+P352	IF ON SKIN: Wash with plenty of soap and water.
P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P313	IF exposed or concerned: Get medical advice.
P312	Call a POISON CENTER or physician if you feel unwell.
P321	Specific treatment (see notice on this label).
P333+P313	If skin irritation or rash occurs: Get medical advice.
P337+P317	If eye irritation persists: Get medical help.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F.
P501	Dispose of contents and container in accordance with local, regional and national regulations.

GHS SDS Precautionary Statements

P363	Wash contaminated clothing before reuse.

3. Composition / Information on Ingredients

HAZARDOUS SUBSTANCES

Chemical Name	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Acetone	67-64-1	10-30	GHS02-GHS07	H225-319-332-336
n-Butyl Acetate	123-86-4	10-30	GHS02-GHS07	H226-336
Propane	74-98-6	10-30	GHS04	H280
n-Butane	106-97-8	5.0-10	GHS04	H280
Xylenes (o-, m-, p- Isomers)	1330-20-7	3.0-7.0	GHS02-GHS07	H226-315-332
Aluminum Flake	7429-90-5	1.0-5.0	GHS02	H228-250-261
Dimethyl Carbonate	616-38-6	0.5-1.5	GHS02-GHS06	H225-331
Ethylbenzene	100-41-4	0.5-1.5	GHS02-GHS07-GHS08	H225-304-332-351-373
1-Methoxy-2-Propyl Acetate	108-65-6	0.5-1.5	GHS02-GHS07	H226-332
Solvent Naphtha, Light Aromatic	64742-95-6	0.1-1.0	GHS07-GHS08	H304-332-340-350
Isobutyl Methacrylate	97-86-9	0.1-1.0	GHS02-GHS07	H226-315-317-319-335
Carbon Black	1333-86-4	0.1-1.0	Not Available	Not Available
Amorphous Precipitated Silica	112926-00-8	0.1-1.0	Not Available	Not Available

Actual concentrations of ingredients are withheld as trade secret.

4. First Aid Measures

First Aid - Eye Contact: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

First Aid - Skin Contact: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists. Wash contaminated clothing and decontaminate footwear before reuse.

First Aid - Inhalation: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

First Aid - Ingestion: If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively. Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Aqueous Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

Unusual Fire and Explosion Hazards: Water spray may be ineffective. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS LESS THAN -7°C (20°F). EXTREMELY FLAMMABLE LIQUID AND VAPOR!

Special Fire Fighting Procedures: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): Not a combustible dust.

6. Accidental Release Measures

Steps to Be Taken If Material Is Released or Spilled: Contain spilled liquid with sand or earth. DO NOT use combustible materials such as sawdust. Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers

7. Handling and Storage

Handling: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid prolonged or repeated contact with skin. Do not get in eyes, on skin or clothing. Do not puncture or incinerate (burn) container, even after use.

Storage: Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Contents under pressure. Do not store above 120°F (49°C). Store large quantities in buildings designed and protected for storage of flammable aerosols. Keep away from heat, sparks, flame and sources of ignition. Contents under pressure. Do not expose to heat or store above 120°F (49°C).

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV-TWA	ACGIH TLV-STEL	OSHA PEL-TWA	OSHA PEL-CEILING
Acetone	67-64-1	30.0	250 ppm	500 ppm	1000 ppm	N.E.
n-Butyl Acetate	123-86-4	25.0	50 ppm	150 ppm	150 ppm	N.E.
Propane	74-98-6	20.0	N.E.	N.E.	1000 ppm	N.E.
n-Butane	106-97-8	10.0	N.E.	1000 ppm	N.E.	N.E.
Xylenes (o-, m-, p- Isomers)	1330-20-7	10.0	20 ppm	N.E.	100 ppm	N.E.
Aluminum Flake	7429-90-5	5.0	1 mg/m3	N.E.	15 mg/m3	N.E.
Dimethyl Carbonate	616-38-6	5.0	N.E.	N.E.	N.E.	N.E.
Ethylbenzene	100-41-4	5.0	20 ppm	N.E.	100 ppm	N.E.
1-Methoxy-2-Propyl Acetate	108-65-6	5.0	N.E.	N.E.	N.E.	N.E.
Solvent Naphtha, Light Aromatic	64742-95-6	1.0	N.E.	N.E.	N.E.	N.E.
Isobutyl Methacrylate	97-86-9	1.0	N.E.	N.E.	N.E.	N.E.
Carbon Black	1333-86-4	1.0	3 mg/m3	N.E.	3.5 mg/m3	N.E.
Amorphous Precipitated Silica	112926-00-8	1.0	N.E.	N.E.	20 mppcf	N.E.

PERSONAL PROTECTION

Engineering Controls: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Facilities storing or utilizing this material should be equipped with an eyewash facility and a safety shower. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

Respiratory Protection: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 (U.S.) and/or SOR/86-304 Part XII 12.13 and CSA Standard Z180.1 (Canada) requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

Skin Protection: Use impervious gloves to prevent skin contact and absorption of this material through the skin.

Eye Protection: Use safety eyewear designed to protect against splash of liquids.

Other Protective Equipment: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications. Refer to safety supervisor or industrial hygienist for further information regarding personal protective equipment and its application.

Hygienic Practices: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Physical State	Liquid	**Decomposition Temperature, °C**	N.D.
Color	Stainless Steel	**pH**	N.D.
Odor	Solvent Like	**Kinematic Viscosity**	N.D.
Odor Threshold	N.E.	**Solubility in Water**	Slight
Freezing Point / Melting Point, °C	N.D.	**Partition Coefficient, n-octanol/water**	N.D.
Boiling Range, °C	-37 - 537	**Vapor Pressure**	N.D.
Flammability	Supports Combustion	**Evaporation Rate**	Faster than Ether
Lower Explosion Limit, vol%	1.0	**Specific Gravity**	0.760
Upper Explosion Limit, vol%	13.0	**Vapor Density**	Heavier than Air
Flash Point, °C	-96	**Particle Characteristics**	N.A.
Auto-Ignition Temperature, °C	N.D.		

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

Conditions to Avoid: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition. Flammable hydrogen gas will evolve when product comes in contact with water or damp air. Heat will be generated. The amount of heat generated will depend upon the volume of material in contact. Avoid excess heat.

Incompatibility: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

Hazardous Decomposition: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

Hazardous Polymerization: Will not occur under normal conditions.

Stability: This product is stable under normal storage conditions.

11. Toxicological Information

Effects of Overexposure - Eye Contact: Can cause severe eye irritation. Causes eye and skin irritation which may lead to dermatitis with repeated exposures. Irritating, and may injure eye tissue if not removed promptly.

Effects of Overexposure - Skin Contact: Substance may cause slight skin irritation. Prolonged or repeated skin contact may cause irritation. Causes skin irritation. Allergic reactions are possible. May cause skin sensitization, an allergic reaction, which becomes evident upon re-exposure to this material. Prolonged or repeated contact may cause skin irritation. Frequent or prolonged contact may irritate the skin and cause a skin rash (dermatitis). Low hazard for usual industrial handling or commercial handling by trained personnel.

Effects of Overexposure - Inhalation: Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled.

Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs.

Effects of Overexposure - Ingestion: Substance may be harmful if swallowed.

Effects of Overexposure - Chronic Hazards: May cause central nervous system disorder (e.g., narcosis involving a loss of coordination, weakness, fatigue, mental confusion, and blurred vision) and/or damage. High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. Contains carbon black. Chronic inflammation, lung fibrosis, and lung tumors have been observed in some rats experimentally exposed for long periods of time to excessive concentrations of carbon black and several insoluble fine dust particles. Tumors have not been observed in other animal species (i.e., mouse and hamster) under similar circumstances and study conditions. Epidemiological studies of North American workers show no evidence of clinically significant adverse health effects due to occupational exposure to carbon black.

Carbon black is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC and is proposed to be listed as A4- "not classified as a human carcinogen" by the American Conference of Governmental Industrial Hygienists. Significant exposure is not anticipated during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of carbon black in the formula. IARC lists Ethylbenzene as a possible human carcinogen (group 2B). Prolonged or repeated skin contact may cause dermatitis. May cause genetic defects.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES
The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
67-64-1	Acetone	5800 mg/kg Rat	>15700 mg/kg Rabbit	50.1 mg/L Rat
123-86-4	n-Butyl Acetate	10768 mg/kg Rat	>17600 mg/kg Rabbit	> 21 mg/L Rat
106-97-8	n-Butane	N.E.	N.E.	658 mg/L Rat
1330-20-7	Xylenes (o-, m-, p- Isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
616-38-6	Dimethyl Carbonate	13000 mg/kg Rat	5000 mg/kg Rabbit	>5.36 mg/L Rat
100-41-4	Ethylbenzene	3500 mg/kg Rat	15400 mg/kg Rabbit	17.4 mg/L Rat
108-65-6	1-Methoxy-2-Propyl Acetate	8532 mg/kg Rat	5000 mg/kg Rabbit	16 mg/L Rat
64742-95-6	Solvent Naphtha, Light Aromatic	8400 mg/kg Rat	>2000 mg/kg Rabbit	25
97-86-9	Isobutyl Methacrylate	9590 mg/kg Rat	N.E.	N.E.
1333-86-4	Carbon Black	>10000 mg/kg Rat	>2000 mg/kg Rabbit	N.E.
112926-00-8	Amorphous Precipitated Silica	>20000 mg/kg Rat	N.E.	N.E.

N.E. - Not Established

12. Ecological Information

Ecological Information: Product is a mixture of listed components. No ecotoxicity data was found for this product.

13. Disposal Considerations

Disposal: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not incinerate closed containers. This product as supplied is a US EPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	Air (IATA)	TDG (Canada)
UN Number:	N.A.	1950	1950	1950
Proper Shipping Name:	Paint and Related Spray Products in Ltd Qty	Aerosols	Aerosols, flammable	AEROSOLS, flammable
Hazard Class:	N.A.	2	2.1	2.1
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	Yes	Yes	Yes	Yes

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Carcinogenicity, Respiratory or Skin Sensitization, Serious eye damage or eye irritation, Specific target organ toxicity (single or repeated exposure), Germ cell mutagenicity

SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

Chemical Name	CAS-No.
Xylenes (o-, m-, p- Isomers)	1330-20-7
Aluminum Flake	7429-90-5
Ethylbenzene	100-41-4

Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

16. Other Information

HMIS RATINGS

Health: 2* **Flammability:** 4 **Physical Hazard:** 0 **Personal Protection:** X

NFPA RATINGS

Health: 2 **Flammability:** 4 **Instability:** 0

Maximum Incremental Reactivity: 1.12

SDS REVISION DATE: 2/5/2026

REASON FOR REVISION:

Product Composition Changed
Substance and/or Product Properties Changed in Section(s):
01 - Identification
02 - Hazard Identification
03 - Composition / Information on Ingredients
08 - Exposure Controls / Personal Protection
09 - Physical & Chemical Properties
11 - Toxicological Information
14 - Transport Information
15 - Regulatory Information
16 - Other Information
Substance Hazard Threshold % Changed
Substance Hazardous Flag Changed
Revision Statement(s) Changed

Legend: N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.