

More output and comfort compared to conventional water pump pliers of the same length: offers 9 adjustment positions for 30% more gripping capacity

- > good access to the workpiece due to slim size in the head and joint area
- > self-locking on pipes and nuts: no slipping off the workpiece and low handforce required
- > gripping surfaces with special hardened teeth, teeth hardness (approx. 61 HRC): low wear and reliable gripping
- > box-joint design: high stability because of double guide
- > robust construction; particularly suitable for outdoor work
- > pinch guard prevents operators' fingers being pinched
- > chrome vanadium electric steel; forged, multi stage oil-hardened

88 02 250 / 88 02 250 T BKA

Slim, two-color multi-component sleeves for better handling and easier transport

88 02 250 T BKA / 88 02 300 T BKA*

Pliers with integrated tether attachment point for tool drop protection system



Self-clamping on pipes and nuts: no slipping off the workpiece. Less handforce is required since handles do not need to be squeezed. Simply put pressure on the upper handle for a powerful grip.



88 01 180
 



88 01 250
 



88 02 250
 



88 02 250 T BKA
 




88 07 300
    



88 08 250 US
    

Alligator®



Product Number	Packaging	↔ Inch mm		Pliers	Head	Handles	Ø Inch Ø mm	Hex Inch mm	Adjustment positions	⚖ lbs
88 01 180	X	7 1/4 180					1 1/2 42	1 27/64 36	9	0.40
88 01 250	X	10 250		black atramentized	polished	non-slip plastic coated	2 50	1 13/16 46	9	0.75
88 01 300	X	12 300					2 3/4 70	2 3/64 60	9	1.19
88 02 180	X	7 1/4 180		black atramentized	polished	multi-component grips	1 1/2 42	1 27/64 36	9	0.47
88 02 250	X	10 250		black atramentized	polished	slim multi-component grips	2 50	1 13/16 46	9	0.83
88 02 250 T BKA	X	10 250		black atramentized	polished	slim multi-component grips, integrated tether attachment point	2 50	1 13/16 46	9	0.88
88 02 300	X	12 300		black atramentized	polished	multi-component grips	2 3/4 70	2 3/64 60	9	1.30
88 02 300 T BKA	X	12 300		black atramentized	polished	multi-component grips, integrated tether attachment point	2 3/4 70	2 3/64 60	9	1.39
88 07 300		12 300		chrome plated	polished	plastic dipped insulated, VDE-tested	2 3/4 70	2 3/64 60	9	1.46
88 08 250 US	X	10 250		black atramentized	polished	insulated, multi-component handles, ASTM-tested	1 31/32 50	1 13/16 46	9	0.87

*Learn more about our tethered tool system on pages 207-211