

With touchscreen function, for all-round work in in dry to slightly moist environments.

TEGERA® INFINITY 8814

Learn more

GREAT FIT, PALM DIPPED, CUT F GLOVE

Dexterous cut resistant glove with highest cut level F and touchscreen function, suitable for all-round work. 13 gg knitted with CRF® cut resistant technology. Palm dipped with super soft nitrile foam that provides excellent grip in dry and slightly moist environments. Reinforced thumb crotch for improved longevity. Breathable materials for all day comfort. Protection against contact heat up to 100°C/212°F. Wide range of sizes means a perfectly fitting glove for everyone. Skin friendly with Derma-test and Oeko-Tex certificate.

CHARACTERISTICS

- Highest level of protection
- Good fingertip sensitivity
- Flexible
- Durable
- Good grip
- Comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- For touchscreen
- Reinforcement between index finger and thumb

CRF®

ORIGINAL EXCELLENT dermatest 2019 dermatest-guarantee.de

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Cut injuries, Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt

PRIMARY ENVIRONMENTS OF USE

Cut risk environments, Dry environments, Moist environments, Dirty environments, Harsh environments

PRIMARY AREAS OF USE

Building and construction, Sheet-metal work, Engineering, Metalwork, Glass industry work, Repair work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Glass, ceramics and construction materials, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Transport equipment manufacturing, Transportation and logistics

TYPE OF WORK

Heavy weight

SPECIFICATION

TYPE Cut resistant gloves, Heat protection gloves
CATEGORY Cat. II
COLLECTION Infinity
KNITTING GAUGE (GG) 13
LINING MATERIAL Basalt fibre thread, CRF® Technology, HPPE, Polyester, Spandex, Stainless steel fibre yarn
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL Nitrile foam, Waterbased PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level F
CUT RESISTANCE (EN ISO 13997) TDM: 41.2 N
INNER MATERIAL SPECIFICATION HPPE (High performance polyethylene), Polyester, Stainless steel fibre yarn, Basalt fibre thread, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4X43F

EN 407:2020 (No flame protection) X1XXXX

ANSI A6 CUT

ANSI 5 ABR

Contact heat rating valid for palm area only

FEATURES

Cut protection

For touchscreen

SIZE		ARTICLE NUMBER	EAN
5	XXS	8814-5	7340118409177
6	XS	8814-6	7340118328683
7	S	8814-7	7340118324753
8	M	8814-8	7340118324760
9	L	8814-9	7340118324777
10	XL	8814-10	7340118324739
11	XXL	8814-11	7340118324746

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.