



EAN:	4013288229526	Size:	230x60x14 mm
Part number:	05006585001	Weight:	40 g
Article number:	Kraftform Kompakt VDE 3065 iS PZ/S TiE SB	Country of origin:	CZ
		Customs tariff number:	82054000

- Kraftform Kompakt VDE blade for PlusMinus screws slotted/Pozidriv
- Insulated, individually tested as per IEC 60900
- Reduced shaft diameter and integrated insulation protection
- In this way, low-lying PlusMinus screws can be accessed and actuated
- Blades made of stainless steel to prevent extraneous rust
- Vacuum ice-hardening provides the required hardness and strength
- 9 mm hex drive with entry chamfer
- Take it easy tool finder: colour coding by profile and laser-engraved size indication

VDE stainless blades for Kraftform Kompakt handle/blade system. Lightning-fast blade changes without special tools. Combination profile slotted and Pozidriv, especially for use with magnetic rails, fuse boxes, switches, relays. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. Reduced blade diameter with integrated protective insulation, low-lying screw and spring elements can be easily reached and operated. Wera's stainless steel tools are vacuum ice tempered and therefore have the hardness and strength properties required for screw connections. Industrial use is possible without restrictions. With Take it easy Tool finder: Colour coding by profile and laser-engraved size indication. The hexagon anti-roll protection avoids blades from rolling away unintentionally.

Web link

<https://www.wera.de/en/05006585001>

Wera - Kraftform Kompakt VDE 3065 iS PZ/S TiE SB
05006585001 - 4013288229526

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Screw stainless steel together with stainless steel!



Solution to the rust problem: screwdriving stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

Vacuum ice-hardened



The stainless steel tools from Wera are vacuum ice-hardened and have the hardness and strength needed for screw connections. There are no limitations to the industrial applications they are suitable for.

Individually tested



Testing the tool for dielectric strength at 10,000 volt gives the user the peace of mind that their tool has been tested for its most important property, insulation. Wera VDE tools are subjected to this test piece by piece which guarantees safe working at up to 1,000 volt.

Blades for handle



The VDE-insulated Kraftform Kompakt stainless blades are suitable for the 3817 VDE Stainless handle.

The handle/blade system – Kraftform Kompakt VDE




The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

PlusMinus screwdrivers




For the use in terminal blocks, control cabinets, switches, relays, sockets etc.

Reduced blade diameter for lower-lying screws



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

Take it easy tool finder



The Kraftform Kompakt VDE blades are equipped with the Take it easy tool finder. Colour coding by profile and laser-engraved size indication make it easy to identify the required tool quickly.

Web link

<https://www.wera.de/en/05006585001>

Wera - Kraftform Kompakt VDE 3065 iS PZ/S TIE SB
05006585001 - 4013288229526

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Set contents:

Kraftform Kompakt VDE 3065 iS PZ/S Take it easy, stainless steel, # 2 x 157 mm



1x # 2 x 157 mm



Web link

<https://www.wera.de/en/05006585001>

Wera - Kraftform Kompakt VDE 3065 iS PZ/S TiE SB
05006585001 - 4013288229526

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de