

EP-16


## Multi Props



| COD   | MOD      | + I    | I      | Kg   |   |
|-------|----------|--------|--------|------|---|
| 34000 | Puntal 0 | 60cm.  | 40cm.  | 1,10 | 5 |
| 30010 | Puntal 1 | 100cm. | 60cm.  | 1,36 |   |
| 30011 | Puntal 2 | 170cm. | 95cm.  | 1,38 |   |
| 30012 | Puntal 3 | 290cm. | 155cm. | 2,61 |   |
| 34004 | Puntal 4 | 375cm. | 200cm. | 3,18 | 1 |

**\* Cuadro de fuerzas  
Pressure table**

| COD     | 34000    | 30010    | 30011    | 30012    | 34004    |
|---------|----------|----------|----------|----------|----------|
| MOD     | Puntal 0 | Puntal 1 | Puntal 2 | Puntal 3 | Puntal 4 |
| 40 cm.  | 450 kg.  |          |          |          |          |
| 60 cm.  | 450 kg.  | 450 kg.  |          |          |          |
| 100 cm. |          | 450 kg.  | 450 kg.  |          |          |
| 155 cm. |          |          | 450 kg.  | 450 kg.  |          |
| 170 cm. |          |          | 300 kg.  | 450 kg.  |          |
| 200 cm. |          |          |          | 450 kg.  | 450 kg.  |
| 250 cm. |          |          |          | 220 kg.  | 350 kg.  |
| 290 cm. |          |          |          | 150 kg.  | 210 kg.  |
| 300 cm. |          |          |          |          | 200 kg.  |
| 325 cm. |          |          |          |          | 150 kg.  |
| 350 cm. |          |          |          |          | 90 kg.   |
| 375 cm. |          |          |          |          | 70 kg.   |



## Main features:

- New patented instant locking system
- Spring mechanism for quick locking
- screw adjusted pressure
- Non-slip pads adjustable for use at different angles
- Easy to use

## Materials and Finishing:

All raw materials without exception used in Ind. Piqueras tools come from countries within the European Union. This guarantees maximum quality and permits easy and full control.

|        |                                                                                                                                                                                                                                                               |
|--------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| TUBES  | <ul style="list-style-type: none"><li>*30x1 mm tube E-220 quality.Follows ruling EN-10130. Phospated and epoxy-polyester painted electrostatically in a rough grey colour.</li><li>*25x1 mm tube DX51DZ quality following ruling EN10327 galvanised</li></ul> |
| HANDLE | <ul style="list-style-type: none"><li>*Nylon and fibre glass handle</li></ul>                                                                                                                                                                                 |
| P ADS  | <ul style="list-style-type: none"><li>*Non-slip EVA pad cover</li><li>*Interior thick white zinc plated metal plate 3,5 mm without hexavalent Chromium</li><li>*Screw axles 12,9 quality DIN912,white zinc plated without hexavalent Chromium</li></ul>       |
| BRAKES | <ul style="list-style-type: none"><li>*Four tempered white zinc plated steel plates without hexavalent Chromium.</li><li>*Spring steel white zinc plated operating mechanism without hexavalent Chromium</li></ul>                                            |
| SCREW  | <ul style="list-style-type: none"><li>*White zinc coated steel without Hexavalent-Chromium</li></ul>                                                                                                                                                          |

The careful design also guarantees optimum mechanical performance.

## Packing and labelling:

In cling film boxed packets of five  
Individually coded label EAN-13

## RULES:

No special safety rulings applied  
All work carried out following ISO:9001 and ISO :14001 rules