DATA SHEET

Premium Efficiency Motor: **PEWWE1-18-143TC** **60 Hz**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 14-Oct-2024
Document ID:

Customer:

MOTOR INFORMATION

HP	1
RPM	1800
Phase	3
Frequency	60 Hz
Voltage	230/460 V
Frame Size	143TC
Enclosure	TEFC
Degree of Protection	IP55
Service Factor	1.25
Poles	4
Full Load Speed	1755
Insulation Class	F
Temp Rise	80°C
NEMA Code Letter	N
Duty Cycle	S1 / Continuous
Slip	2.50%
NEMA Design	B
Moment of Inertia	0.0809 lb.ft.^2
Locked Rotor Time (Hot)	12 seconds
Sound Pressure Level	60 dB(A)
Number of Starts	2 Cold/ 1 Hot
Max Ambient Temperature	40°C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Class 1 Division 2 Groups A,B,C,D T3C(160°C)
Inverter Rating	10:1 CT / 20:1 VT PWM Type
Standard	NEMA MG-1
Approvals	CSA-US, CE

ADDITIONAL DATA

F2 Suitable	Yes
Shaft Material	1045 Carbon Steel
Connection Diagram	230 / 460 V - 9 Lead Y
Approximate Weight	39.2 lbs.

EFFICIENCY/POWER FACTOR

LOAD	EFF	P. F.
100%	85.5 %	0.67
75%	84.5 %	0.60
50%	81.0 %	0.47

TORQUE

FULL LOAD	LRT	BDT
2.99 lb.ft.	300 %	420 %

AMPERAGE INFORMATION

	230V	460V
Full Load Amps	3.27A	1.63A
Locked Rotor Amps	30A	15A
No Load Current	2.2A	1.1A

Usable at 208V 3.61A

BEARING INFORMATION


DE Bearing	6205ZZ C3
ODE Bearing	6205ZZ C3
Grease Type	--
DE Regreasing Interval	- Hours
ODE Regreasing Interval	- Hours

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

MOTOR DRAWING

Premium Efficiency Motor: **PEWWE1-18-143TC**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	J	P	O	T	AB
E	2F1	2F	H	BA										
2.75	--	4	0.34	2.25	6.535	5.394	12.291	3.5	0.433	0.984	7.717	7.6	1.417	6.491

SHAFT & KEY					
S	ES	R	N-W	AH	U
0.188	1.41	0.771	2.25	2.12	0.875

TERMINAL BOX				
AA	XB	XC	XD	XF
3/4	1.61	4.55	4.094	4.256

FLANGE					
AJ	AK	BB	BD	BF	BC
5.875	4.5	0.16	6.496	3/8-16	0.12

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization

PERFORMANCE CURVES


Premium Efficiency Motor: **PEWWE1-18-143TC**


WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated:	14-Oct-2024
Document ID:	

Customer:

Motor Type	PEWWE						
Output Rating (HP)	1		FL Speed	1755			
Full Load Torque	2.99	lb.ft	LRT (%FLT)	300	460 volt FLA	1.63	
Rotor Wk^2	0.0809	lb-ft^2	BDT (%FLT)	420	230 volt FLA	3.27	





This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization.


NAMEPLATE / WIRING

Premium Efficiency Motor: **PEWWE1-18-143TC**

WorldWide Electric Corporation
1 (800) 808-2131
Worldwideelectric.net

Document Generated: 14-Oct-2024 Document ID:	Customer:

SAMPLE NAMEPLATE DATA



Model	PEWWE1-18-143TC						
HP	1	S.F.	1.25	IP	IP55	Encl	TEFC
Frame	143TC	P.F.	0.67	Code	N	Type	
Voltage	230/460 V	Hz	60 Hz	Ins Cl	F	Ambient	40°C
Amps	3.27/1.63	RPM	1755	Design	B	DE Brng	6205ZZ C3
Nom.Eff.	FL 85.5%	3/4	84.5%			ODE Brng	6205ZZ C3
Class 1 Division 2 Groups A,B,C,D T3C(160°C)						Grease type:	--

50Hz

1 HP	200/400 V	4.04/2.(A	1450 rpm
		Eff. 79.6%	

This document is the property of WorldWide Electric Corporation and may not be reproduced without express authorization