


Part #	Power			Flow M ³ /H	0	2	3.2	4.27	5.26	6.11	7.2	7.74	Weight (lbs)
	HP	Volt	Amp	Flow GPM	0	8.8	14.1	18.8	23.2	27	32	34.1	
MA0419X-12A-E SS.MA0419X-12AEXT-230	2	230	10.2	H (ft)	400	369	330	288	232	171	77	5	39
MA0419X-12A SS.MA0419X-12A-230	2	230	10.2	H (ft)	400	369	330	288	232	171	77	5	41

A	B	C	D	E	MAX
44.7"	21.1"	24"	1-1/4 NPT	3.5"	3.8"

Features & Technical Specifications:

- 3.8" deep well submersible pump, 14 stage, 400 feet Max head
- Fits 4" ID or larger well casing.
- Patented impeller provides heavy duty high flow: 35 GPM. That is greater than almost all other 2 HP well pumps.
- Solid stainless steel body with heavy duty cast iron or stainless discharge
- Industrial grade heavy duty, also good for home usage
- Capacitor start motor, and thermal protection for longer life and powerful start.
- MA0419X-12A and SS.MA0419X-12A-230 have a built in control box. This is a 2 wire pump with ground (2 wires + ground wire)
- MA0419X-12A-E and SS.MA0419X-12AEXT-230 have a control box. This is a 3 wire pump with ground (3 wires + ground wire)
- This pump uses high quality UL approved motor, UL file No.: E233961
- 10' long electric cord comes with this submersible deep well pump.
- 1/4" NPT discharge
- Designed to fit inside 4" ID or larger pipe/well casing
- Heavy-duty thermoplastic impellers, diffusers, and intake screen.
- High efficiency, hermetically sealed motor is thermally protected to prevent overheating
- Submersible design eliminates the need for priming and creates quiet operation



HEAD (feet)

HALLMARK INDUSTRIES

