ABB BALDOR RELIANCE

Customer information packet

09K443Y599G3

15 AIR OVERHP, 3525RPM, 3PH, 60HZ, 254TZ, 093
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 2:38:09 PM

Specifications

Enclosure	TEAO
Frame	254TZ
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	15.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	460.0 V @ 60 HZ
Agency Approvals	CSA
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	36.500 A @ 208.0 V
	34.400 A @ 230.0 V
	17.200 A @ 460.0 V
Design Code	A
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None
Heater Indicator	No Heater

Part Detail

Revision	V
Type	AC
Mech. spec.	09K443
Base	
Status	PRD/A
Elec. spec.	09WGY599
Layout	09LYK443
Eff. date	10-24-2024
CD Diagram	CD0180
Poles	02
Leads	9#12
Proprietary	False
Created date	10-22-2014

High Voltage Full Load Amps	17.2 a
Insulation Class	F
Inverter Code	Inverter Ready
KVA Code	H
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 12 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	0934M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	22.16 IN
Power Factor	88
Product Family	General Purpose
Pulley End Bearing Type	Sealed Bearing
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.625 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3525 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP1256L											
CAT.NO.											
SPEC.	09K443Y599G3										
HP	15 AIR OVER										
VOLTS	230/460										
AMP	34.4/17.2										
RPM	3525										
FRAME	254TZ		**HZ**	60			**PH**	3			
SER.F.	1.15	**CODE**	H	**DES**	A	**CLASS**	F				
NEMA-NOM-EFF	91.7	**PF**	88								
RATING	40C AMB-CONT										
CC											
DE	6309		**ODE**	6208							
ENCL	TEAO	**SN**									
	SFA 39.2/19.6										

AC Induction Motor Performance Data
Record # 77448
Typical performance - not guaranteed values

Winding: 09WGY599-R003	**Type:** 0934M	**Enclosure:** TEAO

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			15	**Full Load Torque**	22.2 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			34.4/17.2	**Breakdown Torque**	103 LB-FT
R.P.M.			3525	**Pull-up Torque**	33 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	41 LB-FT
NEMA Design Code	A	**KVA Code**	H	**Starting Current**	128 A
Service Factor (S.F.)			1.15	**No-load Current**	5.9 A
NEMA Nom. Eff.	91.7	**Power Factor**	88	**Line-line Res. @ 25ºC**	0.559 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	55°C
S.F. Amps				**Temp. Rise @ S.F. Load**	69°C
				Locked-rotor Power Factor	28.7
				Rotor inertia	0.868 LB-FT2

Load Characteristics 460 V, 60 Hz, 15 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	57	78	86	88	90	90	89
Efficiency	86.2	90.8	91.9	91.9	91.5	90.7	91.7
Speed	3583	3567	3550	3533	3514	3493	3522
Line amperes	7.2	10	13.4	17.2	21.2	25.5	19.6


ABB Motors and Mechanical Inc.


WINDING # 09WGY599

15 HP 3 PH 60 HZ 3525 RPM 460 V 0934M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=103 PU=33 LR=41 LRA=128





09LYK443
(920 - 960) = 22.16
6.15
4.32
4.00
NAMEPLATE
SH GND
NO KEYWAY
Ø 1.625
1.624
SLINGER
AUTO DRAIN
(EA. END)
8.25
8.25
.75
10.00
4.25
11.50
12.94
10.18
6.63
2.50
12.88
6.25
6.19
LEAD HOLE
Ø1.75
(FAR SIDE)
8 HOLES
Ø.53
5.00
5.00
8.18
5.75
11.50
BP5338A01
WAVY
WASHER
FR BRG DETAIL
PU BRG DETAIL
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT THE PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: CORRECT BOX PER BOM, 09CB3003 WITH 1.75" LEAD HOLE
REV: C
VERSION: 03
REVISED: 10:29:19 02/23/2023
TDR: 000001204617
MODEL NO. 09LYK443
REF: -
BY: USODDIL
B
BALDOR - RELIANCE®
HORZ TEAO 254-6TZ W/SLD BRGS, NO KWY, SH GND & CVR, ROT KOBX
09LYK443

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1