



SAFETY DATA SHEET

1. Identification

Product identifier F6U15Series
Other means of identification Not available.
Recommended use Inkjet printing
Recommended restrictions None known.
Company identification HP Inc.
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
Telephone 650-857-5020

HP Inc. health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-760-710-0048
HP Inc. Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards Not classified.
Health hazards Not classified.
Environmental hazards Not classified.
OSHA defined hazards Not classified.

Label elements

Hazard symbol None.
Signal word None.
Hazard statement Not available.
Precautionary statement
Prevention Not available.
Response Not available.
Storage Not available.
Disposal Not available.

Hazard(s) not otherwise classified (HNOC) Potential routes of exposure to this product are skin and eye contact, ingestion, and inhalation. Carbon black is classified by the IARC as a Group 2B carcinogen (the substance is possibly carcinogenic to humans). Carbon black in this preparation, due to its bound form, does not present this carcinogenic risk. Complete toxicity data are not available for this specific formulation. None of the other ingredients in this preparation are classified as carcinogens according to ACGIH, EU, IARC, MAK, NTP or OSHA.

Supplemental information This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	70-85
2-pyrrolidone		616-45-5	<10
Carbon black		1333-86-4	<5

Composition comments

This ink supply contains an aqueous ink formulation.
This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

Carbon black is present only in a bound form in this preparation.

4. First-aid measures**Inhalation**

Remove to fresh air. If symptoms persist, get medical attention.

Skin contact

Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.

Eye contact

Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.

Ingestion

If ingestion of a large amount does occur, seek medical attention.

Most important symptoms/effects, acute and delayed

Not available.

5. Fire-fighting measures**Suitable extinguishing media**

For small (incipient) fires, use media such as foam, sand, dry chemical, or carbon dioxide.
For large fires use very large (flooding) quantities of water and/or foam, applied as a mist or spray.

Unsuitable extinguishing media

None known.

Specific hazards arising from the chemical

Not applicable.

Special protective equipment and precautions for firefighters

Not available.

Specific methods

None established.

6. Accidental release measures**Personal precautions, protective equipment and emergency procedures**

Wear appropriate personal protective equipment.

Methods and materials for containment and cleaning up

Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.

Environmental precautions

Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage**Precautions for safe handling**

Avoid contact with skin, eyes and clothing.

Conditions for safe storage, including any incompatibilities

Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
Carbon black (CAS 1333-86-4)	PEL	3.5 mg/m3

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Carbon black (CAS 1333-86-4)	TWA	3 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Carbon black (CAS 1333-86-4)	TWA	0.1 mg/m3

Biological limit values

No biological exposure limits noted for the ingredient(s).

Exposure guidelines	Exposure limits have not been established for this product.
Appropriate engineering controls	Use in a well ventilated area.
Individual protection measures, such as personal protective equipment	
Eye/face protection	Not available.
Skin protection	
Hand protection	Not available.
Other	Not available.
Respiratory protection	Not available.
Thermal hazards	Not available.
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice.

9. Physical and chemical properties

Appearance

Physical state	Liquid.
Color	Black.
Odor	Not available.
Odor threshold	Not available.
pH	7.5 - 9
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	> 230.0 °F (> 110.0 °C) Pensky-Martens Closed Cup
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	For other VOC regulatory data/information see Section 15.
VOC (Weight %)	209 g/L

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under recommended storage conditions.
Possibility of hazardous reactions	Will not occur.
Conditions to avoid	Not available.
Incompatible materials	Incompatible with strong bases and oxidizing agents.

Hazardous decomposition products

Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.

11. Toxicological information

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitization

Respiratory sensitization Based on available data, the classification criteria are not met.

Skin sensitization Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

IARC Monographs. Overall Evaluation of Carcinogenicity

Carbon black (CAS 1333-86-4) 2B Possibly carcinogenic to humans.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure Based on available data, the classification criteria are not met.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

Further information Complete toxicity data are not available for this specific formulation

Components	Species	Test Results
-------------------	----------------	---------------------

2-pyrrolidone (CAS 616-45-5)

Acute

Oral

LD50	Guinea pig	6500 mg/kg
	Rat	6500 mg/kg

Carbon black (CAS 1333-86-4)

Acute

Oral

LD50	Rat	> 8000 mg/kg
------	-----	--------------

12. Ecological information

Aquatic toxicity This product has not been tested for ecological effects.

Ecotoxicity

Components	Species	Test Results
-------------------	----------------	---------------------

2-pyrrolidone (CAS 616-45-5)

Aquatic

Crustacea	EC50	Water flea (Daphnia pulex)	13.21 mg/l, 48 hours
-----------	------	----------------------------	----------------------

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Partition coefficient n-octanol / water (log Kow)

2-pyrrolidone	-0.85
---------------	-------

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions

Do not allow this material to drain into sewers/water supplies.
Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations.
HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

ADR

Not regulated as dangerous goods.

Further information

Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations

US TSCA 12(b): Does not contain listed chemicals.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)**Hazard categories**

Immediate Hazard - No
Delayed Hazard - No
Fire Hazard - No
Pressure Hazard - No
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312

No

Hazardous chemical**Other federal regulations****Safe Drinking Water Act (SDWA)**

Not regulated.

US state regulations**US. Massachusetts RTK - Substance List**

2-pyrrolidone (CAS 616-45-5)
Carbon black (CAS 1333-86-4)

US. New Jersey Worker and Community Right-to-Know Act

Carbon black (CAS 1333-86-4)

US. Pennsylvania Worker and Community Right-to-Know Law

2-pyrrolidone (CAS 616-45-5)
Carbon black (CAS 1333-86-4)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65

US - California Proposition 65 - CRT: Listed date/Carcinogenic substance

CARBON BLACK (AIRBORNE, UNBOUND PARTICLES Listed: February 21, 2003
OF RESPIRABLE SIZE [\leq 10 MICROMETERS]) (CAS
1333-86-4)

Other information	VOC content (less water, less exempt compounds) = 899 g/L (U.S. requirement, not for emissions) VOC data based on formulation (Organic compounds minus solids)
Regulatory information	All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision

Issue date	08-Apr-2016
Version #	01
Disclaimer	This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.
Manufacturer information	HP Inc. 1501 Page Mill Road Palo Alto, CA 94304-1112 US Direct 1-650-857-5020
Explanation of abbreviations	

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds