marathon®

General Purpose Motors

Model No: 256TTFCD6030
Catalog No: GT1125A

General Purpose Motor, 20 HP, 3 Ph, 60 Hz, 575 V, 1800 RPM, 256T Frame, TEFC

©2026 Marathon, All Rights Reserved.

marathon®

Product Information Packet: Model No: 256TTFCD6030, Catalog No: GT1125A General Purpose Motor, 20 HP, 3 Ph, 60 Hz, 575 V, 1800 RPM, 256T Frame, TEFC

Nameplate Specifications

Phase	**3**	Output HP	**20 Hp**
Output KW	**14.9 kW**	Voltage	**575 V**
Speed	**1768 r/min**	Synchronous RPM	**1800 r/min**
Service Factor	**1.15**	Frame	**256T**
Enclosure	**Totally Enclosed Fan Cooled**	Thermal Protection	**No Protection**
Efficiency	**93 %**	Ambient Temperature	**40 °C**
Frequency	**60 Hz**	Current	**19.4 A**
Power Factor	**83.5**	Duty	**Continuous**
Insulation Class	**F**	Design Code	**B**
KVA Code	**G**	Drive End Bearing Size	**6309**
Opp Drive End Bearing Size	**6209**	UL	**Listed**
CSA	**Y**	CE	**Y**
IP Code	**55**	Number of Speeds	**1**
Hazardous Location	**DIVISION 2 T2B**		

Technical Specifications


Electrical Type	**Squirrel Cage Inverter Rated**	Starting Method	**Line Or Inverter**
Poles	**4**	Rotation	**Reversible**
Resistance Main	**.513 O**	Mounting	**Rigid Base**
Motor Orientation	**Horizontal**	Drive End Bearing	**Ball**
Opp Drive End Bearing	**Ball**	Frame Material	**Cast Iron**
Shaft Type	**T**	Overall Length	**25.89 in**
Frame Length	**9.84 in**	Shaft Diameter	**1.626 in**
Shaft Extension	**4 in**	Assembly/Box Mounting	**F1/F2 Capable**
Inverter Load	**Constant 10:1/Variable 10:1**		


Drawings


Connection Drawing	**EE7300**	Outline Drawing	**SS620703-200**

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created: 14/10/2026

DASH NO.	B	C	E	2E	2F	2FF	BA	BS	MOUNTING	FRAME
100	9.60	24.15	5.00	10.00	-	8.25	4.25	4.13	F1 OR F2	254T
200	11.34	25.89			8.25	10.00		5.00		254/256T







DRAWING REVISION: E	REVISION BY: SB	REV DATE/© DATE: 07/22/2025
REQUEST NUMBER: CR-0023556	APPROVED BY: SBD	DATE: 07/22/2025
REQUEST NUMBER DESCRIPTION: DRAWING TITLE BLOCK UPDATED		

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: MR	
DATE: 4/5/2015	
APPROVED BY: KRK	
DATE: 4/5/2015	
REFERENCE	MATERIAL / PROCESS/FINISH
THIRD ANGLE PROJECTION	SIZE: B / DRAWING NUMBER: SS620703 / SHEET: 1 OF 1


marathon™

DESCRIPTION: OUTLINE
254/256T FR-TEFC-CAST IRON

THREE PHASE - SINGLE VOLTAGE
MOTOR - CONDUIT BOX @ 'A'


TO REVERSE ROTATION:
INTERCHANGE ANY TWO LINE
LEAD CONNECTIONS

TERMINAL BLOCK WHEN SPECIFIED




VIEW OF TERMINAL END

IF MOTOR HAS
9 LEADS



IF MOTOR HAS
6 LEADS



A-9806 DECAL

OPTIONAL CORD
CONNECTION

L1	WHITE
L2	RED
L3	BLACK

DRAWING REVISION: AD	REVISION BY: SB	REV DATE/© DATE: 08/01/2025
REQUEST NUMBER: CR-0023654	APPROVED BY: SBD	DATE: 08/01/2025

REQUEST NUMBER DESCRIPTION
DRAWING TITLE BLOCK UPDATED

COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY: DA	
DATE: 03-26-1993	
APPROVED BY: TB	
DATE: 03-26-1993	
REFERENCE	
THIRD ANGLE PROJECTION	

marathon™

DESCRIPTION
CONNECTION DIAGRAM
EXTERNAL - SINGLE VOLTAGE - 3Ø MOTOR

MATERIAL	PROCESS/FINISH


SIZE	DRAWING NUMBER	SHEET
A	EE7300	1 OF 1

Uncontrolled Copy

MARATHON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Customer		**Curve at**	575	**Volts**	**HP** 20.00	**PHASE**	3
			60	**HZ**			
Model No	256TTFCD6030		20	**HP**	**VOLTS** 575		
Catalog No	GT1125A				**HZ** 60	**RPM**	1768



Torque in Lb.Ft

FL TORQUE	59.4	**Lb.Ft**	**FL AMPS**	19.4	
BD TORQUE	146.0	**Lb.Ft**	**PU TORQUE**	99.0	**Lb.Ft**
LR TORQUE	119	**Lb.Ft**	**LR AMPS**	115.2	
WINDING	HE31604010-3	**Prepared By**	FAREEDA	**Date**	5/4/2018