TORQUE WRENCH TESTER

PCE-TWT 500



Specification

Torque	
Measuring range up to	0,01 ... 500 Nm
Resolution	0,01 Nm
Accuracy	±1% of the measured value (of m.v.)

General technical data	
Measuring functions	peak, MAX, MIN, AVG
Units	Nm, kgf cm, lbf in
Display Typ	LCD
Display size	3,3 Inch
Storage medium	Internal memory
Storage capacity	99 Values
Data interface	RS232
Automatic shutdown adjustable	0 ... 9999 min.
Automatic switch-off can be deactivated	Yes
Menu language	English (GB), English (US)
Protection class (device)	IP40
Power supply	100 ... 240V AC / 12V DC
Connector type	Euro plug
Operating conditions	5 ... 35 °C , 15 ... 80 %RH
Storage conditions	-10 ... 60 °C , 15 ... 80 %RH
Dimensions (L x W x H)	1150 x 560 x 360 mm
Weight	4300 g

PCE Americas Inc. dba PCE Instruments
1201 Jupiter Park Drive, Suite 8
Jupiter, FL 33458
USA

Phone: +1-561-320-9162
info@pce-americas.com