

PRODUCT DATASHEET

RETROFIT STRIP 4 ft 30W 120-277V 4000K

SYLVANIA STRIP RETROFIT 1A | SYLVANIA Strip Retrofit kit for replacing existing fluorescent strips without removing the original body



Areas of application

- Offices
- Retail
- Manufacturing
- Education
- Warehouses

Product features

- Can be used on fluorescent luminaire bodies 4.25" to 5.25" wide
- Available in 3500K, 4000K, or 5000K color temperature
- Offered in 25, 30, 46, and 54 watts
- 0-10V dimmable down to 10 %
- Emergency battery back-up versions available



TECHNICAL DATA

Additional product data

Ordering Abbreviation	RSTRIP1A/030UNVD840/48U/WH
Abbrev. With Packaging Info.	RSTRIP1A030UNVD84048UWH 1/CS 1/SKU
NAED	61475
General Description	Retrofit Strip LED Fixture 1A, 25 Watts, 4020 lumens, 120-277V, 0-10V Dimmable, 80+ CRI, 4000K, 48in, installs on strip bodies 4.25" to 5.25" wide, White Painted Finish
Warranty	5 years

Electrical data

Nominal Wattage	30.00 W
Nominal voltage	120.00...277.00 V
Power factor	≥0.90
Total Harmonic Distortion	< 20 %

Photometrical data

Lumens	4020 lm
Efficacy	134 lm/W
Color Temperature/CCT	4000 K
Color Rendering Index (CRI)	80
Luminaire Type	Retrofit

Dimensions & Weight

Length	48.03 in
Width	5.83 in
Height	2.42 in
Product weight	5.38 lb

Materials & Colors

Luminaire Finish	White
Housing color	White
Housing	Metal

Application & Mounting

Ambient temperature range	-20...+50 °C
Maximum Operating Temperature	122 °F
Minimum Operating Temperature	-4 °F

Dimming	Yes
Type of Dimming	0-10V
Mounting	Surface
Indoor/Outdoor	Indoor
Replaceable light source	No

Lifespan

Average Rated Life (hr)	150000
-------------------------	--------

Logistical data

Case Qty	1
Case Length (in)	50.000
Case Width (in)	6.863
Case Depth (in)	4.548
Case Cube (ft)	0.903
Case Weight (lbs)	7.369
Pallet Qty	60

Certificates & Standards

Certification Listing	RoHS / FCC / cULus
Replaceable light source (EPREL)	Not replaceable

EQUIPMENT / ACCESSORIES

- All mounting hardware
- Can only be used for retrofitting existing 4' and 8' fluorescent strip luminaires

Safety advice

- 120-277 Vac
- Can only be used for retrofitting existing 4' and 8' fluorescent strip luminaires
- cULus

DOWNLOAD DATA

Spec Sheets and Product Documents		Document name
	Installation Guide	INSTALL GUIDE RSTRIP1A
	Installation Guide	Installation Guide SYLVANIA Strip Retrofit
	Product Family Spec Sheet	ValueLED Strip Retrofit PIB / Cut Sheet

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.