

Highly dexterous and made with 48% Dyneema® bio-circular fiber.

TEGERA® 905

Learn more

THIN WITH BIO-CIRCULAR CUT PROTECTION

Thin and dexterous cut protection glove for fine assembly work with small sharp objects. The glove is made with 48% Dyneema® bio-circular fiber, an innovation that reduces dependence on fossil raw materials. The glove is extremely light, 18 gg, and has PU dipping for better grip. Cut resistance level B.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Good grip
- Extra comfortable

FUNCTIONS

- Ultra thin
- Super soft

Dyneema®

OEKO TEX® STANDARD 100 SE 14-214 RISE

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF
Cut injuries, Scratches, lacerations

PRIMARY ENVIRONMENTS OF USE
Cut risk environments, Dry environments, Clean environments, Moist environments

PRIMARY AREAS OF USE
Fine assembly, Inspection work, Installation work, Painting

PRIMARY INDUSTRIES OF USE
Automotive manufacturing, Building and construction, Electrical equipment manufacturing, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Pulp and paper, Rubber and plastics manufacturing, Transport equipment manufacturing, Warehousing

TYPE OF WORK
Light weight

SPECIFICATION
TYPE Cut resistant gloves
CATEGORY Cat. II
KNITTING GAUGE (GG) 18
LINING MATERIAL Dyneema® fiber from bio-circular feedstock , Nylon, Spandex
LENGTH 210-250 mm
DEXTERITY 5
GRIP DESIGN Smooth finish
COLOUR White
PAIRS PER: BUNDLE/CARTON 12/120
DISPLAY TYPE Bulk pack
DIPPING Palm-dipped
DIPPING MATERIAL PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level B
CUT RESISTANCE (EN ISO 13997) TDM: 5.4 N
INNER MATERIAL SPECIFICATION UHMWPE (Ultra high molecular weight polyethylene), Nylon, Elastane
OUTER MATERIAL SPECIFICATION Polyurethane

COMPLIANCE
CE Cat. II

EAC TP TC 019:2011

EN ISO 21420:2020

EN 388:2016+A1:2018 3X41B

ANSI A2 CUT

ANSI 3 ABR

FEATURES
Cut protection

SIZE		ARTICLE NUMBER	EAN
5	XXS	905-5	7340118329550
6	XS	905-6	7340118324579
7	S	905-7	7340118324586
8	M	905-8	7340118324593
9	L	905-9	7340118324609
10	XL	905-10	7340118324555
11	XXL	905-11	7340118324562

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.