



SAFETY DATA SHEET

1. Identification

Product identifier B6Y22Series
Other means of identification Not available.
Recommended use Inkjet printing. For use only in inkjet printing
Recommended restrictions None known.
Company identification HP
1501 Page Mill Road
Palo Alto, CA 94304-1112
United States
Telephone 650-857-5020

HP health effects line
(Toll-free within the US) 1-800-457-4209
(Direct) 1-760-710-0048
HP Customer Care Line
(Toll-free within the US) 1-800-474-6836
(Direct) 1-208-323-2551
Email: hpcustomer.inquiries@hp.com

2. Hazard(s) identification

Physical hazards Not classified.
Health hazards Not classified.
Environmental hazards Not classified.
OSHA defined hazards Not classified.

Label elements

Hazard symbol None.
Signal word None.
Hazard statement Not available.
Precautionary statement
Prevention Not available.
Response Not available.
Storage Not available.
Disposal Not available.

Hazard(s) not otherwise classified (HNOC) Potential routes of overexposure to this product are skin and eye contact. Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions. Complete toxicity data are not available for this specific formulation.

Supplemental information This product is not classified as hazardous according to OSHA CFR 1910.1200 (HazCom 2012).

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Water		7732-18-5	80-90
Cyclo Amide		Proprietary	<10
Diethylene glycol		111-46-6	<2.5
Carbon black		1333-86-4	<1

Composition comments

This ink supply contains an aqueous ink formulation.
This product has been evaluated using criteria specified in 29 CFR 1910.1200 (Hazard Communication Standard).

Carbon black is present only in a bound form in this preparation.

4. First-aid measures

Inhalation	Remove to fresh air. If symptoms persist, get medical attention.
Skin contact	Wash affected areas thoroughly with mild soap and water. Get medical attention if irritation develops or persists.
Eye contact	Do not rub eyes. Immediately flush with large amounts of clean, warm water (low pressure) for at least 15 minutes or until particles are removed. If irritation persists get medical attention.
Ingestion	If ingestion of a large amount does occur, seek medical attention.
Most important symptoms/effects, acute and delayed	Not available.

5. Fire-fighting measures

Suitable extinguishing media	Dry chemical, CO2, water spray or regular foam.
Unsuitable extinguishing media	None known.
Specific hazards arising from the chemical	Not applicable.
Special protective equipment and precautions for firefighters	Not available.
Specific methods	None established.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Wear appropriate personal protective equipment.
Methods and materials for containment and cleaning up	Dike the spilled material, where this is possible. Absorb with inert absorbent such as dry clay, sand or diatomaceous earth, commercial sorbents, or recover using pumps.
Environmental precautions	Do not let product enter drains. Do not flush into surface water or sanitary sewer system.

7. Handling and storage

Precautions for safe handling	Avoid contact with skin, eyes and clothing.
Conditions for safe storage, including any incompatibilities	Keep out of the reach of children. Keep away from excessive heat or cold.

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
Carbon black (CAS 1333-86-4)	PEL	3.5 mg/m3

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Carbon black (CAS 1333-86-4)	TWA	3 mg/m3	Inhalable fraction.

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Carbon black (CAS 1333-86-4)	TWA	0.1 mg/m3

US. Workplace Environmental Exposure Level (WEEL) Guides

Components	Type	Value
Diethylene glycol (CAS 111-46-6)	TWA	10 mg/m ³
Biological limit values	No biological exposure limits noted for the ingredient(s).	
Exposure guidelines	Exposure limits have not been established for this product.	
Appropriate engineering controls	Not available.	
Individual protection measures, such as personal protective equipment		
Eye/face protection	Wear safety glasses with side shields (or goggles).	
Skin protection		
Hand protection	Use protective gloves made of: Nitrile rubber.	
Other	Wear appropriate chemical resistant clothing.	
Respiratory protection	Not available.	
Thermal hazards	Not available.	
General hygiene considerations	Handle in accordance with good industrial hygiene and safety practice.	

9. Physical and chemical properties**Appearance**

Physical state	Liquid.
Color	Grey
Odor	Not available.
Odor threshold	Not available.
pH	8 - 10
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	> 200.0 °F (> 93.3 °C) Pensky-Martens Closed Cup
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Specific gravity	1 - 1.1
Other information	For other VOC regulatory data/information see Section 15.
VOC (Weight %)	< 141 g/l

10. Stability and reactivity

Reactivity	Not available.
Chemical stability	Stable under recommended storage conditions.
Possibility of hazardous reactions	None known.
Conditions to avoid	Not available.
Incompatible materials	Incompatible with strong bases and oxidizing agents.
Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons., fluorinated hydrocarbons and hydrogen fluoride.

11. Toxicological information

Symptoms related to the physical, chemical and toxicological characteristics Not available.

Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitization

Respiratory sensitization Based on available data, the classification criteria are not met.

Skin sensitization Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met. Carbon black is classified as a carcinogen by the IARC (possibly carcinogenic to humans, Group 2B) and by the State of California under Proposition 65. In their evaluations of carbon black, both organizations indicate that exposure to carbon black, per se, does not occur when it remains bound within a product matrix, specifically, rubber, ink, or paint. Carbon black is present only in a bound form in this preparation.

IARC Monographs. Overall Evaluation of Carcinogenicity

Carbon black (CAS 1333-86-4) 2B Possibly carcinogenic to humans.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure Based on available data, the classification criteria are not met.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

Further information Complete toxicity data are not available for this specific formulation

Components	Species	Test Results
Carbon black (CAS 1333-86-4)		
Acute		
<i>Oral</i>		
LD50	Rat	> 8000 mg/kg
Diethylene glycol (CAS 111-46-6)		
Acute		
<i>Dermal</i>		
LD50	Rabbit	11890 mg/kg
<i>Oral</i>		
LD50	Cat	3300 mg/kg
	Dog	9000 mg/kg
	Guinea pig	8700 mg/kg

Components	Species	Test Results
	Mouse	13.3 g/kg
	Rabbit	26.9 g/kg
	Rat	12565 mg/kg
<i>Other</i>		
LD50	Mouse	9.6 g/kg
	Rabbit	2000 mg/kg
	Rat	7700 mg/kg
		7.7 g/kg

12. Ecological information

Aquatic toxicity No information available.

Ecotoxicity

Product	Species	Test Results
B6Y22Series (CAS Mixture)		
Aquatic		
Fish	LC50	Fathead minnow (<i>Pimephales promelas</i>) > 750 mg/l, 96 Hours
Components	Species	Test Results
Diethylene glycol (CAS 111-46-6)		
Aquatic		
Fish	LC50	Western mosquitofish (<i>Gambusia affinis</i>) > 32000 mg/l, 96 hours

Persistence and degradability Not available.

Bioaccumulative potential Not available.

Mobility in soil Not available.

Other adverse effects Not available.

13. Disposal considerations

Disposal instructions Do not allow this material to drain into sewers/water supplies. Dispose of waste material according to Local, State, Federal, and Provincial Environmental Regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit <http://www.hp.com/recycle>.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

ADR

Not regulated as dangerous goods.

Further information Not a dangerous good under DOT, IATA, ADR, IMDG, or RID.

15. Regulatory information

US federal regulations US TSCA 12(b): Does not contain listed chemicals.
US EPA TSCA Inventory: All chemical substances in this product comply with all rules or orders under TSCA.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories Immediate Hazard - No
 Delayed Hazard - No
 Fire Hazard - No
 Pressure Hazard - No
 Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 No
Hazardous chemical

Other federal regulations

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations**US. Massachusetts RTK - Substance List**

Carbon black (CAS 1333-86-4)

US. New Jersey Worker and Community Right-to-Know Act

Carbon black (CAS 1333-86-4)

US. Pennsylvania Worker and Community Right-to-Know Law

Carbon black (CAS 1333-86-4)

Diethylene glycol (CAS 111-46-6)

US. Rhode Island RTK

Not regulated.

US. California Proposition 65**US - California Proposition 65 - CRT: Listed date/Carcinogenic substance**

CARBON BLACK (AIRBORNE, UNBOUND PARTICLES OF RESPIRABLE SIZE [≤ 10 MICROMETERS]) (CAS 1333-86-4) Listed: February 21, 2003

Other information VOC content (less water, less exempt compounds) = < 1088 g/L (U.S. requirement, not for emissions)
 VOC data based on formulation (Organic compounds minus solids)

Regulatory information All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.

16. Other information, including date of preparation or last revision**Issue date** 03-Jun-2015**Revision date** 31-Aug-2015**Version #** 02

Disclaimer This Safety Data Sheet document is provided without charge to customers of HP. Data is the most current known to HP at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in Section 1 above and may not meet regulatory requirements in other countries.

Revision Information Hazard(s) identification: Hazard(s) not otherwise classified (HNOC)
 Composition / Information on Ingredients
 Other information, including date of preparation or last revision: Disclaimer

Manufacturer information HP
 1501 Page Mill Road
 Palo Alto, CA 94304-1112 US
 Direct 1-650-857-5020

Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds