

Premium Duty Spring Retractable Reels

Air/Water/Oil/Grease - 1/4", 3/8", 1/2" I.D.




- Compact for a wide range of applications with critical space requirements
- Robotically welded steel base offers maximum strength and consistent quality
- Guide arm adjusts to two positions
- All steel components are powder coated for maximum corrosion resistance
- Inlet hose is plumbed into the base to eliminate the risk of stress on the swivel



5650 OLP

Additional Series 5000 / 5005 Models

- Enclosed Reels** - Page 11
- S.S. Fluid Path** - Page 18
- Stainless Steel** - Page 19
- Twin Hydraulic** - Page 22
- Cord Reels** - Page 30-33
- Welding Gas** - Page 35



Side Mount Reels


Visit reelcraft.com/catalog for side mount reels.

Model with hose & bumper	Shipping Weight	Hose I.D.	Hose O.D.	Hose Length	Max Pressure	NPT(M) Hose Outlet	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index #
lbs	kg	in	mm	ft	m	psi	bar	in	in
Low Pressure Air/Water Reels Maximum Temperature 150 °F (65 °C) Max working pressure is at 70 °F (20 °C)									
5450 OLP	26 12	1/4 6	.475 12	50 15	300 21	1/4	3/8	1/4	1
B5450 OLP	26 12	1/4 6	.475 12	50 15	300 21	1/4	3/8	1/4	1
5450 OLP-HTH*	26 12	1/4 6	.475 12	50 15	300 21	1/4	3/8	1/4	1
5635 OLP	25 11	3/8 10	.600 15	35 11	300 21	1/4	3/8	1/4	1
B5635 OLP	25 11	3/8 10	.600 15	35 11	300 21	1/4	3/8	1/4	1
5650 OLP***	36 16	3/8 10	.600 15	50 15	300 21	1/4	3/8	1/4	2
B5650 OLP	36 16	3/8 10	.600 15	50 15	300 21	1/4	3/8	1/4	2
A5825 OLP	27 12	1/2 13	.750 19	25 8	300 21	1/2	3/8	1/2	1
B5825 OLP	27 12	1/2 13	.750 19	25 8	300 21	1/2	3/8	1/2	1
A5835 OLP	39 18	1/2 13	.750 19	35 11	300 21	3/8	3/8	1/2	2
A5850 OLP***	41 19	1/2 13	.750 19	50 15	300 21	1/2	3/8	1/2	3
B5850 OLP	41 19	1/2 13	.750 19	50 15	300 21	1/2	3/8	1/2	3
Medium Pressure Oil Reels Maximum Temperature 210 °F (99 °C)									
5630 OMP	31 14	3/8 10	.690 18	30 9	2600 179	3/8	3/8	3/8	1
A5825 OMP**	34 15	1/2 13	.820 21	25 8	3000 207	1/2	3/8	1/2	1
A5835 OMP	42 19	1/2 13	.820 21	35 11	3000 207	1/2	3/8	1/2	2
High Pressure Grease Reels Maximum Temperature 210 °F (99 °C)									
5430 OHP	30 14	1/4 6	.580 15	30 9	5000 345	1/4	1/4	1/4	1
5625 OHP	32 15	3/8 10	.730 19	25 8	4800 331	1/4	1/4	1/4	1

Low pressure reels furnished standard with PVC hose. Medium pressure reels furnished standard with S.A.E. 100R1-AT (3/8") or S.A.E. 100R17 (1/2") one wire braid hose. High pressure reels furnished standard with S.A.E. 100 R2T two wire braid hose. *Model is supplied with low pressure, rubber hose for temperatures up to 212 °F (not for use with water above 180 °F). **Floor or tank mount only - Do NOT mount on ceiling. ***Side mount configuration available; visit reelcraft.com for more information.

Model without hose & bumper	Shipping Weight	Hose Capacity	Max Pressure	NPT(F) Reel Inlet	NPT(F) Reel Outlet	Size Index #
lbs	kg	I.D. O.D. Length	psi bar	in	in	
in	mm	in	mm	ft	m	
Low Pressure Air/Water Reels Maximum Temperature 210 °F (99 °C)						
5400 OLP	20 9	1/4 6 .475 12	500 35	3/8	1/4	1
5600 OLP	21 10	3/8 10 .600 15	500 35	3/8	1/4	1
5605 OLP	21 10	3/8 10 .600 15	500 35	3/8	1/4	2
A5800 OLP	22 10	1/2 13 .750 19	500 35	3/8	1/2	1
A5806 OLP	35 16	1/2 13 .750 19	500 35	3/8	1/2	3
Medium Pressure Oil Reels Maximum Temperature 210 °F (99 °C)						
5400 OMP	23 10	1/4 6 .530 13	3000 207	3/8	3/8	1
5600 OMP	24 11	3/8 10 .690 18	3000 207	3/8	3/8	1
A5800 OMP**	24 11	1/2 13 .820 21	3000 207	3/8	1/2	1
High Pressure Grease Reels Maximum Temperature 210 °F (99 °C)						
5400 OHP	23 10	1/4 6 .580 15	5000 345	1/4	1/4	1

Dimensions					
	1	2	3		
	in	mm	in	mm	in
A	14 ³ / ₈	365	17 ⁵ / ₈	448	17 ⁵ / ₈
B	13 ³ / ₄	349	16 ³ / ₄	425	16 ³ / ₄
C	9 ³ / ₄	248	9 ³ / ₄	248	9 ³ / ₄
D	2 ¹ / ₂	64	2 ¹ / ₂	64	2 ¹ / ₂
E	6 ¹ / ₈	156	5 ⁷ / ₈	149	7 ¹ / ₄



Series 5000/5005 and A5000/A5005 reels include a speed latch mechanism that uses a cam and disc for quiet operation.

Series B5000/B5005 reels includes a ratchet latch mechanism that produces a distinct "clicking" noise while in use.

See operating instructions for optimum mounting configuration.



Interactive Reel Catalog

Visit reelcraft.com/catalog for complete product specifications, available parts, and accessories.



Pivot Bases & Swing Brackets

See page 43