



# K3A2U2, AL Universal Terminal, 3-Conductor, 2-Hole

By Burndy  
Catalog # [K3A2U2](#)

3-Conductor, 2-Hole, 5/16" Stud, .88" Spacing, #14-2 AWG, Tin Plated, Dual Rated

## Features

- Dual rated lugs
- Constructed from high strength aluminum alloy
- Electro tin plating proving low contact resistance

## Application

For Aluminum and Copper Conductors

## Specifications

|                                         |                                                                                                                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Buy American Compliant                  | Yes                                                                                                                                                                               |
| EU RoHS Indicator                       | Yes                                                                                                                                                                               |
| Buy America(n) Qualified                | <ul style="list-style-type: none"><li>• Buy American Act Compliant (All status valid till December 2026)</li><li>• BABA Compliant (All status valid till December 2026)</li></ul> |
| Industry Standard(s)                    | UL 486A-486B                                                                                                                                                                      |
| Standards - Industry Standards Met      | UL 486A-486B                                                                                                                                                                      |
| Standards - RoHS Compliance Status      | EX                                                                                                                                                                                |
| Certification - UL Listed Direct Burial | No                                                                                                                                                                                |
| UL Listed                               | Yes                                                                                                                                                                               |
| Certification - CSA Approved            | Yes                                                                                                                                                                               |

## Conductor

|                               |                                                                                                                                                                                                                            |
|-------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size       | <ul style="list-style-type: none"><li>• 8 AWG</li><li>• 6 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li></ul>                                                                                                    |
| Conductor - AL Str Size Range | 14-2 AWG                                                                                                                                                                                                                   |
| Conductor - Copper Str Size   | <ul style="list-style-type: none"><li>• 14 AWG</li><li>• 12 AWG</li><li>• 10 AWG</li><li>• 9 AWG</li><li>• 8 AWG</li><li>• 7 AWG</li><li>• 6 AWG</li><li>• 5 AWG</li><li>• 4 AWG</li><li>• 3 AWG</li><li>• 2 AWG</li></ul> |
| Conductor Size                | 14-2 AWG                                                                                                                                                                                                                   |



|                                   |                                                                                         |
|-----------------------------------|-----------------------------------------------------------------------------------------|
| Number Of Conductors              | 3                                                                                       |
| Conductor Type                    | <ul style="list-style-type: none"><li>• AL C Str-Size</li><li>• CU C Str-Size</li></ul> |
| Conductor - Copper Str Size Range | 14-2 AWG                                                                                |

## Configuration

|                                       |                    |
|---------------------------------------|--------------------|
| Physical Attribute - Number of Screws | 3                  |
| Physical Attribute - Number of Holes  | 2                  |
| Connector Type                        | Parallel Set-Screw |

## Dimensions

|                                 |             |
|---------------------------------|-------------|
| Dimension - Pad Width inch      | 1.64 in     |
| Package Height                  | 3.300 in    |
| Dimension - Height mm           | 15.7 mm     |
| Dimension - Hole Size fraction  | 11/32       |
| Dimension - Height inch         | 0.62 in     |
| Dimension - Height fraction     | 5/8 in      |
| Package Weight                  | 0.670 lb.   |
| Package Length                  | 3.800 in    |
| Package Width                   | 3.400 in    |
| Dimension - L Length Overall mm | 55.62 mm    |
| Dimension - Width fraction      | 1-59/100 in |
| Dimension - Hole Size mm        | 9 mm        |
| Dimension - Hole Size inch      | 0.34 in     |
| Dimension - Stud Size inch      | 5/16 in     |
| Dimension - Bolt Hole Size inch | 0.57 in     |
| Dimension - Bolt Size fraction  | 5/16        |
| Dimension - Width mm            | 40 mm       |
| Dimension - Width inch          | 1.64 in     |
| Dimension - D inch              | 1.63 in     |
| Dimension - N inch              | 0.34 in     |
| Dimension - Length Overall inch | 2.19 in     |

## Force Related

|                                       |           |
|---------------------------------------|-----------|
| Installation Torque Recommended in-lb | 50 LBS/in |
|---------------------------------------|-----------|

## General

|                                 |          |
|---------------------------------|----------|
| Material - Hardware             | Aluminum |
| Physical Attribute - Screw Type | Slot     |

|                   |                         |
|-------------------|-------------------------|
| Plated            | Y                       |
| Sub Brand         | UNIVERSAL TERM          |
| UPC               | 781810370360            |
| Type              | Bolted Lugs & Terminals |
| Material          | Aluminum                |
| Plating Type      | Tin plated              |
| UPC 12 Digit      | 781810370360            |
| UPC 14 Digit GTIN | 00781810370360          |

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 3240 |
| Carton Quantity       | 216  |

Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

Product Assets

Logistics

[Catalog \[English\]](#)



A Hubbell brand