ABB BALDOR RELIANCE

Customer information packet

EJPM4108T

30HP, 3525RPM, 3PH, 60HZ, 286JP, 1048M, TEFC, F
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 12:54:14 PM

Specifications

Enclosure	TEFC
Frame	286JP
Frame Material	Iron
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Three Phase
Output @ Frequency	30.000 HP @ 60 HZ
Phase	3
Synchronous Speed @ Frequency	3600 RPM @ 60 HZ
Voltage @ Frequency	460.0 V @ 60 HZ
	230.0 V @ 60 HZ
Agency Approvals	CSA
	CSA EEV
	NEMA PREMIUM
	UR
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	34.000 A @ 460.0 V
	68.000 A @ 230.0 V
Design Code	B
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	91.7 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Face Code	Standard
Front Shaft Indicator	None

Part Detail

Revision	L
Type	AC
Mech. spec.	10E381
Base	
Status	PRD/A
Elec. spec.	10WGZ501
Layout	10LYE381
Eff. date	06-27-2024
CD Diagram	CD0180
Poles	02
Leads	9#10
Proprietary	False
Created date	08-31-2017

Heater Indicator	No Heater
High Voltage Full Load Amps	34.0 a
Insulation Class	F
Inverter Code	Inverter Duty
KVA Code	G
Lifting Lugs	Standard Lifting Lugs
Locked Bearing Indicator	Locked Bearing
Motor Lead Exit	Ko Box
Motor Lead Quantity/Wire Size	9 @ 10 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	1048M
Mounting Arrangement	F1
Number of Poles	2
Overall Length	31.51 IN
Power Factor	90
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	C-Face
Pulley Shaft Indicator	Pump Coupling Shaft
Rodent Screen	None
Service Factor	1.15
Shaft Diameter	1.250 IN
Shaft Extension Location	Pulley End
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	Shaft Slinger
Speed	3525 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None

Winding Thermal 2	None

Nameplate

NP3443LUA												
CAT.NO.	EJPM4108T			**CUST. P/N**						**ENCL**	TEFC	
SPEC.	10E381Z501G1	**CC**	010A	**FRAME**	286JP		**SER.NO.**					
HP	30		**CLASS**	F	**HZ**	60						
R.P.M.	3525		**PH.**	3	**DES.**	B						
VOLTS	230/460			**CODE**	G		**ODE BRG**	6309	**DE BRG**	6312		
AMPS	68/34											
RATING	40C AMB-CONT			**NEMA NOM. EFF.**	91.7			**GREASE**	POLYREX EM			
P.F.	90	**SER.F.**	1.15	**CT6-60H(10:1)VT3-60H(20:1**								
USABLE AT	50HZ 30HP 190/380V 82/41A			SF1.0								
VOLTS	**AMPS**		**MAX. SPACE HEATER TEMP.**									

AC Induction Motor Performance Data
Record # 55452
Typical performance - not guaranteed values

Winding: 10WGZ501-R001	**Type:** 1048M	**Enclosure:** TEFC

Nameplate Data				**460 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			30	**Full Load Torque**	44.8 LB-FT
Volts			230/460	**Start Configuration**	direct on line
Full Load Amps			68/34	**Breakdown Torque**	135 LB-FT
R.P.M.			3520	**Pull-up Torque**	47 LB-FT
Hz	60	**Phase**	3	**Locked-rotor Torque**	65.2 LB-FT
NEMA Design Code	B	**KVA Code**	G	**Starting Current**	212 A
Service Factor (S.F.)			1.15	**No-load Current**	8.74 A
NEMA Nom. Eff.	91.7	**Power Factor**	90	**Line-line Res. @ 25ºC**	0.24052 Ω
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	69°C
S.F. Amps				**Temp. Rise @ S.F. Load**	85°C
				Locked-rotor Power Factor	23.2

Load Characteristics 460 V, 60 Hz, 30 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	67	83	88	90	90	90	90
Efficiency	87	91.3	92	91.7	90.9	89.7	91.2
Speed	3583	3565.7	3547.3	3526.7	3504.4	3479.1	3513
Line amperes	12.4	18.7	26.1	34.1	43.1	52.5	39.5


ABB Motors and Mechanical Inc.


WINDING # 10WGZ501

30 HP 3 PH 60 HZ 3520 RPM 460 V 1048M


Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=135 PU=47 LR=65.2 LRA=212





10LYE381
(1028-1062) = 31.56
8.125±.031
12.93
5.875±.020
CHECK W/GAUGE T-9042
2.375±.020
.25
GREASER & RELIEF (EA. END)
.250 KEYWAY
2.62 LONG
2.50 LONG KEY
Ø 12.502
12.499
13.08
Ø 1.3750
1.3745
Ø 1.750
1.748
SLINGER
8 HOLES Ø .53
9.50
9.50
.92
11.00
4.75
12.84
AUTO DRAIN (EA. END)
.50-13 TAP
CL 3B
1.25 DEEP
15.50
13.12
7.59
45°
45°
3.20
4 HOLES
.63-11 TAP
1.12 DEEP
Ø 11.00 B.C.
14.44
7.00 +.00 -.06
3.25
LEAD HOLE Ø 2.00
5.50
5.50
10.57
6.38
12.75
R .054 .043
1.2495
1.2490
1.750
1.748
1.3750
1.3745
.03 X 45° CHAMFER
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION
REV. DESC: UPDATE NP GRAPHICS TO MATCH NP USED ON CAT SPECS
REV: J
VERSION: 07
REVISED: 08:54:13 07/20/2022
TDR: 000001193922
MODEL NO. 10LYE381
REF: -
BY: USBUFRA
B
BALDOR
HOR TEFC 284-6JP
10LYE381

CD0180







NOTES:

1. INTERCHANGE ANY TWO LINE LEADS TO REVERSE ROTATION.
2. OPTIONAL THERMOSTATS ARE PROVIDED WHEN SPECIFIED.
3. ACTUAL NUMBER OF INTERNAL PARALLEL CIRCUITS MAY BE A MULTIPLE OF THOSE SHOWN ABOVE.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0180

REV. DESC: ADD CLASS CONN00000007		
REV. LTR: D	VERSION: 01	TDR: 000001099922
FILE: \AAA\00005\148	REVISED: 10:25:29 02/19/2019	BY: ENBRIR0
MTL: –		

BALDOR - RELIANCE®

3PH, DV, 9 LEADS, DELTA CONNECTION

SH 1 of 1