



bdw™- Body Wash Safety Data Sheet

SDS No.: SHG202401 0401
Issue Date: May dth, 2024
Revision Date: N/A
Version No.: 1.0

According to US HazCom 2012

Section 1 Identification of the substance/mixture and of the company/undertaking

1. Product identifier:

Identification on the label/Trade Name: Body Wash

Additional identification: Not available

2. Relevant identified uses of the substance and uses advised against:

Relevant Identified uses: Clean skin

Uses advised against: Not Applicable

1.3 Details of the supplier of the safety data sheet:

Supplier: World Amenities, Inc

Address: 8260 Camino Santa Fe, San Diego, CA 92121

Telephone: 1-800-783-9969

Fax: info@worldamenities.com

Email:

1.4 Emergency telephone Number:

Association/Organization: World Amenities, Inc

Emergency Tel No.: 1-800-783-9969

Section 2 Hazards Identification

2.1 Classification of the substance/mixture:

Considered NOT a Hazardous mixture according to GHS US HazCom 2012.

Classified NOT as Dangerous Goods for transport purposes.

2.2 Label element:

Hazard Pictograms: Not Applicable

Signal Words: Not Applicable

Hazard Statements: Not Applicable

Supplementary statement: Not Applicable

Precautionary statements Prevention: Not Applicable

Precautionary statements Response: Not Applicable

Precautionary statements Storage: Not Applicable

Precautionary statements Disposal: Not Applicable

2.3 Other hazards:

Not Applicable

Section 3 Composition/information on ingredients

Product Name: Body Wash
Version #: 1.0

Revision date: N/A

MSDS US
1 / 7

1. Substance/Mixture:

See "Composition on ingredients" in Section 3.2

2. Mixtures of Ingredient(s):

No.	INCI Nome	CASNo.	%	Function
1	Aqua (Water)	7732-18-9	To 100	Solvent
2	Sodium Laureth Sulfate	68581-34-2	12.00	Surfactant
3	Cocamide MEA	68140-00-1	4.00	Surfactant & Thickener & Foam Stabilizer
4	Cocamidopropyl Betaine	61789-40-0	2.00	Surfactant
5	Sodium Lauroyl Sarcosinate	13716-6	1.00	Surfactant
6	Sodium Chloride	7647-14-5	1.00	Viscosity Controlling
7	Citric Acid	5949-29-1	0.30	Buffering
8	Fragrance	N/A	0.30	Perfuming
9	Diazolidinyl Urea	78491-02-8	0.20	Preservative
10	Methylchloroisothiazolinone	21122-514	0.0005d25	Preservative
11	Methylisothiazolinone	2482-20-4	0.0001875	Preservative

Allergens: Hexamethylindanopyran, Tetramethyl Acetyltetrahydronaphthalenes, Linalyl Acetate, Linalool

Section 4 First aid measures

4.1 Description of first aid measures:

Inhalation: If fumes, aerosols or combustion products are inhaled, removed from contaminated area.
Other measures are usually unnecessary.

Skin contact: If skin or hair contact occurs, flush skin and hair with running water (and soap if available).
Seek medical attention in event of irritation.

Eyes contact: If this product comes in contact with eyes, wash out immediately with water.
If irritation continues, seek medical attention.
Removal of contact lenses after eye injury should only be undertaken by skilled personnel.

Ingestion: Immediately give a glass of water. First aid is not generally required.
If in doubt, contact a poisons information center or a doctor.

4.2 Most important symptoms and effects, both acute and delayed:

See Section 1.1

4.3 Indication of any immediate medical attention and special treatment needed:

Treat symptomatically

Section 5 Fire-Fighting measures

5.1 Extinguishing media: There is no restriction on the type of extinguisher which may be used.
Use extinguisher media suitable for surrounding area.

5.2 Special hazards arising from the substance or mixture Fire Fighting: None known.

5.3 Advice for fire-fighters: Fire-fighters: Alert fire brigade and tell them location and nature of hazard.
Wear breathing apparatus plus protective gloves in the event of a fire.
Fire/Explosion Hazard: Noncombustible. Not considered a significant, however containers may burn.

Section 6 Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures:

See Section 8

6.2 Environmental Precautions:

See Section 12

6.3 Methods and material for Confinement and Cleaning up:

Minor spills: Clean up all spills immediately. Avoid breathing vapours and contact with skin and eyes.

Major spills: Clear area of personnel and move upwind.

4. Reference to other sections:

Personal Protection Equipment advice is contained in Section 8 of the SDS.

5. Additional information:

Not applicable.

Section 7 Handling and storage

7.1 Precautions for safe handling:

7.11 Safe Handling:

Limit all unnecessary personal contact. Wear protective clothing when risk of exposure occurs.

12. Fire and explosion protection:

See Section 5.

13. Other information:

Store in original containers. Keep the containers sealed.

7.2 Conditions for safe storage, including any incompatibilities

21. Suitable container:

Tube, bottle or sachet

22. Storage Incompatibility:

None known

7.3 Specific end uses

See Section 1.2

Section 8 Exposure Controls/Personal Protection

8.1 Control parameters:

DERIVED NO EFFECT LEVEL(DNEL):

Not Available

PREDICTED NO EFFECT LEVEL(PNEC):

Not Available

OCCUPATIONAL EXPOSURE LIMITS(OEL):

Not Available

INGREDIENT DATA


Source	Ingredient	Material Name	TWA	STEL	PEAK	NOTES
Not Available	Not Available	Not Available	Not Available	Not Available	Not Available	Not Available

2. Exposure controls:

1. Appropriate engineering controls:

Engineering controls are used to remove a hazard or place a barrier between the worker and the hazard. Well-designed engineering controls can be highly effective in protecting workers and will typically be independent of worker interactions to provide this level of protection.

8.2.2 Individual protection measures, such as personal protective equipment:



Eye/face protection:

Safety glasses with side shields; chemical goggles.

Hands/feet protection:

Wear chemical protective gloves, e.g. PVC. Wear safety footwear or safety gumboots, e.g. Rubber.

NOTE: The material may product skin sensitization in predisposed individuals. Care must be taken, when removing gloves and protective equipment, to avoid all possible skin contact.

Body protection:

See other protection below

Other protection:

Overalls. P.V.C.

8.2.3 Environmental exposure controls:

See Section 12.

Section 9 Physical and chemical properties

9.1 Information on basic physical and chemical properties:

Appearance:	Liquid
Physical state:	Liquid
Odor:	Pleasant smell
Odor threshold:	Not applicable
PH(20V):	4.0 —7.0
Melting point/range (°C):	Not available
Freezing point/range (°C):	Not available
Boiling point/range (°C):	Not available
Flash point (°C):	Not applicable
Evaporation rate:	Not available
Flammability:	Not flammable
Upper/lower/explosive limits:	Not available
Vapor pressure (kPa):	Not available
Vapor density(Air=1):	Not available
Water solubility (g/l):	Not available
Relative Density(Water=1):	Not available
Partition coefficient n-octanol/water:	Not available
Auto-ignition temperature:	Not available
Decomposition temperature:	Not available
Viscosity (mPa.s):	4000 - 6000
Explosive properties:	Not available
Molecular Weight(g/mol):	Not available
Taste:	Not applicable
Explosive properties:	Not available
Oxidizing properties:	Not available
Surface Tension(Dyn/cm or mN/m):	Not available
Volatile Component(% vol):	Not available
Gas group:	Not available
PH as a solution(1%):	Not applicable
VOC g/l:	Not applicable

9.2. Other information:

Not available

Section 10 Stability and reactivity

- | | |
|--|--|
| 1. Reactivity: | Product is non-reactive under normal conditions of use, storage and transport. |
| 2. Chemical stability: | Product is considered stable and hazardous polymerization will not occur. |
| 3. Possibility of hazardous reactions: | No dangerous reactions known under normal conditions of use. |
| 4. Conditions to avoid: | None |
| 5. Incompatible materials: | No additional information available. |
| 6. Hazardous decomposition products: | See section 5.3 |

Section 11 Toxicological information

11.1 Information on toxicological effects

Acute toxicity:

Sodium Laureth Sulfate (CAS No.: 68585-34-2):

Oral (rat) LD50:	4000 mg/kg ***
Dermal (rat) LD50:	2000 mg/kg "

Cocamide Methyl MEA (CAS No.: 666889-75-0):

Oral (rat) LD50:	2700 mg/kg ***
------------------	----------------

Cocamidopropyl Betaine (CAS No.: 61789-40-0):

Oral (rat) LD50:	2700 mg/kg "
Oral (rat) LD50:	4900 mg/kg "

Sodium Chloride (CAS No.: 7647-14-5):

Oral (rat) LD50:	3000 mg/kg ***
------------------	----------------

Citric Acid (CAS No.: 5949-29-1):

Oral (mouse) LD50:	5790 mg/kg ***
Dermal (rat) LD50:	2000 mg/kg "

Sodium Lauroyl Sarcosinate (CAS No.: 137-16-6):

Oral (rat) LD50:	5000 mg/kg "
------------------	--------------

Methylchloroisothiazolinone&Methylisothiazolinone(CAS No. 26172-55-4& 2682-20-4)

Oral (rat) LD50:	4400 mg/kg ***
Dermal (rabbit) LD50:	5000 mg/kg ***

Diozolidinyl Urea (CAS No. 78491-02-8):

Oral (rat) LD50:	2250 mg/kg "
Dermal (rabbit) LD50:	2000 mg/kg "

Serious eye damage/irritation: No serious eye damage.

Respiratory or skin sensitization: May cause an allergic skin reaction.

Germ cell mutagenicity: No data available.

Carcinogenicity: Not Applicable

Reproductive toxicity: No data available.

STOT- single exposure: No data available.

STOT-repeated exposure: No data available.

Aspiration hazard: No data available.

Legend:

1. Value obtained from Europe ECHA and US CIR —Acute toxicity.

2. Value obtained from the SDS from raw material suppliers. Unless otherwise specified do to extracted from RTECH — Register of Toxic Effects of chemical substance.

Section 12 Ecological information

12.1 Toxicity:

Body Wash:

No data available for the mixture.

12.2 Persistence and degradability:

Ingredient	Persistence: Water/Soil	Persistence: Air	Biodegradation: Water/Soil
Sodium Laureth Sulfate	LOW	LOW	Readily biodegradable (100%) in Water
Cocamidopropyl Betaine	LOW	LOW	Half-life in freshwater: 15 days @ 25 °C Half-life in soil: 30 days @ 25 °C
Sodium chloride	LOW	LOW	/
Citric Acid	LOW	LOW	Readily biodegradable (100%) in Water
Sodium Lauryl Sarcosinate	LOW	LOW	Readily biodegradable (100%) in Water

12.3 Bio-accumulative potential

Ingredient	Bioaccumulation
Sodium chloride	Low (LogKOW = -0.408)

12.4 Mobility in soil

Ingredient	Bioaccumulation
Sodium chloride	Low KOC = 14.3

12.5 Results of PBT and vPvB assessment

	P	B	T
Relevant available data	Not Applicable	Not Applicable	Not Applicable
PBT Criteria fulfilled	Not Applicable	Not Applicable	Not Applicable

12.6 Other adverse effects

No data available

Section 13 Disposal considerations

13.1 Waste treatment methods:

Dispose of contents/container in accordance with licensed collector's sorting instructions

Section 14 Transport information

In accordance with DOT/IMDG/IATA

DOT	IMDG	IATA
14.1 UN No.		
Not Regulated	Not Regulated	Not Regulated
14.2 Proper Ship Name		
Not Applicable	Not Applicable	Not Applicable
14.3 Transport Hazard Class(es)		
Not Applicable	Not Applicable	Not Applicable
14.4 Packing Group		

Not Applicable	Not Applicable	Not Applicable
14.5 Environmental Hazards		
Not Applicable	Not Applicable	Not Applicable
No supplementary information available		

14.6 Special precautions for users

Not regulated for DOT/IMDG/IATA

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not Applicable

The product is not classified as dangerous and is safe for all the means of transportation based on the Certification for Safe Transport of Chemical Goods by Shanghai Institute of Chemical Industry Testing Co., Ltd.

Section 15 Regulation information

1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory.

This product or mixture is not known to contain a toxic chemical or chemicals in excess of the applicable de minimis concentration as specified in 40CFR 5372.38(a) subject to the reporting requirements of section 313 of Title II of the Superfund Amendments and Reauthorization Act of 1980 and 40CFR Part 372.

2. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm.

Section 16 Other information

The health and safety information contained in this MSDS is believed to be true and correct. However, because World Amenities, Inc. has no control over the method of use of this product, all statements or suggestions are made without warranty, expressed or implied, regarding the reliability of the information, or the hazards resulting from the use of the material. Every user should consider the information given in this MSDS in the context of how this product will be used in the user's workplace, including the effects of other products on the premises.