ABB BALDOR RELIANCE

Customer information packet

L3514T

1.5HP, 1725RPM, 1PH, 60HZ, 145T, 3532LC, TEFC
Class - None
Division - Not Applicable

Copyright © All product information within this document is subject to ABB Motors and Mechanical Inc. copyright © protection, unless otherwise noted.
11/5/2026 5:24:37 PM

Specifications

Enclosure	TEFC
Frame	145T
Frame Material	Steel
Frequency	60.00 Hz
Haz Area Class and Group	None
Haz Area Division	Not Applicable
Motor Letter Type	Cap Start, Cap Run
Output @ Frequency	1.500 HP @ 60 HZ
Phase	1
Synchronous Speed @ Frequency	1800 RPM @ 60 HZ
Voltage @ Frequency	230.0 V @ 60 HZ
	208.0 V @ 60 HZ
	115.0 V @ 60 HZ
Agency Approvals	C UR US
Ambient Temperature	40 °C
Auxiliary Box	NO AUXILLARY BOX
Auxiliary Box Lead Termination	None
Base Indicator	Rigid
Bearing Grease Type	Polyrex EM (-20F +300F)
Blower	None
Current @ Voltage	6.900 A @ 208.0 V
	6.100 A @ 230.0 V
	12.200 A @ 115.0 V
Design Code	L
Drip Cover	No Drip Cover
Duty Rating	CONT
Efficiency @ 100% Load	80.0 %
Electrically Isolated Bearing	Not Electrically Isolated
Feedback Device	NO FEEDBACK
Front Shaft Indicator	None
Heater Indicator	No Heater
High Voltage Full Load Amps	6.1 a

Part Detail

Revision	M
Type	AC
Mech. spec.	35EE001
Base	
Status	PRD/A
Elec. spec.	35WGG242
Layout	35LYEE001
Eff. date	11-13-2025
CD Diagram	CD0055
Poles	04
Leads	6#18
Proprietary	False
Created date	09-18-2020

Insulation Class	F
Inverter Code	Not Inverter
KVA Code	H
Lifting Lugs	No Lifting Lugs
Locked Bearing Indicator	No Locked Bearing
Motor Lead Quantity/Wire Size	6 @ 18 AWG
Motor Lead Termination	Flying Leads
Motor Standards	NEMA
Motor Type	3532LC
Mounting Arrangement	F1
Number of Poles	4
Overall Length	14.16 IN
Power Factor	98
Product Family	General Purpose
Pulley End Bearing Type	Ball
Pulley Face Code	Standard
Pulley Shaft Indicator	Standard
Rodent Screen	None
RoHS Status	ROHS COMPLIANT
Service Factor	1.15
Shaft Diameter	0.875 IN
Shaft Ground Indicator	No Shaft Grounding
Shaft Rotation	Reversible
Shaft Slinger Indicator	No Slinger
Speed	1725 rpm
Speed Code	Single Speed
Starting Method	Direct on line
Thermal Device - Bearing	None
Thermal Device - Winding	None
Vibration Sensor Indicator	No Vibration Sensor
Winding Thermal 1	None
Winding Thermal 2	None

Nameplate

NP2116L											
CAT.NO.	L3514T										
SPEC.	35EE001G242G1										
HP	1.5										
VOLTS	115/208-230										
AMP	12.2/6.9-6.1										
RPM	1725										
FRAME	145T		**HZ**	60		**PH**	1				
SER.F.	1.15	**CODE**	H	**DES**	L	**CL**	F				
NEMA-NOM-EFF	80	**PF**	98								
RATING	40C AMB-CONT										
CC	010A										
DE	6205	**ODE**	6203								
ENCL	TEFC	**SN**									
	SFA 17.8/10.4-8.9										

Accessories

Part number	Description	Multiplier
35-8762	C FACE KIT	A8
35EP1506A01SP	D-FLANGE KIT	A8

AC Induction Motor Performance Data
Record # 88493
Typical performance - not guaranteed values

Winding: 35WGG242-R002	**Type:** 3532LC	**Enclosure:** TEFC

Nameplate Data				**230 V, 60 Hz: High Voltage Connection**	
Rated Output (HP)			1.5	**Full Load Torque**	4.566 LB-FT
Volts			115/208-230	**Start Configuration**	direct on line
Full Load Amps			12.2/6.9-6.1	**Breakdown Torque**	9.93 LB-FT
R.P.M.			1725	**Pull-up Torque**	8.07 LB-FT
Hz	60	**Phase**	1	**Locked-rotor Torque**	13 LB-FT
NEMA Design Code	L	**KVA Code**	H	**Starting Current**	44 A
Service Factor (S.F.)			1.15	**No-load Current**	0.84 A
NEMA Nom. Eff.	80	**Power Factor**	98	**Line-line Res. @ 25ºC**	2.1263 Ω A Ph 1.3142 Ω B Ph
Rating - Duty			40C AMB-CONT	**Temp. Rise @ Rated Load**	61°C
S.F. Amps				**Temp. Rise @ S.F. Load**	84°C

Load Characteristics 230 V, 60 Hz, 1.5 HP

% of Rated Load	**25**	**50**	**75**	**100**	**125**	**150**	**S.F.**
Power Factor	94	98	98	98	97	96	97
Efficiency	71.4	77.6	81.3	82.3	77.7	70.5	79.5
Speed	1782.1	1765.3	1746.2	1722.8	1689.8	1641.6	1703
Line amperes	1.77	3.01	4.42	6.1	8.04	10.7	7.24


ABB Motors and Mechanical Inc.

WINDING # 35WGG242


1.5 HP 1 PH 60 HZ 1725 RPM 230 V 3532LC

Typical performance - not guaranteed values.


TORQUES(LB-FT): PO=9.93 PU=8.07 LR=13 LRA=44



11/5/2026 ACPERF, record # 88493


35LYEE001
510-528 = 13.29
529-535 = 14.16
536-546 = 15.53
GREASE FITTINGS
EACH END
2.88
5.31
2.50
2.25
.19 KEY
1.38 LG
Ø7.19
NAMEPLATE
Ø .8750
Ø .8745
3.76
4.00
2.25
6 HOLES
.34 DIA.
5.00
.50
5.94
6.61
5.75
2.27
6.77
3.47
3.41
LEAD HOLE
1.09 DIA
2.75
2.75
4.63
3.25
6.50
CUSTOMER IS RESPONSIBLE FOR DETERMINING THAT BALDOR'S PRODUCT WILL PERFORM SUITABLY IN THE INTENDED APPLICATION.
REV. DESC: UPDATE 3D MODEL BOM PER REV C, NO CHG TO 2D PRINT
REV: C
VERSION: 03
REVISED: 08:30:07 03/09/2022
TDR: 000001187335
MODEL NO. 35LYEE001
REF: -
BY: USBUFRA
Material: -
B
BALDOR - RELIANCE®
STD HORZ 143-5T TEFC 35LC W/1.09 DIA. LEAD HOLE
SH 1 of 1
35LYEE001

CD0055



	LINE A	LINE B	JOIN
HIGH STD	1	4,5	2,3,8
HIGH OPP	1	4,8	2,3,5
LOW STD	1,3,8	2,4,5	–
LOW OPP	1,3,5	2,4,8	–

NOTES:

1. STANDARD ROTATION IS CCW FACING END OPPOSITE SHAFT EXTENSION.
2. OPTIONAL THERMOSTAT IS PROVIDED WHEN SPECIFIED.
3. MULTIPLE CAPACITORS ARE CONNECTED IN PARALLEL UNLESS OTHERWISE SPECIFIED.
4. LEAD COLORS ARE OPTIONAL. LEADS MUST ALWAYS BE NUMBERED AS SHOWN.

CD0055

REV. DESC: REVISE TO SHOW OPTIONAL COLORS			BALDOR ELECTRIC Co.
REV. LTR: D	BY: JLP	REVISED: 04/08/99 1:17	TDR: 0178636
CD0055		FILE: AAA00007414	MDL: –
		MTL: –	TYPE LC, DV, REV, 6 LEADS