



LSL™

LED Flood Light



SKU	Model #
151350	BLT-FL02-SQ03
151331	BLT-FL07-01
151333	BLT-FL07-01

SKU	Model #
151351	BLT-FL02-SQ03
151332	BLT-FL07-01

Our New 2021 LSL Flood lights are the best solutions for landscaping, signage, and accent lighting in heavy commercial and residential applications. Our 100W LSL Flood Light is a power-packed, narrow-beam spotlight that produces high lumens to illuminate objects up to 98 feet away and our 36W up to 49ft. Its great for lighting flags, monuments, steeples, and bridges.

Product Features

- RGB lights - High Lm 3-in-1 Osram LED Chips
- Single color lights - High Lm Bridgelux LED Chips
- RGB models are controlled by an APP to generate maximum colors
- High lumens per watt
- Die-Cast aluminum housing
- Installation Method Wall/Ceiling/Ground
- Heat resistant polycarbonate optical lens
- IP65 rating and many beam angles
- Optional DMX512 Controller
- LSL RGB Controller with APP is Included
- Input Voltage 100-277Vac
- ETL Listed



SKU	WATT	MAX LUMENS	CCT	INPUT VOLTAGE	LIGHT SPREAD	CONSTRUCTION	IP RATING	CERTIFICATIONS
151350	36W	3200	3000K	100-277V	8°	Die-Cast Aluminum	IP65	ETL
151351	36W	-	Green	100-277V	8°	Die-Cast Aluminum	IP65	ETL
151331	100W	9000	3000K	100-277V	30°	Die-Cast Aluminum	IP65	ETL
151332	100W	-	Blue	100-277V	30°	Die-Cast Aluminum	IP65	ETL
151333	100W	-	Blue	100-277V	30°	Die-Cast Aluminum	IP65	ETL

1 Color Lights

Grey Fixture Housing

8° / 30°
Beam Angle

36W
3000K / Green



100W
3000K / Blue



3000K Green Blue



3000K Green Blue





LSL™

LED Flood Light

SKU: 151350

Specifications

Parameter	Description	Value
General Performance	Model #.	BLT-FL02-SQ03
	Watt	36W
	Max Lumens	3200
	Lumen Efficacy	Up to 88LM/W
	Color Temperature	3000K
	CRI (Ra)	N/A
	Light Spread	8°
	Diffuser Type	N/A
Electrical	Input Voltage	100-277Vac
	Frequency	N/A
	Dimming	N/A
	Power Factor	>0.9
	Driver Efficiency	90%
	Flicker Percent	N/A
Physical	Operating Temperature	-40°C to 50°C
	Storage Temperature	-40°C to 70°C
	Power Supply	Done UL Listed Driver for one color/ WN driver for RGB color
	LED Brand	Bridgelux
	Control Way	on off one color/DMX512 for RGB color
	LED QTY	60 Pcs
	Construction	Die-Cast Aluminum
Qualification	Housing Color	grey
	IP Rating	IP65
	Warranty	5 Years

LSL™

LED Flood Light



SKU: 151351

Specifications

Parameter	Description	Value
General Performance	Model #.	BLT-FL02-SQ03
	Watt	36W
	Max Lumens	N/A
	Lumen Efficacy	High lumens per watt
	Color Temperature	Green
	CRI (Ra)	N/A
	Light Spread	8°
	Diffuser Type	N/A
Electrical	Input Voltage	100-277Vac
	Frequency	N/A
	Dimming	N/A
	Power Factor	>0.9
	Driver Efficiency	90%
	Flicker Percent	N/A
Physical	Operating Temperature	-40°C to 50°C
	Storage Temperature	-40°C to 70°C
	Power Supply	Done UL Listed Driver for one color/ WN driver for RGB color
	LED Brand	Bridgelux
	Control Way	on off one color/DMX512 for RGB color
	LED QTY	60 Pcs
	Construction	Die-Cast Aluminum
Qualification	Housing Color	grey
	IP Rating	IP65
	Warranty	5 Years

LED FLOOD LIGHT



LSL™

LED Flood Light

SKU: 151331

Specifications

Parameter	Description	Value
General Performance	Model #.	BLT-FL02-SQ03
	Watt	100W
	Max Lumens	9000
	Lumen Efficacy	Up to 90LM/W
	Color Temperature	3000K
	CRI (Ra)	N/A
	Light Spread	30°
	Diffuser Type	N/A
Electrical	Input Voltage	100-277Vac
	Frequency	N/A
	Dimming	N/A
	Power Factor	>0.9
	Driver Efficiency	90%
	Flicker Percent	N/A
Physical	Operating Temperature	-40°C to 50°C
	Storage Temperature	-40°C to 70°C
	Power Supply	Done UL Listed Driver for one color/ WN driver for RGB color
	LED Brand	Bridgelux
	Control Way	on off one color/DMX512 for RGB color
	LED QTY	60 Pcs
	Construction	Die-Cast Aluminum
Qualification	Housing Color	grey
	IP Rating	IP65
	Warranty	5 Years

LSL™

LED Flood Light



SKU: 151332

Specifications

Parameter	Description	Value
General Performance	Model #.	BLT-FL07-01
	Watt	100W
	Max Lumens	N/A
	Lumen Efficacy	High lumens per watt
	Color Temperature	Blue
	CRI (Ra)	N/A
	Light Spread	30°
	Diffuser Type	N/A
Electrical	Input Voltage	100-277Vac
	Frequency	N/A
	Dimming	N/A
	Power Factor	>0.9
	Driver Efficiency	90%
	Flicker Percent	N/A
Physical	Operating Temperature	-40°C to 50°C
	Storage Temperature	-40°C to 70°C
	Power Supply	Done UL Listed Driver for one color/ WN driver for RGB color
	LED Brand	Bridgelux
	Control Way	on off one color/DMX512 for RGB color
	LED QTY	60 Pcs
	Construction	Die-Cast Aluminum
Qualification	Housing Color	grey
	IP Rating	IP65
	Warranty	5 Years

LED FLOOD LIGHT



LSL™

LED Flood Light

SKU: 151333

Specifications



Parameter	Description	Value
General Performance	Model #.	BLT-FL07-01
	Watt	100W
	Max Lumens	N/A
	Lumen Efficacy	High lumens per watt
	Color Temperature	Blue
	CRI (Ra)	N/A
	Light Spread	30°
	Diffuser Type	N/A
Electrical	Input Voltage	100-277Vac
	Frequency	N/A
	Dimming	N/A
	Power Factor	>0.9
	Driver Efficiency	90%
	Flicker Percent	N/A
Physical	Operating Temperature	-40°C to 50°C
	Storage Temperature	-40°C to 70°C
	Power Supply	Done UL Listed Driver for one color/ WN driver for RGB color
	LED Brand	Bridgelux
	Control Way	on off one color/DMX512 for RGB color
	LED QTY	60 Pcs
	Construction	Die-Cast Aluminum
Qualification	Housing Color	grey
	IP Rating	IP65
	Warranty	5 Years

LSL™

LED Flood Light



Dimensions







LSL™ LED Flood Light

Dimensions

Single Color Wiring Diagram



RGB Color Wiring Diagram





SKU: 151350

Distribution Diagram

LUMINAIRE PHOTOMETRIC TEST REPORT



Luminaire Property

Manufacturer:

Luminaire Type: WN-FL02-SQ03 3000k

Lamp Type:

Luminous Width: 0 mm

Luminous Length: 0 mm

Luminous Height: 0 mm

Voltage(V): 219.59 V

Current(A): 0.1780 A

Power(W): 37.06 W

Power Factor: 0.9470

Lamp Luminous Flux: 3580.00

Photometric Results

CIE Class: Direct

Luminaire Luminous Flux: 3579.999

Downward Ratio: 100.00%

Luminaire Efficacy Rating(LER): 96.61 lm/W

Beam Angle(50%Imax): L=-10.37 R=8.48

Field Angle(10%Imax): L=-18.71 R=16.76

Max. Intensity: 23245.28 cd


Max.Intensity Angle: C=0 Gamma=3

Upward Ratio: 0.00%


Efficacy: 100.00%

Center Intensity: 21793.78 cd

Luminous Intensity Distribution Curve



LX-DISTANCE DIAGRAM





LSL™ LED Flood Light

SKU: 151351

Distribution Diagram

LUMINAIRE PHOTOMETRIC TEST REPORT



Luminaire Property

Manufacturer:

Luminaire Type: WN-FL02-SQ03 3000K

Luminous Width: 0 mm

Luminous Length: 0 mm

Luminous Height: 0 mm

Voltage(V): 219.54 V

Current(A): 0.1770 A

Power(W): 36.88 W

Power Factor: 0.9470

Lamp Luminous Flux: 2764.79

Photometric Results

CIE Class: Direct

Luminaire Luminous Flux: 2764.792

Downward Ratio: 100.00%

Luminaire Efficacy Rating(LER): 74.97 lm/W

Beam Angle(50%Imax): L=-7.39 R=5.58

Field Angle(10%Imax): L=-11.67 R=10.60

Max. Intensity: 38376.31 cd


Max.Intensity Angle: C=0 Gamma=1

Upward Ratio: 0.00%


Efficacy: 100.00%

Center Intensity: 38128.49 cd

Luminous Intensity Distribution Curve



LX-DISTANCE DIAGRAM





SKU: 151331

Distribution Diagram

LUMINAIRE PHOTOMETRIC TEST REPORT



Luminaire Property

Manufacturer:
Luminaire Type: WN-FL07-01 3000k
Lamp Type:
Luminous Width: 0 mm
Luminous Length: 0 mm
Luminous Height: 0 mm


Voltage(V): 220.46 V
Current(A): 0.4760 A
Power(W): 103.55 W
Power Factor: 0.9860
Lamp Luminous Flux: 10142.02

Photometric Results


CIE Class: Direct
Luminaire Luminous Flux: 10142.01
Downward Ratio: 100.00%
Luminaire Efficacy Rating(LER): 97.94 lm/W
Beam Angle(50%Imax): L=-16.42 R=14.84
Field Angle(10%Imax): L=-29.22 R=27.83

Max. Intensity: 30757.69 cd
Max.Intensity Angle: C=180 Gamma=3
Upward Ratio: 0.00%
Efficacy: 100.00%
Center Intensity: 30527.57 cd

Luminous Intensity Distribution Curve



LX-DISTANCE DIAGRAM





LSLTM

LED Flood Light

SKU: 151332

Distribution Diagram

LUMINAIRE PHOTOMETRIC TEST REPORT



Luminaire Property

Manufacturer:

Luminaire Type: WN-FL07-01 Green

Lamp Type:

Luminous Width: 0 mm

Luminous Length: 0 mm

Luminous Height: 0 mm

Voltage(V): 220.19 V

Current(A): 0.4230 A

Power(W): 91.71 W

Power Factor: 0.9830

Lamp Luminous Flux: 6834.41

Photometric Results

CIE Class: Direct

Luminaire Luminous Flux: 6834.412

Downward Ratio: 100.00%

Luminaire Efficacy Rating(LER): 74.52 lm/W

Beam Angle(50%Imax): L=-11.57 R=11.17

Field Angle(10%Imax): L=-23.73 R=22.41

Max. Intensity: 33101.34 cd


Max.Intensity Angle: C=0 Gamma=1

Upward Ratio: 0.00%


Efficacy: 100.00%

Center Intensity: 32839.36 cd

Luminous Intensity Distribution Curve



LX-DISTANCE DIAGRAM



LSL™ LED Flood Light



SKU: 151333

Distribution Diagram

LUMINAIRE PHOTOMETRIC TEST REPORT



Luminaire Property

Manufacturer:

Luminaire Type: WN-FL07-01 Blue

Lamp Type:

Luminous Width: 0 mm

Luminous Length: 0 mm

Luminous Height: 0 mm

Voltage(V): 219.99 V

Current(A): 0.3750 A

Power(W): 80.89 W

Power Factor: 0.9790

Lamp Luminous Flux: 1318.41

Photometric Results

CIE Class: Direct

Luminaire Luminous Flux: 1318.405

Downward Ratio: 100.00%

Luminaire Efficacy Rating(LER): 16.30 lm/W

Beam Angle(50%Imax): L=-9.52 R=11.19

Field Angle(10%Imax): L=-22.39 R=23.72



Max. Intensity: 5367.02 cd

Max.Intensity Angle: C=135 Gamma=2

Upward Ratio: 0.00%

Efficacy: 100.00%

Center Intensity: 5136.90 cd



LED FLOOD LIGHT



LSL™

LED Flood Light

Installation

36 Watt



I .Feature:

Quality aviation die-casting Aluminium, Polishing, Nano electrostatic spraying, large plate tough heat dissipation design, ensure long life span in the bad environment. With tempered glass and silicon sealed IP65 design, water proof, cross-ion proof, used in rainy and cold area.

II .Attention:

- 1.Make sure that the voltage is within the permissible range
- 2.Switch off the power supply before installation
- 3.Keep away from the cover and do not stare at the lamp when it electrified
- 4.The luminaire should be installed by a professional electrician.
- 5.Storage temperature:-65°C~+50°C, working temperature: -30°C~+50°C, best working temperature:-0°C~+30°C
- 6.Because the luminaire includes glass accessories, please be careful when moving it.

LSL™


LED Flood Light




Installation

III. Installation diagram


1. Available in ground-mounting, wall-mounting installation and ceiling mounting installation
2. The rotation angle of the bracket is up to 180 degrees
3. Install the floodlight onto the ground, wall, or ceiling and fix it with screw
4. Then connect it with power installation.





Wall mounting



Ground mounting



Ceiling mounting



IV. Maintenance

1. Before Maintain, please cut out the power.
2. Clean the luminaire glass regularly, to keep the good transmission of light.
3. Keep the luminaire heat sinker and housing clean, to make sure good heat dissipation.
4. Please not use water or corrosion liquid to clean the luminaire, better use dry staff.
5. When change the power supply, use the screw driver to open the back cover, connect the wire based on the original color.



LSL™

LED Flood Light

Installation

100 Watt



I .Feature:

Quality aviation die-casting Aluminium, Polishing, Nano electrostatic spraying, large plate tough heat dissipation design, ensure long life span in the bad environment. With tempered glass and silicon sealed IP65 design, water proof, cross-ion proof, used in rainy and cold area.

II .Attention:

- 1.Make sure that the voltage is within the permissible range
- 2.Switch off the power supply before installation
- 3.Keep away from the cover and do not stare at the lamp when it electrified
- 4.The luminaire should be installed by a professional electrician.
- 5.Storage temperature:-65°C~+50°C, working temperature: -30°C~+50°C, best working temperature:-0°C~+30°C
- 6.Because the luminaire includes glass accessories, please be careful when moving it.

LSL™


LED Flood Light




Installation

III. Installation diagram


1. Available in ground-mounting, wall-mounting installation and ceiling mounting installation
2. The rotation angle of the bracket is up to 180 degrees
3. Install the floodlight onto the ground, wall, or ceiling and fix it with screw
4. Then connect it with power installation.





Wall mounting



Ground mounting



Ceiling mounting



IV. Maintenance

1. Before Maintain, please cut out the power.
2. Clean the luminaire glass regularly, to keep the good transmission of light.
3. Keep the luminaire heat sinker and housing clean, to make sure good heat dissipation.
4. Please not use water or corrosion liquid to clean the luminaire, better use dry staff.
5. When change the power supply, use the screw driver to open the back cover, connect the wire based on the original color.



LSL™

LED Flood Light

Packaging

SKU#	Box Dimension	Qty	Net Weight	Gross Weight
151350	24" X 11" X 14"	4 Pcs/Box		
151351	24" X 11" X 14"	4 Pcs/Box		
151331	18" X 12" X 7"	1 Pc/Box		
151332	18" X 12" X 7"	1 Pc/Box		
151333	18" X 12" X 7"	1 Pc/Box		

Application Image



LSL™

LED Flood Light



Application Image



LED FLOOD LIGHT

Warranty

This product is covered under a 5-year warranty. For complete warranty details, [Click Here.](#)