



Foot switch with metal enclosure


GF 2 1ÖS/1ÖS

Article no.: 1048770 (old article no.: 82105001)

Product features

- 2-pedal type
- Metal enclosure
- Low pedal height
- Wiring compartment

Dimensions



Technical data

Applied standards
EN 60947-5-1

Enclosure
aluminium die-cast, powder-coated

Cover
aluminium die-cast, powder-coated

Pedal
thermoplastic, glass-fibre reinforced, shockproof, self-extinguishing UL 94 V-0

Degree of protection
IP65 (IEC/EN 60529)

B_{10d} (10 % load)
2 million

T_M
max. 20 years

Connection
screw connection terminals

Cable cross-section
max. 2.5 mm² (incl. conductor ferrules)

Cable entry
1 x M25 x 1.5

Contact material
silver

Switching system
slow action, positive break NC contacts ⊖

Switching elements
1 NC/1 NO contact, type Zb

Switch insert
1 x ES 60 GF per pedal

Utilisation category
AC-15

Rated operating current/voltage I_e/U_e
16 A/400 VAC

Short-circuit protection
16 A gG/gN fuse

Ambient temperature
-25 °C ... +80 °C

Mechanical life
> 1 million operations

Approvals
cULus CCC

Weight
1920 g


Errors and omissions excepted.



Foot switch with metal enclosure GF 2 1ÖS/1ÖS

Article no.: 1048770 (old article no.: 82105001)

Contact diagram



Switching diagram

